

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298488

Luminaire Tested: P3AS13R60W2N902765DE010 E3DLP1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298488
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60W2N902765DE010 E3DLP1LI_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 561.0 lumens
Efficiency: N/A
Efficacy: 45.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298488
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLP1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298488

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLP1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.8	10.5
10°-20°	142.8	25.5
20°-30°	156.6	27.9
30°-40°	114.1	20.3
40°-50°	53.9	9.6
50°-60°	17.7	3.1
60°-70°	10.0	1.8
70°-80°	5.4	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	358.2	63.9
0°-40°	472.4	84.2
0°-60°	543.9	97.0
0°-90°	561.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	561.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	631	59
15°	514	143
25°	343	157
35°	182	114
45°	68	54
55°	18	18
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298488

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLP1LI_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	648.4
2.5°	644.5
5°	631.4
7.5°	611.4
10°	584.4
12.5°	552.0
15°	514.2
17.5°	473.4
20°	430.2
22.5°	386.2
25°	343.1
27.5°	299.9
30°	259.0
32.5°	219.7
35°	181.9
37.5°	148.0
40°	117.2
42.5°	90.2
45°	67.8
47.5°	49.3
50°	33.9
52.5°	22.4
55°	17.7
57.5°	15.4
60°	13.9
62.5°	11.6
65°	10.0
67.5°	8.5
70°	6.9
72.5°	6.2
75°	5.4
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)