

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298568

Luminaire Tested: P3AS13R65W2N902750DE010 E3DL1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298568
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902750DE010 E3DL1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 695.0 lumens
Efficiency: N/A
Efficacy: 56.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298568
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1298568
 CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	9.9
10°-20°	178.9	25.7
20°-30°	209.1	30.1
30°-40°	146.1	21.0
40°-50°	64.3	9.3
50°-60°	14.3	2.1
60°-70°	7.3	1.0
70°-80°	4.4	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	457.1	65.8
0°-40°	603.2	86.8
0°-60°	681.8	98.1
0°-90°	695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	695.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	747	
5°	736	69
15°	643	179
25°	461	209
35°	232	146
45°	81	64
55°	12	14
65°	8	7
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P1298568
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1H_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	747.4
2.5°	744.7
5°	735.7
7.5°	720.4
10°	699.7
12.5°	674.0
15°	642.8
17.5°	604.7
20°	562.5
22.5°	514.7
25°	460.7
27.5°	403.9
30°	344.3
32.5°	286.8
35°	232.1
37.5°	184.3
40°	142.0
42.5°	107.4
45°	81.0
47.5°	59.6
50°	37.4
52.5°	19.4
55°	11.8
57.5°	10.4
60°	9.0
62.5°	8.3
65°	7.6
67.5°	6.2
70°	5.5
72.5°	4.8
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)