

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298615

Luminaire Tested: P3AS13R65W2N902750DE010 E3DLD1WH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902750DE010 E3DLD1WH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 611.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298615
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLD1WH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1298615

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLD1WH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	7.5
10°-20°	120.5	19.7
20°-30°	154.8	25.3
30°-40°	143.3	23.4
40°-50°	86.5	14.2
50°-60°	29.5	4.8
60°-70°	17.7	2.9
70°-80°	10.0	1.6
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	321.2	52.6
0°-40°	464.4	76.0
0°-60°	580.4	95.0
0°-90°	611.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	611.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	496	
5°	487	46
15°	431	120
25°	338	155
35°	230	143
45°	112	86
55°	29	29
65°	18	18
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1298615
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLD1WH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	495.8
2.5°	493.5
5°	487.3
7.5°	478.0
10°	465.6
12.5°	450.1
15°	430.7
17.5°	409.7
20°	386.4
22.5°	362.4
25°	338.3
27.5°	312.7
30°	286.3
32.5°	260.0
35°	230.5
37.5°	201.8
40°	171.5
42.5°	141.2
45°	111.7
47.5°	84.6
50°	59.0
52.5°	37.2
55°	28.7
57.5°	25.6
60°	23.3
62.5°	20.2
65°	17.8
67.5°	15.5
70°	13.2
72.5°	11.6
75°	9.3
77.5°	7.8
80°	5.4
82.5°	3.9
85°	2.3
87.5°	1.6
90°	0.0

(END OF REPORT)