

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298634

Luminaire Tested: P3AS13R65W2N902750DE010 E3DLP1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902750DE010 E3DLP1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 530.0 lumens
Efficiency: N/A
Efficacy: 43.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298634
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLP1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298634

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLP1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.5	10.5
10°-20°	134.2	25.3
20°-30°	148.4	28.0
30°-40°	107.8	20.3
40°-50°	50.5	9.5
50°-60°	17.0	3.2
60°-70°	9.8	1.9
70°-80°	5.1	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.1	63.8
0°-40°	445.9	84.1
0°-60°	513.4	96.9
0°-90°	530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	530.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	614	
5°	597	55
15°	483	134
25°	326	148
35°	172	108
45°	63	50
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298634
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLP1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	614.4
2.5°	610.5
5°	596.8
7.5°	576.2
10°	549.4
12.5°	518.1
15°	482.9
17.5°	444.7
20°	405.8
22.5°	365.3
25°	325.5
27.5°	285.0
30°	245.3
32.5°	207.1
35°	171.9
37.5°	139.8
40°	110.8
42.5°	84.8
45°	63.4
47.5°	45.8
50°	31.3
52.5°	21.4
55°	17.6
57.5°	15.3
60°	13.0
62.5°	11.5
65°	9.9
67.5°	8.4
70°	6.9
72.5°	6.1
75°	4.6
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)