

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298648

Luminaire Tested: P3AS13R65W2N902750DE010 E3DLP1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R65W2N902750DE010 E3DLP1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 480.0 lumens
Efficiency: N/A
Efficacy: 39.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298648
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLP1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1298648

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLP1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	10.5
10°-20°	121.6	25.3
20°-30°	134.4	28.0
30°-40°	97.6	20.3
40°-50°	45.7	9.5
50°-60°	15.4	3.2
60°-70°	8.9	1.9
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.2	63.8
0°-40°	403.8	84.1
0°-60°	464.9	96.9
0°-90°	480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	480.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	556	
5°	540	50
15°	437	122
25°	295	134
35°	156	98
45°	57	46
55°	16	15
65°	9	9
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1298648

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLP1WMH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	556.4
2.5°	552.9
5°	540.5
7.5°	521.8
10°	497.6
12.5°	469.2
15°	437.4
17.5°	402.8
20°	367.5
22.5°	330.8
25°	294.8
27.5°	258.1
30°	222.1
32.5°	187.5
35°	155.7
37.5°	126.6
40°	100.3
42.5°	76.8
45°	57.4
47.5°	41.5
50°	28.4
52.5°	19.4
55°	15.9
57.5°	13.8
60°	11.8
62.5°	10.4
65°	9.0
67.5°	7.6
70°	6.2
72.5°	5.5
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)