

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298807

Luminaire Tested: P3AS13R65W2N902765DE010 E3DLP1LI\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298807  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R65W2N902765DE010 E3DLP1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 535.0 lumens  
Efficiency: N/A  
Efficacy: 43.5 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298807  
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLP1LI\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298807

CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLP1LI\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.0	10.5
10°-20°	135.5	25.3
20°-30°	149.8	28.0
30°-40°	108.8	20.3
40°-50°	51.0	9.5
50°-60°	17.1	3.2
60°-70°	9.9	1.9
70°-80°	5.2	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.3	63.8
0°-40°	450.1	84.1
0°-60°	518.2	96.9
0°-90°	535.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	535.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	620	
5°	602	56
15°	488	135
25°	329	150
35°	174	109
45°	64	51
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298807  
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLP1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	620.2
2.5°	616.3
5°	602.4
7.5°	581.6
10°	554.6
12.5°	523.0
15°	487.5
17.5°	448.9
20°	409.6
22.5°	368.7
25°	328.6
27.5°	287.7
30°	247.6
32.5°	209.0
35°	173.6
37.5°	141.2
40°	111.8
42.5°	85.6
45°	64.0
47.5°	46.3
50°	31.6
52.5°	21.6
55°	17.7
57.5°	15.4
60°	13.1
62.5°	11.6
65°	10.0
67.5°	8.5
70°	6.9
72.5°	6.2
75°	4.6
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)