

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298819

Luminaire Tested: P3AS13R65W2N902765DE010 E3DLP1WH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298819  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R65W2N902765DE010 E3DLP1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 774.0 lumens  
Efficiency: N/A  
Efficacy: 62.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298819  
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLP1WH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298819  
 CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLP1WH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.9	9.9
10°-20°	199.2	25.7
20°-30°	232.9	30.1
30°-40°	162.7	21.0
40°-50°	71.6	9.3
50°-60°	15.9	2.1
60°-70°	8.1	1.0
70°-80°	4.9	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	509.0	65.8
0°-40°	671.7	86.8
0°-60°	759.3	98.1
0°-90°	774.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	774.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	832	
5°	819	77
15°	716	199
25°	513	233
35°	258	163
45°	90	72
55°	13	16
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298819  
CATALOG NUMBER: P3AS13R65W2N902765DE010 E3DLP1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	832.4
2.5°	829.3
5°	819.3
7.5°	802.3
10°	779.2
12.5°	750.6
15°	715.9
17.5°	673.5
20°	626.4
22.5°	573.2
25°	513.0
27.5°	449.8
30°	383.4
32.5°	319.4
35°	258.4
37.5°	205.2
40°	158.2
42.5°	119.6
45°	90.3
47.5°	66.3
50°	41.7
52.5°	21.6
55°	13.1
57.5°	11.6
60°	10.0
62.5°	9.3
65°	8.5
67.5°	6.9
70°	6.2
72.5°	5.4
75°	4.6
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)