

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299071

Luminaire Tested: P3AS13R70W2N902765DE010 E3DLP1LI_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70W2N902765DE010 E3DLP1LI_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 6500K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 554.0 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299071
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1LI_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299071

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1LI_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.1	9.8
10°-20°	133.8	24.2
20°-30°	152.4	27.5
30°-40°	119.1	21.5
40°-50°	58.5	10.6
50°-60°	18.0	3.2
60°-70°	10.7	1.9
70°-80°	5.7	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.3	61.4
0°-40°	459.4	82.9
0°-60°	535.9	96.7
0°-90°	554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	593	
5°	580	54
15°	481	134
25°	333	152
35°	191	119
45°	75	59
55°	18	18
65°	11	11
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1299071

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1LI_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	592.6
2.5°	589.5
5°	579.5
7.5°	563.3
10°	540.2
12.5°	513.2
15°	480.9
17.5°	446.2
20°	409.2
22.5°	370.7
25°	332.9
27.5°	295.9
30°	260.5
32.5°	225.0
35°	191.1
37.5°	158.7
40°	127.9
42.5°	99.4
45°	74.7
47.5°	52.4
50°	33.9
52.5°	22.3
55°	18.5
57.5°	16.2
60°	13.9
62.5°	12.3
65°	10.8
67.5°	9.2
70°	7.7
72.5°	6.2
75°	5.4
77.5°	4.6
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)