

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299353

Luminaire Tested: P3AS17R15W2N902765DE010 E3DL1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902765DE010 E3DL1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 735.0 lumens
Efficiency: N/A
Efficacy: 37.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299353
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299353

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	16.0
10°-20°	217.5	29.6
20°-30°	193.6	26.3
30°-40°	114.6	15.6
40°-50°	47.0	6.4
50°-60°	22.1	3.0
60°-70°	13.4	1.8
70°-80°	7.1	1.0
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.0	72.0
0°-40°	643.6	87.6
0°-60°	712.7	97.0
0°-90°	735.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	735.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1445	
5°	1331	118
15°	778	218
25°	424	194
35°	179	115
45°	57	47
55°	24	22
65°	13	13
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1299353

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DL1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1445.4
1°	1441.8
2°	1431.1
3°	1409.6
4°	1373.8
5°	1330.8
6°	1284.3
7°	1229.4
8°	1172.1
9°	1113.6
10°	1050.3
12.5°	905.9
15°	778.2
17.5°	668.4
20°	576.5
22.5°	495.3
25°	423.7
27.5°	354.5
30°	290.0
32.5°	231.6
35°	179.0
37.5°	137.3
40°	102.6
42.5°	76.4
45°	57.3
47.5°	44.2
50°	34.6
52.5°	28.6
55°	23.9
57.5°	20.3
60°	17.9
62.5°	15.5
65°	13.1
67.5°	11.9
70°	9.5
72.5°	8.4
75°	7.2
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)