

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299369

Luminaire Tested: P3AS17R15W2N902765DE010 E3DLD1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902765DE010 E3DLD1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 6500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 466.0 lumens
Efficiency: N/A
Efficacy: 24.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299369
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299369

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	10.3
10°-20°	112.4	24.1
20°-30°	123.8	26.6
30°-40°	92.7	19.9
40°-50°	48.1	10.3
50°-60°	19.9	4.3
60°-70°	12.3	2.6
70°-80°	6.9	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	284.1	61.0
0°-40°	376.8	80.8
0°-60°	444.7	95.4
0°-90°	466.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	466.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	536	
5°	520	48
15°	403	112
25°	271	124
35°	147	93
45°	60	48
55°	21	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1299369
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	536.0
1°	536.6
2°	534.9
3°	531.3
4°	526.0
5°	519.5
6°	511.2
7°	502.4
8°	491.8
9°	480.5
10°	469.3
12.5°	436.9
15°	403.2
17.5°	369.6
20°	336.5
22.5°	302.8
25°	271.0
27.5°	239.1
30°	207.2
32.5°	175.9
35°	147.0
37.5°	122.2
40°	99.8
42.5°	79.1
45°	60.2
47.5°	45.5
50°	34.2
52.5°	25.4
55°	20.7
57.5°	18.3
60°	15.9
62.5°	14.2
65°	12.4
67.5°	10.6
70°	9.4
72.5°	7.7
75°	6.5
77.5°	5.3
80°	4.1
82.5°	3.0
85°	1.8
87.5°	0.6
90°	0.0

(END OF REPORT)