

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299421

Luminaire Tested: P3AS17R15W2N902765DE010 E3DLP1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R15W2N902765DE010 E3DLP1MW_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 745.9 lumens
Efficiency: N/A
Efficacy: 38.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299421
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLP1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299421

CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLP1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	16.0
10°-20°	220.8	29.6
20°-30°	196.5	26.3
30°-40°	116.3	15.6
40°-50°	47.7	6.4
50°-60°	22.4	3.0
60°-70°	13.6	1.8
70°-80°	7.2	1.0
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.0	72.0
0°-40°	653.3	87.6
0°-60°	723.4	97.0
0°-90°	745.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	745.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1467	
5°	1351	120
15°	790	221
25°	430	197
35°	182	116
45°	58	48
55°	24	22
65°	13	14
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1299421
CATALOG NUMBER: P3AS17R15W2N902765DE010 E3DLP1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1467.0
1°	1463.4
2°	1452.5
3°	1430.7
4°	1394.3
5°	1350.7
6°	1303.5
7°	1247.8
8°	1189.6
9°	1130.3
10°	1066.1
12.5°	919.5
15°	789.8
17.5°	678.4
20°	585.1
22.5°	502.7
25°	430.1
27.5°	359.8
30°	294.4
32.5°	235.0
35°	181.7
37.5°	139.3
40°	104.2
42.5°	77.5
45°	58.1
47.5°	44.8
50°	35.1
52.5°	29.1
55°	24.2
57.5°	20.6
60°	18.2
62.5°	15.7
65°	13.3
67.5°	12.1
70°	9.7
72.5°	8.5
75°	7.3
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)