

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299579

Luminaire Tested: P3AS17R20W2N902750DE010 E3PHLP1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R20W2N902750DE010 E3PHLP1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 530.0 lumens
Efficiency: N/A
Efficacy: 27.3 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299579
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3PHLP1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1299579

CATALOG NUMBER: P3AS17R20W2N902750DE010 E3PHLP1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.6	13.5
10°-20°	136.6	25.8
20°-30°	120.2	22.7
30°-40°	77.6	14.6
40°-50°	41.1	7.8
50°-60°	30.9	5.8
60°-70°	26.3	5.0
70°-80°	18.5	3.5
80°-90°	7.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.4	62.0
0°-40°	406.0	76.6
0°-60°	478.0	90.2
0°-90°	530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	530.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	860	
5°	799	72
15°	491	137
25°	260	120
35°	122	78
45°	50	41
55°	34	31
65°	26	26
75°	17	19
85°	6	7
90°	0	



TEST NUMBER: P1299579
CATALOG NUMBER: P3AS17R20W2N902750DE010 E3PHLP1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	859.5
2.5°	842.3
5°	798.7
7.5°	731.6
10°	655.2
12.5°	570.9
15°	491.4
17.5°	419.6
20°	358.8
22.5°	307.3
25°	260.5
27.5°	219.9
30°	184.1
32.5°	151.3
35°	121.7
37.5°	98.3
40°	78.0
42.5°	62.4
45°	49.9
47.5°	43.7
50°	39.0
52.5°	35.9
55°	34.3
57.5°	32.8
60°	31.2
62.5°	28.1
65°	26.5
67.5°	25.0
70°	21.8
72.5°	20.3
75°	17.2
77.5°	15.6
80°	12.5
82.5°	10.9
85°	6.2
87.5°	3.1
90°	0.0

(END OF REPORT)