

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300980

Luminaire Tested: P3AS17R40W2N902765DE010 E3DL1LI_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R40W2N902765DE010 E3DL1LI_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1404.0 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300980
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DL1LI_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1300980

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DL1LI_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	18.0
10°-20°	542.4	38.6
20°-30°	387.1	27.6
30°-40°	142.5	10.2
40°-50°	44.9	3.2
50°-60°	15.6	1.1
60°-70°	10.7	0.8
70°-80°	6.3	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1182.1	84.2
0°-40°	1324.6	94.3
0°-60°	1385.1	98.7
0°-90°	1404.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1404.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2833	
5°	2740	253
15°	1992	542
25°	834	387
35°	211	143
45°	55	45
55°	17	16
65°	11	11
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1300980
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DL1LI_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2833.2
2.5°	2811.5
5°	2740.4
7.5°	2622.3
10°	2458.4
12.5°	2249.9
15°	1992.0
17.5°	1702.8
20°	1397.9
22.5°	1097.8
25°	833.9
27.5°	612.2
30°	431.4
32.5°	302.5
35°	210.9
37.5°	149.4
40°	107.3
42.5°	77.1
45°	55.4
47.5°	37.4
50°	25.3
52.5°	18.1
55°	16.9
57.5°	15.7
60°	13.3
62.5°	12.1
65°	10.8
67.5°	9.6
70°	8.4
72.5°	7.2
75°	6.0
77.5°	4.8
80°	3.6
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)