

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301030

Luminaire Tested: P3AS17R40W2N902765DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301030
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R40W2N902765DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1067.0 lumens
Efficiency: N/A
Efficacy: 55.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301030
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301030

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	9.3
10°-20°	247.1	23.2
20°-30°	285.6	26.8
30°-40°	225.1	21.1
40°-50°	115.5	10.8
50°-60°	44.2	4.1
60°-70°	29.2	2.7
70°-80°	15.9	1.5
80°-90°	4.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	632.3	59.3
0°-40°	857.4	80.4
0°-60°	1017.2	95.3
0°-90°	1067.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1067.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1092	
5°	1068	100
15°	887	247
25°	624	286
35°	360	225
45°	149	116
55°	47	44
65°	30	29
75°	16	16
85°	4	5
90°	0	



TEST NUMBER: P1301030
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1092.3
2.5°	1086.3
5°	1068.4
7.5°	1037.4
10°	995.6
12.5°	946.7
15°	887.0
17.5°	824.9
20°	758.0
22.5°	690.0
25°	624.3
27.5°	558.7
30°	494.2
32.5°	428.6
35°	360.5
37.5°	297.2
40°	239.9
42.5°	191.0
45°	149.2
47.5°	108.6
50°	74.0
52.5°	53.7
55°	46.6
57.5°	41.8
60°	38.2
62.5°	33.4
65°	29.8
67.5°	25.1
70°	21.5
72.5°	17.9
75°	15.5
77.5°	11.9
80°	8.4
82.5°	7.2
85°	3.6
87.5°	2.4
90°	0.0

(END OF REPORT)