

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301059

Luminaire Tested: P3AS17R40W2N902765DE010 E3DLP1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301059
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R40W2N902765DE010 E3DLP1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1261.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301059
CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLP1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301059

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLP1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	226.9	18.0
10°-20°	487.2	38.6
20°-30°	347.7	27.6
30°-40°	128.0	10.1
40°-50°	40.3	3.2
50°-60°	14.0	1.1
60°-70°	9.6	0.8
70°-80°	5.7	0.5
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1061.7	84.2
0°-40°	1189.7	94.3
0°-60°	1244.0	98.7
0°-90°	1261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2545	
5°	2461	227
15°	1789	487
25°	749	348
35°	189	128
45°	50	40
55°	15	14
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1301059

CATALOG NUMBER: P3AS17R40W2N902765DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2544.6
2.5°	2525.1
5°	2461.3
7.5°	2355.2
10°	2208.0
12.5°	2020.8
15°	1789.1
17.5°	1529.4
20°	1255.5
22.5°	986.0
25°	749.0
27.5°	549.8
30°	387.5
32.5°	271.7
35°	189.4
37.5°	134.2
40°	96.3
42.5°	69.3
45°	49.8
47.5°	33.6
50°	22.7
52.5°	16.2
55°	15.2
57.5°	14.1
60°	11.9
62.5°	10.8
65°	9.7
67.5°	8.7
70°	7.6
72.5°	6.5
75°	5.4
77.5°	4.3
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)