

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301274

Luminaire Tested: P3AS17R45W2N902765DE010 E3DLD1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R45W2N902765DE010 E3DLD1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 459.9 lumens
Efficiency: N/A
Efficacy: 23.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301274
CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLD1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301274

CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLD1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.7	8.8
10°-20°	101.4	22.0
20°-30°	120.5	26.2
30°-40°	104.7	22.8
40°-50°	52.5	11.4
50°-60°	18.2	4.0
60°-70°	12.7	2.8
70°-80°	7.1	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	262.5	57.1
0°-40°	367.2	79.8
0°-60°	437.9	95.2
0°-90°	459.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	459.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	445	
5°	435	41
15°	364	101
25°	262	120
35°	170	105
45°	67	52
55°	20	18
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1301274
CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLD1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	444.8
2.5°	442.7
5°	435.2
7.5°	423.6
10°	407.1
12.5°	387.0
15°	364.2
17.5°	338.7
20°	313.3
22.5°	287.3
25°	262.4
27.5°	238.6
30°	215.2
32.5°	193.0
35°	169.6
37.5°	144.7
40°	118.2
42.5°	92.2
45°	66.8
47.5°	44.0
50°	28.1
52.5°	21.7
55°	19.6
57.5°	18.0
60°	16.4
62.5°	14.8
65°	12.7
67.5°	11.1
70°	9.5
72.5°	8.0
75°	6.9
77.5°	5.3
80°	4.2
82.5°	3.2
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)