

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301286

Luminaire Tested: P3AS17R45W2N902765DE010 E3DLD1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301286
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R45W2N902765DE010 E3DLD1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 939.0 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301286
CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLD1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301286

CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLD1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.0	8.8
10°-20°	207.0	22.0
20°-30°	245.9	26.2
30°-40°	213.7	22.8
40°-50°	107.2	11.4
50°-60°	37.2	4.0
60°-70°	26.1	2.8
70°-80°	14.6	1.6
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.9	57.1
0°-40°	749.6	79.8
0°-60°	894.0	95.2
0°-90°	939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	908	
5°	888	83
15°	743	207
25°	536	246
35°	346	214
45°	136	107
55°	40	37
65°	26	26
75°	14	15
85°	3	4
90°	0	



TEST NUMBER: P1301286
CATALOG NUMBER: P3AS17R45W2N902765DE010 E3DLD1LI_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	907.9
2.5°	903.6
5°	888.4
7.5°	864.6
10°	831.1
12.5°	790.0
15°	743.4
17.5°	691.5
20°	639.5
22.5°	586.5
25°	535.7
27.5°	487.0
30°	439.4
32.5°	393.9
35°	346.3
37.5°	295.4
40°	241.3
42.5°	188.3
45°	136.4
47.5°	89.8
50°	57.4
52.5°	44.4
55°	40.0
57.5°	36.8
60°	33.5
62.5°	30.3
65°	26.0
67.5°	22.7
70°	19.5
72.5°	16.2
75°	14.1
77.5°	10.8
80°	8.7
82.5°	6.5
85°	3.2
87.5°	2.2
90°	0.0

(END OF REPORT)