

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301882

Luminaire Tested: P3AS17R55W2N902765DE010 E3DL1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301882
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R55W2N902765DE010 E3DL1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1180.0 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301882
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DL1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1301882

CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DL1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.0	11.6
10°-20°	348.7	29.6
20°-30°	365.5	31.0
30°-40°	213.2	18.1
40°-50°	79.8	6.8
50°-60°	18.8	1.6
60°-70°	9.6	0.8
70°-80°	5.7	0.5
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	851.2	72.1
0°-40°	1064.5	90.2
0°-60°	1163.0	98.6
0°-90°	1180.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1180.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1478	
5°	1457	137
15°	1261	349
25°	806	365
35°	333	213
45°	97	80
55°	15	19
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1301882
CATALOG NUMBER: P3AS17R55W2N902765DE010 E3DL1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1477.6
2.5°	1473.3
5°	1457.1
7.5°	1431.1
10°	1391.0
12.5°	1334.8
15°	1261.1
17.5°	1168.0
20°	1058.7
22.5°	936.4
25°	806.5
27.5°	673.3
30°	546.7
32.5°	431.9
35°	333.4
37.5°	253.3
40°	187.3
42.5°	134.2
45°	97.4
47.5°	70.4
50°	47.6
52.5°	27.1
55°	15.2
57.5°	13.0
60°	11.9
62.5°	10.8
65°	9.7
67.5°	8.7
70°	7.6
72.5°	6.5
75°	5.4
77.5°	4.3
80°	3.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)