

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302063

Luminaire Tested: P3AS17R60W2N902750DE010 E3DL1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302063
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DL1WH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 875.9 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302063
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DL1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302063

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DL1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.8	10.5
10°-20°	223.0	25.5
20°-30°	244.6	27.9
30°-40°	178.2	20.3
40°-50°	84.2	9.6
50°-60°	27.6	3.1
60°-70°	15.6	1.8
70°-80°	8.4	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	559.4	63.9
0°-40°	737.6	84.2
0°-60°	849.3	97.0
0°-90°	875.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	875.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1012	
5°	986	92
15°	803	223
25°	536	245
35°	284	178
45°	106	84
55°	28	28
65°	16	16
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1302063
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DL1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1012.4
2.5°	1006.4
5°	985.9
7.5°	954.6
10°	912.5
12.5°	861.9
15°	803.0
17.5°	739.2
20°	671.7
22.5°	603.1
25°	535.7
27.5°	468.3
30°	404.5
32.5°	343.1
35°	284.1
37.5°	231.1
40°	183.0
42.5°	140.8
45°	105.9
47.5°	77.0
50°	53.0
52.5°	34.9
55°	27.7
57.5°	24.1
60°	21.7
62.5°	18.1
65°	15.6
67.5°	13.2
70°	10.8
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)