

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302099

Luminaire Tested: P3AS17R60W2N902750DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 386.0 lumens
Efficiency: N/A
Efficacy: 19.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302099
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302099

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	10.5
10°-20°	98.3	25.5
20°-30°	107.8	27.9
30°-40°	78.5	20.3
40°-50°	37.1	9.6
50°-60°	12.1	3.1
60°-70°	6.9	1.8
70°-80°	3.7	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	246.5	63.9
0°-40°	325.0	84.2
0°-60°	374.2	97.0
0°-90°	386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	386.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	446	
5°	434	40
15°	354	98
25°	236	108
35°	125	79
45°	47	37
55°	12	12
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1302099
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	446.1
2.5°	443.5
5°	434.4
7.5°	420.7
10°	402.1
12.5°	379.8
15°	353.8
17.5°	325.7
20°	296.0
22.5°	265.8
25°	236.1
27.5°	206.3
30°	178.2
32.5°	151.2
35°	125.2
37.5°	101.8
40°	80.6
42.5°	62.1
45°	46.7
47.5°	33.9
50°	23.3
52.5°	15.4
55°	12.2
57.5°	10.6
60°	9.5
62.5°	8.0
65°	6.9
67.5°	5.8
70°	4.8
72.5°	4.2
75°	3.7
77.5°	2.7
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)