

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302106

Luminaire Tested: P3AS17R60W2N902750DE010 E3DLP1H_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DLP1H_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3500K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 881.0 lumens
Efficiency: N/A
Efficacy: 45.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302106
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1H_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1302106

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1H_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.3	10.5
10°-20°	224.3	25.5
20°-30°	246.0	27.9
30°-40°	179.2	20.3
40°-50°	84.7	9.6
50°-60°	27.7	3.1
60°-70°	15.7	1.8
70°-80°	8.5	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.6	63.9
0°-40°	741.8	84.2
0°-60°	854.2	97.0
0°-90°	881.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	881.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1018	
5°	992	92
15°	808	224
25°	539	246
35°	286	179
45°	106	85
55°	28	28
65°	16	16
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1302106
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1H_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1018.2
2.5°	1012.2
5°	991.6
7.5°	960.1
10°	917.7
12.5°	866.9
15°	807.5
17.5°	743.4
20°	675.6
22.5°	606.6
25°	538.8
27.5°	471.0
30°	406.8
32.5°	345.1
35°	285.7
37.5°	232.5
40°	184.0
42.5°	141.7
45°	106.5
47.5°	77.5
50°	53.3
52.5°	35.1
55°	27.8
57.5°	24.2
60°	21.8
62.5°	18.2
65°	15.7
67.5°	13.3
70°	10.9
72.5°	9.7
75°	8.5
77.5°	6.1
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)