

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302123

Luminaire Tested: P3AS17R60W2N902750DE010 E3DLP1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302123
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902750DE010 E3DLP1WH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1268.0 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302123
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302123

CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.9	10.0
10°-20°	329.7	26.0
20°-30°	375.8	29.6
30°-40°	266.5	21.0
40°-50°	120.9	9.5
50°-60°	25.7	2.0
60°-70°	12.4	1.0
70°-80°	7.6	0.6
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	832.3	65.6
0°-40°	1098.8	86.7
0°-60°	1245.4	98.2
0°-90°	1268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1365	
5°	1347	127
15°	1188	330
25°	826	376
35°	424	266
45°	152	121
55°	19	26
65°	12	12
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302123
CATALOG NUMBER: P3AS17R60W2N902750DE010 E3DLP1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1365.4
2.5°	1360.6
5°	1347.4
7.5°	1324.5
10°	1293.1
12.5°	1248.5
15°	1188.3
17.5°	1112.4
20°	1023.2
22.5°	926.8
25°	825.5
27.5°	721.9
30°	618.2
32.5°	519.4
35°	424.2
37.5°	339.9
40°	263.9
42.5°	200.1
45°	151.9
47.5°	113.3
50°	74.7
52.5°	34.9
55°	19.3
57.5°	16.9
60°	15.7
62.5°	14.5
65°	12.1
67.5°	10.8
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)