

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302134

Luminaire Tested: P3AS17R60W2N902765DE010 E3CB1MB_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902765DE010 E3CB1MB_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 6500K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1558.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302134
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3CB1MB_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1302134

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3CB1MB_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.2	10.0
10°-20°	449.4	28.8
20°-30°	524.2	33.6
30°-40°	338.3	21.7
40°-50°	75.8	4.9
50°-60°	7.5	0.5
60°-70°	3.6	0.2
70°-80°	2.1	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1129.9	72.5
0°-40°	1468.2	94.2
0°-60°	1551.5	99.6
0°-90°	1558.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1558.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1697	
5°	1623	156
15°	1641	449
25°	1146	524
35°	547	338
45°	83	76
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1302134

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3CB1MB_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1696.6
2.5°	1668.9
5°	1623.1
7.5°	1620.7
10°	1652.1
12.5°	1672.5
15°	1641.2
17.5°	1547.2
20°	1409.9
22.5°	1266.5
25°	1146.0
27.5°	1027.9
30°	888.1
32.5°	724.2
35°	547.1
37.5°	373.6
40°	235.0
42.5°	141.0
45°	83.1
47.5°	48.2
50°	25.3
52.5°	8.4
55°	6.0
57.5°	4.8
60°	4.8
62.5°	3.6
65°	3.6
67.5°	3.6
70°	2.4
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)