

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302204

Luminaire Tested: P3AS17R60W2N902765DE010 E3DL1H_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302204
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902765DE010 E3DL1H_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1275.0 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302204
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1H_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302204

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.6	10.0
10°-20°	331.5	26.0
20°-30°	377.8	29.6
30°-40°	268.0	21.0
40°-50°	121.6	9.5
50°-60°	25.8	2.0
60°-70°	12.4	1.0
70°-80°	7.7	0.6
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	836.9	65.6
0°-40°	1104.9	86.7
0°-60°	1252.3	98.2
0°-90°	1275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1275.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1373	
5°	1355	128
15°	1195	331
25°	830	378
35°	427	268
45°	153	122
55°	19	26
65°	12	12
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302204
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1H_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1373.0
2.5°	1368.1
5°	1354.8
7.5°	1331.8
10°	1300.3
12.5°	1255.4
15°	1194.8
17.5°	1118.5
20°	1028.8
22.5°	931.9
25°	830.1
27.5°	725.9
30°	621.7
32.5°	522.3
35°	426.6
37.5°	341.7
40°	265.4
42.5°	201.2
45°	152.7
47.5°	113.9
50°	75.1
52.5°	35.1
55°	19.4
57.5°	17.0
60°	15.8
62.5°	14.5
65°	12.1
67.5°	10.9
70°	9.7
72.5°	8.5
75°	7.3
77.5°	6.1
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)