

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302208

Luminaire Tested: P3AS17R60W2N902765DE010 E3DL1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902765DE010 E3DL1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1256.0 lumens
Efficiency: N/A
Efficacy: 64.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302208
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302208

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.7	10.0
10°-20°	326.6	26.0
20°-30°	372.2	29.6
30°-40°	264.0	21.0
40°-50°	119.8	9.5
50°-60°	25.4	2.0
60°-70°	12.2	1.0
70°-80°	7.6	0.6
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	824.4	65.6
0°-40°	1088.4	86.7
0°-60°	1233.6	98.2
0°-90°	1256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1352	
5°	1335	126
15°	1177	327
25°	818	372
35°	420	264
45°	150	120
55°	19	25
65°	12	12
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302208
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1LI_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1352.5
2.5°	1347.7
5°	1334.6
7.5°	1311.9
10°	1280.9
12.5°	1236.7
15°	1177.0
17.5°	1101.8
20°	1013.5
22.5°	918.0
25°	817.7
27.5°	715.1
30°	612.4
32.5°	514.5
35°	420.2
37.5°	336.6
40°	261.4
42.5°	198.2
45°	150.4
47.5°	112.2
50°	74.0
52.5°	34.6
55°	19.1
57.5°	16.7
60°	15.5
62.5°	14.3
65°	11.9
67.5°	10.7
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)