

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302225

Luminaire Tested: P3AS17R60W2N902765DE010 E3DL1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R60W2N902765DE010 E3DL1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1139.0 lumens
Efficiency: N/A
Efficacy: 58.7 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302225
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302225

CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.0	10.0
10°-20°	296.1	26.0
20°-30°	337.5	29.6
30°-40°	239.4	21.0
40°-50°	108.6	9.5
50°-60°	23.0	2.0
60°-70°	11.1	1.0
70°-80°	6.9	0.6
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	747.6	65.6
0°-40°	987.0	86.7
0°-60°	1118.7	98.2
0°-90°	1139.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1139.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1226	
5°	1210	114
15°	1067	296
25°	742	338
35°	381	239
45°	136	109
55°	17	23
65°	11	11
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1302225
CATALOG NUMBER: P3AS17R60W2N902765DE010 E3DL1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1226.5
2.5°	1222.2
5°	1210.3
7.5°	1189.7
10°	1161.6
12.5°	1121.5
15°	1067.4
17.5°	999.2
20°	919.1
22.5°	832.5
25°	741.5
27.5°	648.4
30°	555.3
32.5°	466.6
35°	381.1
37.5°	305.3
40°	237.1
42.5°	179.7
45°	136.4
47.5°	101.8
50°	67.1
52.5°	31.4
55°	17.3
57.5°	15.2
60°	14.1
62.5°	13.0
65°	10.8
67.5°	9.7
70°	8.7
72.5°	7.6
75°	6.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)