

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302363

Luminaire Tested: P3AS17R65W2N902750DE010 E3DL1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902750DE010 E3DL1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1086.0 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302363
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DL1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302363

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DL1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.9	9.9
10°-20°	279.6	25.7
20°-30°	326.7	30.1
30°-40°	228.3	21.0
40°-50°	100.5	9.3
50°-60°	22.4	2.1
60°-70°	11.4	1.0
70°-80°	6.9	0.6
80°-90°	2.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.2	65.8
0°-40°	942.5	86.8
0°-60°	1065.4	98.1
0°-90°	1086.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1086.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1168	
5°	1150	108
15°	1004	280
25°	720	327
35°	363	228
45°	127	100
55°	18	22
65°	12	11
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1302363
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DL1H_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1168.0
2.5°	1163.6
5°	1149.6
7.5°	1125.7
10°	1093.3
12.5°	1053.2
15°	1004.5
17.5°	945.0
20°	878.9
22.5°	804.3
25°	719.8
27.5°	631.1
30°	538.0
32.5°	448.1
35°	362.6
37.5°	287.9
40°	221.9
42.5°	167.8
45°	126.6
47.5°	93.1
50°	58.5
52.5°	30.3
55°	18.4
57.5°	16.2
60°	14.1
62.5°	13.0
65°	11.9
67.5°	9.7
70°	8.7
72.5°	7.6
75°	6.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)