

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302442

Luminaire Tested: P3AS17R65W2N902750DE010 E3DLP1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902750DE010 E3DLP1WH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1209.0 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302442
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DLP1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302442

CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DLP1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.2	9.9
10°-20°	311.2	25.7
20°-30°	363.7	30.1
30°-40°	254.2	21.0
40°-50°	111.9	9.3
50°-60°	24.9	2.1
60°-70°	12.7	1.0
70°-80°	7.6	0.6
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	795.1	65.8
0°-40°	1049.3	86.8
0°-60°	1186.1	98.1
0°-90°	1209.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1280	120
15°	1118	311
25°	801	364
35°	404	254
45°	141	112
55°	20	25
65°	13	13
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302442
CATALOG NUMBER: P3AS17R65W2N902750DE010 E3DLP1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1300.2
2.5°	1295.4
5°	1279.8
7.5°	1253.2
10°	1217.1
12.5°	1172.5
15°	1118.3
17.5°	1052.0
20°	978.5
22.5°	895.3
25°	801.4
27.5°	702.5
30°	598.9
32.5°	498.9
35°	403.7
37.5°	320.5
40°	247.0
42.5°	186.8
45°	141.0
47.5°	103.6
50°	65.1
52.5°	33.7
55°	20.5
57.5°	18.1
60°	15.7
62.5°	14.5
65°	13.3
67.5°	10.8
70°	9.6
72.5°	8.4
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)