

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302497

Luminaire Tested: P3AS17R65W2N902765DE010 E3D1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302497
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3D1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1477.1 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302497
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302497

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.7	9.9
10°-20°	405.3	27.4
20°-30°	530.5	35.9
30°-40°	307.3	20.8
40°-50°	65.8	4.5
50°-60°	10.7	0.7
60°-70°	5.9	0.4
70°-80°	3.5	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1082.5	73.3
0°-40°	1389.8	94.1
0°-60°	1466.3	99.3
0°-90°	1477.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1477.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1646	
5°	1543	147
15°	1451	405
25°	1193	531
35°	485	307
45°	78	66
55°	10	11
65°	6	6
75°	4	3
85°	1	1
90°	0	



TEST NUMBER: P1302497

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3D1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1646.0
2.5°	1599.5
5°	1543.3
7.5°	1520.6
10°	1506.3
12.5°	1486.0
15°	1451.3
17.5°	1397.6
20°	1333.1
22.5°	1272.2
25°	1193.3
27.5°	1060.7
30°	886.3
32.5°	686.8
35°	485.0
37.5°	307.0
40°	182.8
42.5°	114.7
45°	77.6
47.5°	50.2
50°	27.5
52.5°	13.1
55°	9.6
57.5°	8.4
60°	7.2
62.5°	7.2
65°	6.0
67.5°	4.8
70°	4.8
72.5°	3.6
75°	3.6
77.5°	2.4
80°	2.4
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)