

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302538

Luminaire Tested: P3AS17R65W2N902765DE010 E3DL1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3DL1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 750.0 lumens
Efficiency: N/A
Efficacy: 38.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302538
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DL1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302538

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DL1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	10.5
10°-20°	189.9	25.3
20°-30°	210.0	28.0
30°-40°	152.5	20.3
40°-50°	71.5	9.5
50°-60°	24.1	3.2
60°-70°	13.9	1.9
70°-80°	7.3	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.4	63.8
0°-40°	630.9	84.1
0°-60°	726.5	96.9
0°-90°	750.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	750.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	869	
5°	844	78
15°	683	190
25°	461	210
35°	243	153
45°	90	71
55°	25	24
65°	14	14
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1302538
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DL1WH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	869.4
2.5°	864.0
5°	844.5
7.5°	815.3
10°	777.5
12.5°	733.1
15°	683.4
17.5°	629.3
20°	574.2
22.5°	516.9
25°	460.6
27.5°	403.3
30°	347.1
32.5°	293.0
35°	243.3
37.5°	197.9
40°	156.8
42.5°	120.0
45°	89.7
47.5°	64.9
50°	44.3
52.5°	30.3
55°	24.9
57.5°	21.6
60°	18.4
62.5°	16.2
65°	14.1
67.5°	11.9
70°	9.7
72.5°	8.7
75°	6.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)