

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302556

Luminaire Tested: P3AS17R65W2N902765DE010 E3DLD1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3DLD1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 853.0 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302556
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLD1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1302556

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLD1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.0	7.5
10°-20°	168.2	19.7
20°-30°	216.2	25.3
30°-40°	200.0	23.4
40°-50°	120.7	14.2
50°-60°	41.2	4.8
60°-70°	24.8	2.9
70°-80°	14.0	1.6
80°-90°	4.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.4	52.6
0°-40°	648.3	76.0
0°-60°	810.2	95.0
0°-90°	853.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	853.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	692	
5°	680	64
15°	601	168
25°	472	216
35°	322	200
45°	156	121
55°	40	41
65°	25	25
75°	13	14
85°	3	4
90°	0	



TEST NUMBER: P1302556
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLD1H_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	692.2
2.5°	689.0
5°	680.3
7.5°	667.3
10°	650.0
12.5°	628.3
15°	601.2
17.5°	572.0
20°	539.5
22.5°	505.9
25°	472.3
27.5°	436.6
30°	399.7
32.5°	362.9
35°	321.7
37.5°	281.7
40°	239.4
42.5°	197.2
45°	156.0
47.5°	118.1
50°	82.3
52.5°	52.0
55°	40.1
57.5°	35.7
60°	32.5
62.5°	28.2
65°	24.9
67.5°	21.7
70°	18.4
72.5°	16.2
75°	13.0
77.5°	10.8
80°	7.6
82.5°	5.4
85°	3.2
87.5°	2.2
90°	0.0

(END OF REPORT)