

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302612

Luminaire Tested: P3AS17R65W2N902765DE010 E3DLP1WH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3DLP1WH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1216.0 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302612
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1302612

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.8	9.9
10°-20°	313.0	25.7
20°-30°	365.8	30.1
30°-40°	255.7	21.0
40°-50°	112.5	9.3
50°-60°	25.0	2.1
60°-70°	12.7	1.0
70°-80°	7.7	0.6
80°-90°	2.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	799.7	65.8
0°-40°	1055.4	86.8
0°-60°	1193.0	98.1
0°-90°	1216.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1216.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1308	
5°	1287	121
15°	1125	313
25°	806	366
35°	406	256
45°	142	113
55°	21	25
65°	13	13
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302612
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1307.8
2.5°	1302.9
5°	1287.2
7.5°	1260.5
10°	1224.1
12.5°	1179.3
15°	1124.8
17.5°	1058.1
20°	984.2
22.5°	900.5
25°	806.0
27.5°	706.6
30°	602.4
32.5°	501.8
35°	406.0
37.5°	322.4
40°	248.5
42.5°	187.9
45°	141.8
47.5°	104.2
50°	65.4
52.5°	33.9
55°	20.6
57.5°	18.2
60°	15.8
62.5°	14.5
65°	13.3
67.5°	10.9
70°	9.7
72.5°	8.5
75°	7.3
77.5°	6.1
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)