

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302618

Luminaire Tested: P3AS17R65W2N902765DE010 E3DLP1WMH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R65W2N902765DE010 E3DLP1WMH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 840.0 lumens
Efficiency: N/A
Efficacy: 43.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302618
CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WMH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1302618

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WMH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	10.5
10°-20°	212.7	25.3
20°-30°	235.2	28.0
30°-40°	170.9	20.3
40°-50°	80.0	9.5
50°-60°	27.0	3.2
60°-70°	15.6	1.9
70°-80°	8.2	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.8	63.8
0°-40°	706.7	84.1
0°-60°	813.7	96.9
0°-90°	840.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	840.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	974	
5°	946	88
15°	765	213
25°	516	235
35°	272	171
45°	100	80
55°	28	27
65°	16	16
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1302618

CATALOG NUMBER: P3AS17R65W2N902765DE010 E3DLP1WMH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	973.7
2.5°	967.6
5°	945.8
7.5°	913.1
10°	870.8
12.5°	821.1
15°	765.4
17.5°	704.8
20°	643.1
22.5°	578.9
25°	515.9
27.5°	451.7
30°	388.8
32.5°	328.2
35°	272.5
37.5°	221.6
40°	175.6
42.5°	134.4
45°	100.5
47.5°	72.7
50°	49.7
52.5°	33.9
55°	27.9
57.5°	24.2
60°	20.6
62.5°	18.2
65°	15.7
67.5°	13.3
70°	10.9
72.5°	9.7
75°	7.3
77.5°	6.1
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)