

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302733

Luminaire Tested: P3AS17R70W2N902750DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902750DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 858.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302733
CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302733

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	9.8
10°-20°	207.2	24.2
20°-30°	236.0	27.5
30°-40°	184.6	21.5
40°-50°	90.7	10.6
50°-60°	27.9	3.2
60°-70°	16.5	1.9
70°-80°	8.8	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	527.0	61.4
0°-40°	711.5	82.9
0°-60°	830.1	96.7
0°-90°	858.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	858.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	918	
5°	898	84
15°	745	207
25°	516	236
35°	296	185
45°	116	91
55°	29	28
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1302733

CATALOG NUMBER: P3AS17R70W2N902750DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	917.8
2.5°	913.0
5°	897.5
7.5°	872.4
10°	836.6
12.5°	794.9
15°	744.7
17.5°	691.0
20°	633.7
22.5°	574.1
25°	515.6
27.5°	458.3
30°	403.4
32.5°	348.5
35°	296.0
37.5°	245.9
40°	198.1
42.5°	154.0
45°	115.8
47.5°	81.2
50°	52.5
52.5°	34.6
55°	28.6
57.5°	25.1
60°	21.5
62.5°	19.1
65°	16.7
67.5°	14.3
70°	11.9
72.5°	9.5
75°	8.4
77.5°	7.2
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)