

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302823

Luminaire Tested: P3AS17R70W2N902765DE010 E3DL1H_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902765DE010 E3DL1H_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1213.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302823
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DL1H_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1302823
 CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DL1H_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.3	8.2
10°-20°	266.0	21.9
20°-30°	345.7	28.5
30°-40°	293.3	24.2
40°-50°	151.2	12.5
50°-60°	29.2	2.4
60°-70°	15.8	1.3
70°-80°	9.7	0.8
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	711.0	58.6
0°-40°	1004.3	82.8
0°-60°	1184.7	97.7
0°-90°	1213.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1213.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1071	
5°	1054	99
15°	950	266
25°	759	346
35°	472	293
45°	195	151
55°	23	29
65°	16	16
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1302823
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DL1H_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1070.9
2.5°	1067.3
5°	1054.0
7.5°	1034.8
10°	1011.9
12.5°	983.0
15°	950.4
17.5°	910.7
20°	866.1
22.5°	815.5
25°	758.9
27.5°	695.1
30°	626.4
32.5°	550.5
35°	472.2
37.5°	395.1
40°	321.6
42.5°	253.0
45°	195.1
47.5°	143.3
50°	83.1
52.5°	36.1
55°	22.9
57.5°	21.7
60°	19.3
62.5°	18.1
65°	15.7
67.5°	14.5
70°	12.0
72.5°	10.8
75°	9.6
77.5°	7.2
80°	6.0
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)