

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302857

Luminaire Tested: P3AS17R70W2N902765DE010 E3DLP1H_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302857
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R70W2N902765DE010 E3DLP1H_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 871.0 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302857
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1H_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1302857

CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1H_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	9.8
10°-20°	210.4	24.2
20°-30°	239.6	27.5
30°-40°	187.4	21.5
40°-50°	92.0	10.6
50°-60°	28.3	3.2
60°-70°	16.8	1.9
70°-80°	9.0	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.0	61.4
0°-40°	722.3	82.9
0°-60°	842.6	96.7
0°-90°	871.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	871.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	932	
5°	911	85
15°	756	210
25°	523	240
35°	300	187
45°	118	92
55°	29	28
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1302857
CATALOG NUMBER: P3AS17R70W2N902765DE010 E3DLP1H_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	931.7
2.5°	926.8
5°	911.1
7.5°	885.7
10°	849.3
12.5°	806.9
15°	756.0
17.5°	701.5
20°	643.3
22.5°	582.8
25°	523.4
27.5°	465.2
30°	409.5
32.5°	353.8
35°	300.5
37.5°	249.6
40°	201.1
42.5°	156.3
45°	117.5
47.5°	82.4
50°	53.3
52.5°	35.1
55°	29.1
57.5°	25.4
60°	21.8
62.5°	19.4
65°	17.0
67.5°	14.5
70°	12.1
72.5°	9.7
75°	8.5
77.5°	7.3
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)