

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265972

Luminaire Tested: P3A20R609730D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R609730D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1102.0 lumens
Efficiency: N/A
Efficacy: 38.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265972
CATALOG NUMBER: P3A20R609730D010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1265972
 CATALOG NUMBER: P3A20R609730D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.5	10.5
10°-20°	280.5	25.5
20°-30°	307.7	27.9
30°-40°	224.2	20.3
40°-50°	105.9	9.6
50°-60°	34.7	3.1
60°-70°	19.7	1.8
70°-80°	10.6	1.0
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	703.7	63.9
0°-40°	927.9	84.2
0°-60°	1068.5	97.0
0°-90°	1102.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1102.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1274	
5°	1240	115
15°	1010	281
25°	674	308
35°	357	224
45°	133	106
55°	35	35
65°	20	20
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P1265972
CATALOG NUMBER: P3A20R609730D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1273.6
2.5°	1266.1
5°	1240.3
7.5°	1200.9
10°	1147.9
12.5°	1084.3
15°	1010.1
17.5°	929.9
20°	845.0
22.5°	758.7
25°	673.9
27.5°	589.1
30°	508.8
32.5°	431.6
35°	357.4
37.5°	290.8
40°	230.2
42.5°	177.2
45°	133.3
47.5°	96.9
50°	66.6
52.5°	43.9
55°	34.8
57.5°	30.3
60°	27.3
62.5°	22.7
65°	19.7
67.5°	16.7
70°	13.6
72.5°	12.1
75°	10.6
77.5°	7.6
80°	6.1
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)