

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297846

Luminaire Tested: P3A13R50W2N902765DE010 E3DLP1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297846
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R50W2N902765DE010 E3DLP1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 512.0 lumens
Efficiency: N/A
Efficacy: 41.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297846
CATALOG NUMBER: P3A13R50W2N902765DE010 E3DLP1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297846

CATALOG NUMBER: P3A13R50W2N902765DE010 E3DLP1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.0	11.9
10°-20°	143.4	28.0
20°-30°	146.6	28.6
30°-40°	93.0	18.2
40°-50°	37.0	7.2
50°-60°	15.0	2.9
60°-70°	9.6	1.9
70°-80°	4.9	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.0	68.5
0°-40°	443.9	86.7
0°-60°	495.9	96.9
0°-90°	512.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	512.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	679	
5°	658	61
15°	518	143
25°	322	147
35°	147	93
45°	45	37
55°	17	15
65°	10	10
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1297846
CATALOG NUMBER: P3A13R50W2N902765DE010 E3DLP1LI_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	679.1
2.5°	674.2
5°	658.3
7.5°	633.4
10°	600.1
12.5°	560.6
15°	517.6
17.5°	470.5
20°	421.3
22.5°	372.1
25°	322.2
27.5°	272.3
30°	225.9
32.5°	184.3
35°	146.9
37.5°	115.0
40°	87.3
42.5°	64.4
45°	45.0
47.5°	30.5
50°	22.2
52.5°	18.7
55°	16.6
57.5°	14.6
60°	12.5
62.5°	11.1
65°	9.7
67.5°	8.3
70°	6.9
72.5°	5.5
75°	4.9
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)