

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298304

Luminaire Tested: P3A13R60W2N902750DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R60W2N902750DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 247.0 lumens
Efficiency: N/A
Efficacy: 20.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298304
CATALOG NUMBER: P3A13R60W2N902750DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1298304

CATALOG NUMBER: P3A13R60W2N902750DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.9	10.5
10°-20°	62.9	25.5
20°-30°	69.0	27.9
30°-40°	50.2	20.3
40°-50°	23.7	9.6
50°-60°	7.8	3.1
60°-70°	4.4	1.8
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.7	63.9
0°-40°	208.0	84.2
0°-60°	239.5	97.0
0°-90°	247.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	247.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	286	
5°	278	26
15°	226	63
25°	151	69
35°	80	50
45°	30	24
55°	8	8
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1298304
CATALOG NUMBER: P3A13R60W2N902750DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	285.5
2.5°	283.8
5°	278.0
7.5°	269.2
10°	257.3
12.5°	243.0
15°	226.4
17.5°	208.4
20°	189.4
22.5°	170.1
25°	151.0
27.5°	132.0
30°	114.1
32.5°	96.7
35°	80.1
37.5°	65.2
40°	51.6
42.5°	39.7
45°	29.9
47.5°	21.7
50°	14.9
52.5°	9.8
55°	7.8
57.5°	6.8
60°	6.1
62.5°	5.1
65°	4.4
67.5°	3.7
70°	3.1
72.5°	2.7
75°	2.4
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)