

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299890

Luminaire Tested: P3A17R25W2N902750DE010 E3PHLD1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R25W2N902750DE010 E3PHLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 869.0 lumens
Efficiency: N/A
Efficacy: 44.8 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299890
CATALOG NUMBER: P3A17R25W2N902750DE010 E3PHLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1299890

CATALOG NUMBER: P3A17R25W2N902750DE010 E3PHLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	10.2
10°-20°	185.4	21.3
20°-30°	182.7	21.0
30°-40°	148.7	17.1
40°-50°	110.4	12.7
50°-60°	77.0	8.9
60°-70°	48.2	5.6
70°-80°	23.2	2.7
80°-90°	4.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.9	52.6
0°-40°	605.6	69.7
0°-60°	793.0	91.3
0°-90°	869.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	869.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1034	
5°	978	89
15°	668	185
25°	395	183
35°	236	149
45°	142	110
55°	86	77
65°	48	48
75°	22	23
85°	3	4
90°	0	



TEST NUMBER: P1299890
CATALOG NUMBER: P3A17R25W2N902750DE010 E3PHLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1034.0
2.5°	1020.0
5°	977.8
7.5°	913.7
10°	837.2
12.5°	752.9
15°	668.5
17.5°	585.7
20°	513.9
22.5°	451.4
25°	395.2
27.5°	346.8
30°	306.1
32.5°	268.7
35°	235.9
37.5°	207.7
40°	182.7
42.5°	160.9
45°	142.1
47.5°	125.0
50°	109.3
52.5°	96.8
55°	85.9
57.5°	75.0
60°	65.6
62.5°	56.2
65°	48.4
67.5°	40.6
70°	34.4
72.5°	28.1
75°	21.9
77.5°	15.6
80°	10.9
82.5°	6.2
85°	3.1
87.5°	1.6
90°	0.0

(END OF REPORT)