

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301344

Luminaire Tested: P3A17R45W2N902765DE010 E3DLP1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R45W2N902765DE010 E3DLP1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 868.9 lumens
Efficiency: N/A
Efficacy: 44.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301344
CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLP1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1301344

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLP1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.4	12.2
10°-20°	247.1	28.4
20°-30°	245.3	28.2
30°-40°	158.0	18.2
40°-50°	60.8	7.0
50°-60°	24.7	2.8
60°-70°	15.6	1.8
70°-80°	8.4	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.8	68.9
0°-40°	756.7	87.1
0°-60°	842.3	96.9
0°-90°	868.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	868.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1180	
5°	1149	106
15°	894	247
25°	536	245
35°	252	158
45°	74	61
55°	28	25
65°	16	16
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1301344

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1180.4
2.5°	1174.4
5°	1149.1
7.5°	1105.7
10°	1047.9
12.5°	975.6
15°	893.7
17.5°	804.6
20°	714.3
22.5°	622.7
25°	536.0
27.5°	454.1
30°	378.2
32.5°	312.0
35°	251.7
37.5°	197.5
40°	146.9
42.5°	106.0
45°	73.5
47.5°	49.4
50°	36.1
52.5°	30.1
55°	27.7
57.5°	24.1
60°	21.7
62.5°	18.1
65°	15.7
67.5°	13.2
70°	10.8
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)