

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289463

Luminaire Tested: P3A05R40W2N902750DE010 E3DLD1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R40W2N902750DE010 E3DLD1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 353.0 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289463
CATALOG NUMBER: P3A05R40W2N902750DE010 E3DLD1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1289463

CATALOG NUMBER: P3A05R40W2N902750DE010 E3DLD1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.0	9.3
10°-20°	81.7	23.2
20°-30°	94.5	26.8
30°-40°	74.5	21.1
40°-50°	38.2	10.8
50°-60°	14.6	4.1
60°-70°	9.7	2.7
70°-80°	5.2	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	209.2	59.3
0°-40°	283.7	80.4
0°-60°	336.5	95.3
0°-90°	353.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	353.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	361	
5°	354	33
15°	293	82
25°	207	94
35°	119	74
45°	49	38
55°	15	15
65°	10	10
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1289463

CATALOG NUMBER: P3A05R40W2N902750DE010 E3DLD1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	361.4
2.5°	359.4
5°	353.5
7.5°	343.2
10°	329.4
12.5°	313.2
15°	293.4
17.5°	272.9
20°	250.8
22.5°	228.3
25°	206.6
27.5°	184.8
30°	163.5
32.5°	141.8
35°	119.3
37.5°	98.3
40°	79.4
42.5°	63.2
45°	49.4
47.5°	35.9
50°	24.5
52.5°	17.8
55°	15.4
57.5°	13.8
60°	12.6
62.5°	11.1
65°	9.9
67.5°	8.3
70°	7.1
72.5°	5.9
75°	5.1
77.5°	3.9
80°	2.8
82.5°	2.4
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)