

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289655

Luminaire Tested: P3A05R40W2N902765DE010 E3DLP1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289655
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R40W2N902765DE010 E3DLP1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 144.0 lumens
Efficiency: N/A
Efficacy: 24.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289655
CATALOG NUMBER: P3A05R40W2N902765DE010 E3DLP1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1289655

CATALOG NUMBER: P3A05R40W2N902765DE010 E3DLP1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.5	12.9
10°-20°	43.2	30.0
20°-30°	40.8	28.3
30°-40°	23.6	16.4
40°-50°	9.4	6.5
50°-60°	4.2	2.9
60°-70°	2.6	1.8
70°-80°	1.4	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.5	71.2
0°-40°	126.1	87.6
0°-60°	139.7	97.0
0°-90°	144.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	144.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	204	
5°	200	19
15°	157	43
25°	89	41
35°	37	24
45°	12	9
55°	4	4
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1289655
CATALOG NUMBER: P3A05R40W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	204.5
2.5°	203.3
5°	199.6
7.5°	192.7
10°	183.7
12.5°	171.5
15°	157.0
17.5°	140.8
20°	123.1
22.5°	105.5
25°	89.0
27.5°	73.7
30°	59.8
32.5°	47.6
35°	37.1
37.5°	28.0
40°	21.0
42.5°	15.7
45°	11.6
47.5°	8.4
50°	6.3
52.5°	5.1
55°	4.5
57.5°	4.1
60°	3.5
62.5°	2.9
65°	2.5
67.5°	2.2
70°	2.0
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)