

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291202

Luminaire Tested: P3A05R65W2N902765DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R65W2N902765DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 134.0 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291202
CATALOG NUMBER: P3A05R65W2N902765DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291202

CATALOG NUMBER: P3A05R65W2N902765DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.0	10.5
10°-20°	33.9	25.3
20°-30°	37.5	28.0
30°-40°	27.3	20.4
40°-50°	12.8	9.5
50°-60°	4.3	3.2
60°-70°	2.5	1.8
70°-80°	1.3	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	85.5	63.8
0°-40°	112.7	84.1
0°-60°	129.8	96.9
0°-90°	134.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	134.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	155	
5°	151	14
15°	122	34
25°	82	38
35°	44	27
45°	16	13
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1291202
CATALOG NUMBER: P3A05R65W2N902765DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	155.3
2.5°	154.4
5°	150.9
7.5°	145.7
10°	138.9
12.5°	131.0
15°	122.1
17.5°	112.4
20°	102.6
22.5°	92.3
25°	82.3
27.5°	72.1
30°	62.0
32.5°	52.4
35°	43.5
37.5°	35.4
40°	28.0
42.5°	21.4
45°	16.0
47.5°	11.6
50°	7.9
52.5°	5.4
55°	4.4
57.5°	3.9
60°	3.3
62.5°	2.9
65°	2.5
67.5°	2.1
70°	1.7
72.5°	1.5
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)