

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292305

Luminaire Tested: P3A09R25W2N902750DE010 E3PHLP1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R25W2N902750DE010 E3PHLP1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 305.0 lumens
Efficiency: N/A
Efficacy: 33.9 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292305
CATALOG NUMBER: P3A09R25W2N902750DE010 E3PHLP1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1292305

CATALOG NUMBER: P3A09R25W2N902750DE010 E3PHLP1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.7	13.0
10°-20°	79.5	26.1
20°-30°	70.4	23.1
30°-40°	44.8	14.7
40°-50°	23.7	7.8
50°-60°	17.4	5.7
60°-70°	14.8	4.9
70°-80°	10.5	3.4
80°-90°	4.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.5	62.2
0°-40°	234.4	76.9
0°-60°	275.5	90.3
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	440	40
15°	287	79
25°	153	70
35°	71	45
45°	29	24
55°	19	17
65°	15	15
75°	10	10
85°	4	4
90°	0	



TEST NUMBER: P1292305
CATALOG NUMBER: P3A09R25W2N902750DE010 E3PHLP1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	467.3
2.5°	460.5
5°	439.9
7.5°	407.8
10°	369.6
12.5°	328.4
15°	287.1
17.5°	247.4
20°	212.3
22.5°	180.2
25°	152.7
27.5°	128.3
30°	106.1
32.5°	87.1
35°	71.0
37.5°	56.5
40°	45.1
42.5°	35.9
45°	29.0
47.5°	25.2
50°	22.1
52.5°	20.6
55°	19.1
57.5°	18.3
60°	17.6
62.5°	16.0
65°	15.3
67.5°	13.7
70°	12.2
72.5°	11.5
75°	9.9
77.5°	8.4
80°	7.6
82.5°	6.1
85°	3.8
87.5°	1.5
90°	0.0

(END OF REPORT)