

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332319-840

Luminaire Tested: **S123RDIP-S775D1025U840-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332319-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIP-S775D1025U840-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1025 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6634.4 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46
1	98	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	67	64	60	57	53	50	48	42	41	39	35
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34	30
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26
5	69	58	50	44	63	54	47	42	46	40	36	38	34	31	31	28	26	23
6	64	52	44	39	58	48	41	36	41	36	32	35	31	28	28	26	23	20
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21	18
8	55	43	35	30	50	40	33	29	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	37	30	26	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13295	13295	13295	13295
5°	15847	13351	11757	13351
10°	19787	13274	10622	13274
15°	23226	13138	9686	13138
20°	25921	12936	8891	12936
25°	25508	12722	8402	12722
30°	18334	12525	7899	12525
35°	12242	12269	7573	12269
40°	9020	11960	7235	11960
45°	7566	11420	6905	11420
50°	6677	10712	6445	10712
55°	5853	9903	5814	9903
60°	5214	9128	5326	9128
65°	4579	8295	4956	8295
70°	3594	7553	4526	7553
75°	3165	6596	4134	6596
80°	2752	5604	4060	5604
85°	2223	4508	4310	4508



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	1.8
10°-20°	379.5	5.7
20°-30°	596.1	9.0
30°-40°	621.9	9.4
40°-50°	532.3	8.0
50°-60°	405.7	6.1
60°-70°	260.0	3.9
70°-80°	125.1	1.9
80°-90°	36.9	0.6
90°-100°	83.6	1.3
100°-110°	250.2	3.8
110°-120°	425.6	6.4
120°-130°	559.8	8.4
130°-140°	629.2	9.5
140°-150°	618.5	9.3
150°-160°	520.7	7.8
160°-170°	346.6	5.2
170°-180°	121.4	1.8
0°-30°	1097.0	16.5
0°-40°	1719.0	25.9
0°-60°	2656.9	40.0
0°-90°	3078.9	46.4
90°-120°	759.4	11.4
90°-150°	2566.9	38.7
90°-180°	3555.0	53.6
0°-180°	6634.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1235	1235	1235	1235	1235	
5°	1467	1236	1088	1236	1467	151
15°	2084	1179	869	1179	2084	591
25°	2148	1071	707	1071	2148	923
35°	932	934	576	934	932	611
45°	497	750	454	750	497	391
55°	312	528	310	528	312	282
65°	180	326	195	326	180	177
75°	76	159	99	159	76	82
85°	18	36	35	36	18	21
90°	30	1	30	1	30	15
95°	79	60	79	60	79	81
105°	240	227	240	227	240	255
115°	429	428	429	428	429	425
125°	620	627	620	627	620	554
135°	812	814	812	814	812	625
145°	987	987	987	987	987	616
155°	1128	1130	1128	1130	1128	519
165°	1227	1231	1227	1231	1227	346
175°	1275	1280	1275	1280	1275	121
180°	1283	1283	1283	1283	1283	



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1315.5	1317.2	1311.6	1310.8	1304.4	1302.7	1302.7	1293.8	1288.4	1281.2	1277.0
5°	1466.6	1475.1	1470.9	1461.4	1445.5	1441.8	1431.8	1415.9	1398.0	1375.7	1365.1
7.5°	1655.5	1667.1	1662.6	1647.9	1631.3	1617.9	1589.5	1563.2	1526.3	1493.9	1466.2
10°	1810.3	1798.2	1788.7	1774.3	1759.1	1734.1	1704.6	1663.9	1616.8	1579.8	1538.5
12.5°	1926.2	1924.2	1912.2	1897.4	1875.8	1852.2	1815.8	1766.3	1711.5	1658.1	1610.9
15°	2084.2	2087.4	2079.4	2064.1	2033.5	1991.7	1936.7	1916.0	1837.9	1779.7	1721.5
17.5°	2193.5	2192.9	2191.8	2170.6	2139.3	2109.6	2058.6	2004.4	1933.5	1851.6	1773.2
20°	2262.9	2257.7	2258.7	2234.8	2211.6	2177.3	2127.6	2048.8	1990.6	1896.0	1815.0
22.5°	2261.2	2260.2	2264.2	2256.0	2239.1	2212.8	2173.6	2107.2	2033.0	1937.4	1846.3
25°	2147.7	2143.4	2168.3	2175.1	2202.1	2206.9	2195.2	2158.8	2088.4	1990.0	1877.4
27.5°	1797.5	1795.1	1841.2	1899.0	1972.1	2029.0	2084.0	2110.5	2088.4	2018.0	1905.2
30°	1475.1	1524.8	1548.1	1631.6	1724.6	1835.7	1933.0	2025.5	2048.2	2017.6	1925.0
32.5°	1224.8	1268.1	1287.5	1359.2	1445.9	1576.0	1721.9	1852.9	1945.5	1968.9	1913.2
35°	931.6	932.1	976.5	1008.2	1088.6	1222.3	1364.1	1539.6	1714.0	1846.2	1860.0
37.5°	743.4	746.0	772.8	804.5	864.7	935.5	1060.3	1206.2	1407.8	1610.6	1729.6
40°	641.9	646.6	666.7	697.9	741.2	794.7	891.9	1029.5	1197.5	1423.3	1607.8
42.5°	576.7	584.4	594.8	618.8	645.7	695.7	774.4	880.5	1033.4	1246.9	1459.8
45°	497.0	501.2	509.2	520.3	544.6	579.5	632.4	703.7	830.6	1002.5	1215.5
47.5°	438.4	436.2	444.5	453.5	469.7	493.5	529.0	587.2	677.7	815.6	996.3
50°	398.7	398.1	403.9	410.8	426.2	443.6	472.7	516.5	588.4	702.7	868.2
52.5°	361.4	363.5	367.6	376.2	387.2	401.3	427.4	459.0	520.8	619.4	757.3
55°	311.9	313.6	319.3	324.1	332.0	346.3	362.7	389.1	431.4	500.2	613.8
57.5°	270.0	269.3	274.9	276.1	285.1	296.7	309.4	329.9	360.6	411.6	488.2
60°	242.2	240.5	245.3	249.0	253.8	263.3	273.9	294.0	318.3	355.8	421.4
62.5°	216.8	216.0	219.5	223.2	227.1	235.8	244.7	260.1	279.3	311.0	363.0
65°	179.8	181.4	182.9	184.5	186.6	191.9	200.4	211.0	224.2	246.4	283.9
67.5°	141.3	142.9	143.4	146.6	151.2	154.5	159.7	169.1	178.2	197.0	218.3
70°	114.2	113.7	114.2	115.8	121.6	127.4	134.3	141.2	146.9	160.2	178.1
72.5°	98.2	97.1	98.6	98.9	101.7	103.3	107.7	114.1	121.6	130.6	143.5
75°	76.1	76.1	76.1	76.1	78.3	79.3	80.9	82.5	85.1	89.4	98.9
77.5°	56.2	56.4	57.1	57.7	58.1	58.7	59.7	61.2	62.2	64.4	68.6
80°	44.4	44.9	44.4	44.9	44.9	45.9	46.6	48.1	48.7	51.3	52.9
82.5°	33.4	33.1	33.4	33.9	33.9	35.0	35.1	36.3	36.4	37.8	39.4
85°	18.0	17.0	18.0	17.5	18.5	17.5	18.0	19.0	19.0	19.6	21.7
87.5°	10.3	11.0	10.1	10.4	10.3	10.6	10.4	10.3	10.9	10.3	10.2
90°	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0	25.0	24.2	21.3
92.5°	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2	39.4	38.7	37.1
95°	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3	75.5	74.6	72.8
97.5°	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8	117.8	116.7	115.4
100°	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6	148.9	148.1	147.0
102.5°	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0	184.3	183.7	182.2
105°	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9	237.9	237.9	235.9
107.5°	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2	294.5	293.8	293.0
110°	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5	332.5	331.6	331.2



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7	370.6	369.5	369.5
115°	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9	429.7	429.4	429.9
117.5°	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6	488.7	488.7	489.3
120°	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8	528.0	528.3	529.4
122.5°	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3	567.9	568.6	569.2
125°	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2	627.1	628.0	628.4
127.5°	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4	685.6	686.9	687.4
130°	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0	723.9	724.8	725.5
132.5°	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5	761.6	762.7	763.2
135°	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8	817.7	818.5	818.8
137.5°	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7	872.6	873.5	873.0
140°	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8	908.1	908.3	908.1
142.5°	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7	941.9	942.1	941.7
145°	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5	991.7	991.9	991.3
147.5°	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5	1067.5	1067.5	1067.1
152.5°	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1	1093.7	1093.4	1093.1
155°	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9	1132.0	1131.0	1130.8
157.5°	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2	1165.3	1164.3	1164.2
160°	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7	1185.6	1184.5	1184.5
162.5°	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1	1205.0	1203.9	1203.7
165°	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5	1229.1	1227.8	1227.8
167.5°	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6	1247.4
170°	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1	1258.1
172.5°	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7	1268.3	1266.9	1266.9
175°	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9	1277.6	1276.2	1276.2
177.5°	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0	1281.9	1280.8	1280.8
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1275.3	1273.9	1268.1	1261.3	1252.4	1246.5	1241.8	1239.3	1231.7	1222.3	1216.1
5°	1354.0	1338.2	1321.3	1300.6	1281.6	1262.0	1249.9	1235.6	1218.2	1198.6	1184.9
7.5°	1438.5	1407.3	1373.8	1339.3	1305.0	1274.4	1247.4	1224.2	1196.4	1168.3	1148.7
10°	1503.2	1457.6	1410.6	1362.5	1318.6	1277.4	1245.7	1214.5	1181.1	1148.9	1124.6
12.5°	1562.0	1502.1	1447.8	1388.8	1332.6	1283.3	1237.6	1200.9	1160.8	1126.5	1098.7
15°	1636.4	1575.1	1509.4	1419.6	1345.0	1282.6	1227.2	1179.0	1130.4	1088.1	1061.2
17.5°	1706.0	1613.7	1525.6	1450.6	1353.7	1275.8	1208.0	1150.4	1097.1	1052.3	1019.1
20°	1734.7	1645.4	1549.6	1454.0	1358.8	1271.5	1192.8	1129.3	1073.8	1023.1	992.4
22.5°	1752.0	1650.8	1550.0	1447.2	1346.2	1255.5	1177.6	1107.7	1047.6	999.4	961.5
25°	1772.2	1651.7	1540.7	1439.2	1336.1	1237.7	1145.2	1071.2	1006.1	954.8	914.6
27.5°	1785.5	1643.8	1512.6	1399.7	1295.2	1197.2	1112.4	1034.0	968.0	913.7	870.6
30°	1788.1	1637.4	1491.0	1368.9	1262.5	1172.7	1082.8	1007.7	938.0	880.3	840.1
32.5°	1791.5	1621.7	1461.8	1332.0	1223.2	1134.2	1052.8	981.1	909.6	852.8	811.8
35°	1777.6	1613.2	1417.4	1268.4	1159.4	1073.3	999.8	933.7	863.4	808.4	766.6
37.5°	1717.5	1578.7	1371.6	1196.7	1082.8	1003.0	943.1	885.4	821.0	761.6	722.4
40°	1657.0	1544.9	1336.1	1153.2	1034.2	952.2	898.3	851.2	788.8	733.4	691.1
42.5°	1566.9	1498.8	1302.2	1107.4	979.2	900.2	854.7	810.6	755.9	699.5	659.7
45°	1401.6	1410.6	1232.9	1034.7	903.0	823.7	780.9	750.2	701.7	655.1	614.4
47.5°	1194.4	1278.4	1151.7	957.2	822.7	748.3	710.9	684.2	651.4	605.7	568.6
50°	1059.0	1179.0	1086.5	905.1	772.4	698.4	661.5	639.7	611.2	575.2	539.8
52.5°	934.2	1063.2	1007.8	847.2	717.9	650.3	614.1	596.2	573.5	539.7	507.7
55°	761.8	892.5	879.8	759.7	636.0	575.2	547.8	527.7	512.3	487.0	461.6
57.5°	616.3	740.1	746.7	662.5	563.9	503.8	480.2	465.0	455.0	435.9	412.4
60°	524.5	638.1	660.4	596.9	512.3	459.5	436.2	424.0	416.1	400.8	382.8
62.5°	448.4	545.1	570.3	524.6	462.8	413.3	395.2	383.4	378.0	364.8	348.9
65°	343.2	423.5	447.8	422.4	390.2	350.5	335.8	325.7	320.9	313.6	301.8
67.5°	258.0	316.6	343.3	325.4	313.8	288.7	279.2	273.9	269.6	264.6	254.9
70°	207.2	250.6	278.1	273.4	263.9	250.6	243.8	240.0	235.8	231.6	223.1
72.5°	166.6	196.5	222.3	224.7	216.9	214.2	208.2	206.6	204.1	199.0	194.4
75°	110.5	131.1	149.1	155.9	159.2	161.8	159.2	158.6	158.0	153.9	151.2
77.5°	72.4	83.5	94.8	106.5	111.6	115.1	116.0	118.0	116.5	114.3	113.0
80°	55.5	58.2	66.0	76.1	84.0	87.3	89.4	90.4	89.9	89.4	87.3
82.5°	40.3	42.5	46.3	53.3	60.0	65.2	66.6	66.3	67.5	67.8	66.0
85°	21.7	22.2	23.2	24.3	28.0	33.8	35.4	36.5	37.6	37.6	34.3
87.5°	10.4	9.4	9.7	9.2	10.0	10.0	12.1	13.7	14.6	13.3	13.8
90°	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0	3.2	5.5	7.8
92.5°	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4	26.0	27.5	29.0
95°	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5	61.0	62.6	64.2
97.5°	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6	106.8	108.0	109.2
100°	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1	138.5	139.8	141.1
102.5°	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4	174.2	175.0	175.8
105°	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8	227.2	227.7	228.1
107.5°	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9	289.2	289.4	289.7
110°	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6	328.1	328.5	328.9



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9	368.2	368.5	368.7
115°	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4	429.1	429.8	430.4
117.5°	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3	489.8	490.2	490.7
120°	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3	528.6	529.9	531.3
122.5°	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7	567.7	568.7	569.7
125°	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0	627.7	628.3	629.0
127.5°	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7	684.1	685.5	686.9
130°	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7	721.5	723.4	725.1
132.5°	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9	758.6	760.4	762.2
135°	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5	814.9	816.2	817.5
137.5°	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0	867.1	868.2	869.3
140°	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2	903.3	904.4	905.5
142.5°	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2	936.3	937.6	938.7
145°	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8	987.3	987.7	988.3
147.5°	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1	1032.9	1033.7	1034.5
150°	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5	1064.0	1064.4	1064.8
152.5°	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3	1089.9	1090.6	1091.2
155°	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7	1164.5	1164.2	1163.9
160°	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5	1186.0	1185.6	1185.2
162.5°	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9	1205.2	1204.6	1204.0
165°	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8	1230.1	1229.5	1228.8
167.5°	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8	1249.9	1249.0	1248.1
170°	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1	1261.2	1260.3	1259.4
172.5°	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9	1270.1	1269.2	1268.3
175°	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2	1279.3	1278.4	1277.6
177.5°	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0	1283.3	1282.6	1281.9
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1214.0	1208.4	1204.7	1196.2	1190.6	1184.8	1178.8	1182.7	1182.2	1181.7	1181.7
5°	1173.3	1161.0	1149.9	1135.7	1126.7	1115.6	1107.1	1106.1	1108.2	1100.8	1096.5
7.5°	1132.9	1116.2	1100.4	1084.7	1068.0	1054.7	1046.3	1042.4	1037.0	1032.5	1027.7
10°	1104.5	1084.9	1069.5	1050.1	1032.1	1016.2	1006.1	999.3	995.5	991.9	985.0
12.5°	1075.3	1056.1	1036.6	1014.5	997.3	979.0	971.5	963.7	956.6	952.5	943.1
15°	1032.6	1007.7	987.1	963.8	944.8	926.9	916.3	900.9	898.8	893.5	884.0
17.5°	989.8	962.8	934.3	917.2	895.6	877.0	860.8	855.7	840.5	834.9	826.6
20°	955.9	931.1	909.4	886.7	855.5	838.0	825.4	818.5	806.3	798.9	793.6
22.5°	926.8	901.5	876.4	849.9	824.2	804.6	795.3	784.6	778.0	767.6	761.8
25°	885.0	857.6	827.5	798.9	780.4	765.6	750.7	741.2	731.7	727.0	716.4
27.5°	836.7	807.9	779.7	758.1	735.4	720.7	707.3	698.8	687.4	679.4	673.6
30°	810.0	776.2	751.8	732.3	703.2	689.4	679.4	668.8	660.4	651.9	646.1
32.5°	779.1	748.2	725.2	700.9	678.6	663.7	650.7	641.4	634.1	626.1	620.3
35°	730.6	704.8	681.0	656.6	640.3	624.9	609.7	601.7	594.8	587.4	582.1
37.5°	686.9	662.7	640.1	617.0	596.7	584.2	571.9	565.8	556.5	551.6	546.1
40°	659.8	636.0	611.7	589.6	568.4	558.9	547.8	538.8	530.3	526.6	520.8
42.5°	630.3	606.4	585.9	562.0	544.7	531.8	521.5	511.7	505.3	500.0	496.7
45°	586.3	565.2	545.1	521.3	504.9	493.8	482.2	473.2	467.4	463.7	457.9
47.5°	543.7	522.6	502.2	481.4	465.5	452.9	441.3	435.0	427.3	422.7	418.9
50°	512.8	493.8	472.1	453.1	437.3	424.5	415.1	407.1	400.2	394.5	391.8
52.5°	484.5	464.2	445.5	427.8	411.0	396.7	388.0	379.6	374.5	367.8	364.7
55°	437.8	418.2	402.3	384.9	368.5	356.4	345.8	338.4	333.1	325.7	321.4
57.5°	393.8	376.4	357.4	342.2	325.4	315.1	306.3	296.3	289.8	284.1	279.9
60°	364.3	344.2	327.8	313.6	298.7	285.5	277.6	269.6	262.8	256.9	253.3
62.5°	333.5	315.9	300.3	284.8	271.2	259.7	250.5	243.9	237.8	234.1	230.5
65°	286.0	272.3	256.4	243.8	231.1	222.6	215.2	209.3	205.1	202.5	199.3
67.5°	242.5	229.1	215.3	202.8	194.4	187.9	183.1	178.0	175.9	172.6	170.5
70°	214.1	200.4	188.2	178.7	170.3	165.5	162.3	158.6	156.5	152.3	150.2
72.5°	183.3	173.3	164.5	156.7	150.0	145.6	141.6	137.0	133.7	129.0	126.9
75°	144.3	135.3	128.5	123.2	119.0	113.1	107.3	102.6	101.0	99.4	98.9
77.5°	106.9	101.2	96.2	91.8	86.5	82.3	81.0	80.0	79.6	78.8	78.8
80°	84.0	78.8	75.0	69.8	66.7	66.7	66.7	65.5	66.0	66.0	66.0
82.5°	62.5	57.7	55.6	53.7	53.1	53.5	53.5	53.7	53.4	54.2	53.8
85°	32.2	32.8	33.8	33.3	33.8	33.8	34.9	34.3	34.9	33.8	34.9
87.5°	13.8	15.7	16.7	17.7	18.7	18.8	19.4	19.6	20.2	20.4	20.5
90°	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0	26.9	27.8	28.5
92.5°	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2	40.9	41.6	41.8
95°	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3	77.3	78.2	78.7
97.5°	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8	119.9	120.9	121.3
100°	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6	150.2	150.9	151.5
102.5°	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0	185.7	186.3	186.6
105°	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9	237.9	237.9	238.1
107.5°	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2	295.9	296.6	296.8
110°	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5	334.4	335.3	335.5



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7	372.7	373.9	374.4
115°	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9	430.1	430.3	430.3
117.5°	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6	488.6	488.6	488.2
120°	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8	527.6	527.4	526.9
122.5°	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3	566.8	566.2	565.6
125°	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2	625.3	624.4	623.5
127.5°	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4	683.2	681.9	680.8
130°	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0	722.1	721.2	719.9
132.5°	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5	759.5	758.4	757.3
135°	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8	815.9	815.0	814.3
137.5°	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7	870.8	869.8	868.9
140°	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8	907.6	907.4	906.5
142.5°	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7	941.5	941.2	940.5
145°	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5	991.3	991.0	990.5
147.5°	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5	1038.5	1038.5	1037.8
150°	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5	1067.5	1067.5	1066.8
152.5°	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1	1094.4	1094.8	1094.4
155°	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9	1133.8	1134.6	1134.3
157.5°	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2	1167.1	1168.1	1167.9
160°	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7	1187.8	1188.9	1189.0
162.5°	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1	1207.2	1208.3	1208.1
165°	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5	1231.8	1233.1	1233.0
167.5°	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1
170°	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4
172.5°	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7	1271.1	1272.4	1272.4
175°	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9	1280.2	1281.6	1281.4
177.5°	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0	1284.0	1285.2	1285.1
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1176.7	1176.3	1176.7	1175.0	1176.7	1176.3	1176.7	1181.7	1181.7	1182.2	1182.7
5°	1095.0	1094.4	1092.9	1088.1	1092.9	1094.4	1095.0	1096.5	1100.8	1108.2	1106.1
7.5°	1023.6	1022.9	1018.2	1018.3	1018.2	1022.9	1023.6	1027.7	1032.5	1037.0	1042.4
10°	981.3	981.8	975.5	971.8	975.5	981.8	981.3	985.0	991.9	995.5	999.3
12.5°	940.3	937.9	932.7	928.7	932.7	937.9	940.3	943.1	952.5	956.6	963.7
15°	886.2	880.8	868.2	869.2	868.2	880.8	886.2	884.0	893.5	898.8	900.9
17.5°	822.3	818.5	818.2	810.8	818.2	818.5	822.3	826.6	834.9	840.5	855.7
20°	785.2	782.5	783.6	776.2	783.6	782.5	785.2	793.6	798.9	806.3	818.5
22.5°	756.0	753.4	748.9	746.6	748.9	753.4	756.0	761.8	767.6	778.0	784.6
25°	713.3	709.0	704.8	707.4	704.8	709.0	713.3	716.4	727.0	731.7	741.2
27.5°	670.6	667.3	663.1	662.6	663.1	667.3	670.6	673.6	679.4	687.4	698.8
30°	643.5	640.3	638.1	635.5	638.1	640.3	643.5	646.1	651.9	660.4	668.8
32.5°	615.9	615.3	611.5	611.0	611.5	615.3	615.9	620.3	626.1	634.1	641.4
35°	580.0	576.8	575.7	576.3	575.7	576.8	580.0	582.1	587.4	594.8	601.7
37.5°	545.8	541.6	539.7	537.9	539.7	541.6	545.8	546.1	551.6	556.5	565.8
40°	521.3	517.1	516.0	514.9	516.0	517.1	521.3	520.8	526.6	530.3	538.8
42.5°	493.8	492.1	491.5	489.6	491.5	492.1	493.8	496.7	500.0	505.3	511.7
45°	456.3	455.8	452.6	453.6	452.6	455.8	456.3	457.9	463.7	467.4	473.2
47.5°	416.8	414.4	412.2	413.6	412.2	414.4	416.8	418.9	422.7	427.3	435.0
50°	389.7	388.6	383.8	384.9	383.8	388.6	389.7	391.8	394.5	400.2	407.1
52.5°	362.6	358.6	356.8	356.2	356.8	358.6	362.6	364.7	367.8	374.5	379.6
55°	317.8	313.0	310.8	309.8	310.8	313.0	317.8	321.4	325.7	333.1	338.4
57.5°	273.8	272.5	270.8	272.0	270.8	272.5	273.8	279.9	284.1	289.8	296.3
60°	247.9	247.9	247.9	247.4	247.9	247.9	247.9	253.3	256.9	262.8	269.6
62.5°	228.1	226.8	226.4	227.1	226.4	226.8	228.1	230.5	234.1	237.8	243.9
65°	197.7	197.2	195.1	194.6	195.1	197.2	197.7	199.3	202.5	205.1	209.3
67.5°	169.1	167.1	166.5	165.8	166.5	167.1	169.1	170.5	172.6	175.9	178.0
70°	147.5	146.4	143.3	143.8	143.3	146.4	147.5	150.2	152.3	156.5	158.6
72.5°	124.2	123.2	122.6	121.8	122.6	123.2	124.2	126.9	129.0	133.7	137.0
75°	98.4	97.9	97.3	99.4	97.3	97.9	98.4	98.9	99.4	101.0	102.6
77.5°	78.8	78.8	79.1	78.3	79.1	78.8	78.8	78.8	78.8	79.6	80.0
80°	66.0	66.0	65.5	65.5	65.5	66.0	66.0	66.0	66.0	66.0	65.5
82.5°	53.0	53.4	53.7	52.9	53.7	53.4	53.0	53.8	54.2	53.4	53.7
85°	34.9	34.3	35.4	34.9	35.4	34.3	34.9	34.9	33.8	34.9	34.3
87.5°	21.4	20.7	20.8	21.3	20.8	20.7	21.4	20.5	20.4	20.2	19.6
90°	28.9	29.4	29.8	30.2	29.8	29.4	28.9	28.5	27.8	26.9	26.0
92.5°	41.5	41.3	41.0	40.7	41.0	41.3	41.5	41.8	41.6	40.9	40.2
95°	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.7	78.2	77.3	76.3
97.5°	121.3	121.2	121.1	121.0	121.1	121.2	121.3	121.3	120.9	119.9	118.8
100°	151.9	152.3	152.8	153.2	152.8	152.3	151.9	151.5	150.9	150.2	149.6
102.5°	186.5	186.4	186.4	186.3	186.4	186.4	186.5	186.6	186.3	185.7	185.0
105°	238.5	239.0	239.4	239.9	239.4	239.0	238.5	238.1	237.9	237.9	237.9
107.5°	296.6	296.3	296.0	295.8	296.0	296.3	296.6	296.8	296.6	295.9	295.2
110°	335.0	334.6	334.2	333.7	334.2	334.6	335.0	335.5	335.3	334.4	333.5



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	374.3	374.2	374.1	374.0	374.1	374.2	374.3	374.4	373.9	372.7	371.7
115°	430.1	429.9	429.7	429.4	429.7	429.9	430.1	430.3	430.3	430.1	429.9
117.5°	487.6	487.0	486.4	485.6	486.4	487.0	487.6	488.2	488.6	488.6	488.6
120°	526.5	526.1	525.6	525.2	525.6	526.1	526.5	526.9	527.4	527.6	527.8
122.5°	565.0	564.3	563.7	563.1	563.7	564.3	565.0	565.6	566.2	566.8	567.3
125°	622.7	621.8	620.9	620.0	620.9	621.8	622.7	623.5	624.4	625.3	626.2
127.5°	679.7	678.6	677.6	676.6	677.6	678.6	679.7	680.8	681.9	683.2	684.4
130°	718.4	716.8	715.3	713.7	715.3	716.8	718.4	719.9	721.2	722.1	723.0
132.5°	756.1	754.9	753.7	752.5	753.7	754.9	756.1	757.3	758.4	759.5	760.5
135°	813.9	813.3	812.9	812.5	812.9	813.3	813.9	814.3	815.0	815.9	816.8
137.5°	868.1	867.2	866.4	865.6	866.4	867.2	868.1	868.9	869.8	870.8	871.7
140°	904.9	903.3	901.8	900.2	901.8	903.3	904.9	906.5	907.4	907.6	907.8
142.5°	939.3	938.1	936.9	935.6	936.9	938.1	939.3	940.5	941.2	941.5	941.7
145°	989.6	988.7	987.7	986.8	987.7	988.7	989.6	990.5	991.0	991.3	991.5
147.5°	1036.5	1035.1	1033.8	1032.5	1033.8	1035.1	1036.5	1037.8	1038.5	1038.5	1038.5
150°	1065.5	1064.2	1062.8	1061.5	1062.8	1064.2	1065.5	1066.8	1067.5	1067.5	1067.5
152.5°	1093.2	1092.1	1090.9	1089.7	1090.9	1092.1	1093.2	1094.4	1094.8	1094.4	1094.1
155°	1132.8	1131.1	1129.5	1128.0	1129.5	1131.1	1132.8	1134.3	1134.6	1133.8	1132.9
157.5°	1166.7	1165.4	1164.2	1162.9	1164.2	1165.4	1166.7	1167.9	1168.1	1167.1	1166.2
160°	1188.2	1187.3	1186.4	1185.5	1186.4	1187.3	1188.2	1189.0	1188.9	1187.8	1186.7
162.5°	1206.7	1205.3	1203.9	1202.4	1203.9	1205.3	1206.7	1208.1	1208.3	1207.2	1206.1
165°	1231.5	1229.9	1228.4	1226.8	1228.4	1229.9	1231.5	1233.0	1233.1	1231.8	1230.5
167.5°	1251.7	1250.3	1249.0	1247.6	1249.0	1250.3	1251.7	1253.1	1253.1	1251.7	1250.3
170°	1262.7	1261.2	1259.6	1258.1	1259.6	1261.2	1262.7	1264.4	1264.4	1262.7	1261.2
172.5°	1270.8	1269.3	1267.7	1266.1	1267.7	1269.3	1270.8	1272.4	1272.4	1271.1	1269.7
175°	1279.9	1278.3	1276.8	1275.2	1276.8	1278.3	1279.9	1281.4	1281.6	1280.2	1278.9
177.5°	1283.8	1282.5	1281.3	1280.0	1281.3	1282.5	1283.8	1285.1	1285.2	1284.0	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1178.8	1184.8	1190.6	1196.2	1204.7	1208.4	1214.0	1216.1	1222.3	1231.7	1239.3
5°	1107.1	1115.6	1126.7	1135.7	1149.9	1161.0	1173.3	1184.9	1198.6	1218.2	1235.6
7.5°	1046.3	1054.7	1068.0	1084.7	1100.4	1116.2	1132.9	1148.7	1168.3	1196.4	1224.2
10°	1006.1	1016.2	1032.1	1050.1	1069.5	1084.9	1104.5	1124.6	1148.9	1181.1	1214.5
12.5°	971.5	979.0	997.3	1014.5	1036.6	1056.1	1075.3	1098.7	1126.5	1160.8	1200.9
15°	916.3	926.9	944.8	963.8	987.1	1007.7	1032.6	1061.2	1088.1	1130.4	1179.0
17.5°	860.8	877.0	895.6	917.2	934.3	962.8	989.8	1019.1	1052.3	1097.1	1150.4
20°	825.4	838.0	855.5	886.7	909.4	931.1	955.9	992.4	1023.1	1073.8	1129.3
22.5°	795.3	804.6	824.2	849.9	876.4	901.5	926.8	961.5	999.4	1047.6	1107.7
25°	750.7	765.6	780.4	798.9	827.5	857.6	885.0	914.6	954.8	1006.1	1071.2
27.5°	707.3	720.7	735.4	758.1	779.7	807.9	836.7	870.6	913.7	968.0	1034.0
30°	679.4	689.4	703.2	732.3	751.8	776.2	810.0	840.1	880.3	938.0	1007.7
32.5°	650.7	663.7	678.6	700.9	725.2	748.2	779.1	811.8	852.8	909.6	981.1
35°	609.7	624.9	640.3	656.6	681.0	704.8	730.6	766.6	808.4	863.4	933.7
37.5°	571.9	584.2	596.7	617.0	640.1	662.7	686.9	722.4	761.6	821.0	885.4
40°	547.8	558.9	568.4	589.6	611.7	636.0	659.8	691.1	733.4	788.8	851.2
42.5°	521.5	531.8	544.7	562.0	585.9	606.4	630.3	659.7	699.5	755.9	810.6
45°	482.2	493.8	504.9	521.3	545.1	565.2	586.3	614.4	655.1	701.7	750.2
47.5°	441.3	452.9	465.5	481.4	502.2	522.6	543.7	568.6	605.7	651.4	684.2
50°	415.1	424.5	437.3	453.1	472.1	493.8	512.8	539.8	575.2	611.2	639.7
52.5°	388.0	396.7	411.0	427.8	445.5	464.2	484.5	507.7	539.7	573.5	596.2
55°	345.8	356.4	368.5	384.9	402.3	418.2	437.8	461.6	487.0	512.3	527.7
57.5°	306.3	315.1	325.4	342.2	357.4	376.4	393.8	412.4	435.9	455.0	465.0
60°	277.6	285.5	298.7	313.6	327.8	344.2	364.3	382.8	400.8	416.1	424.0
62.5°	250.5	259.7	271.2	284.8	300.3	315.9	333.5	348.9	364.8	378.0	383.4
65°	215.2	222.6	231.1	243.8	256.4	272.3	286.0	301.8	313.6	320.9	325.7
67.5°	183.1	187.9	194.4	202.8	215.3	229.1	242.5	254.9	264.6	269.6	273.9
70°	162.3	165.5	170.3	178.7	188.2	200.4	214.1	223.1	231.6	235.8	240.0
72.5°	141.6	145.6	150.0	156.7	164.5	173.3	183.3	194.4	199.0	204.1	206.6
75°	107.3	113.1	119.0	123.2	128.5	135.3	144.3	151.2	153.9	158.0	158.6
77.5°	81.0	82.3	86.5	91.8	96.2	101.2	106.9	113.0	114.3	116.5	118.0
80°	66.7	66.7	66.7	69.8	75.0	78.8	84.0	87.3	89.4	89.9	90.4
82.5°	53.5	53.5	53.1	53.7	55.6	57.7	62.5	66.0	67.8	67.5	66.3
85°	34.9	33.8	33.8	33.3	33.8	32.8	32.2	34.3	37.6	37.6	36.5
87.5°	19.4	18.8	18.7	17.7	16.7	15.7	13.8	13.8	13.3	14.6	13.7
90°	25.0	24.2	21.3	18.4	15.5	12.5	10.0	7.8	5.5	3.2	1.0
92.5°	39.4	38.7	37.1	35.3	33.7	32.1	30.5	29.0	27.5	26.0	24.4
95°	75.5	74.6	72.8	71.0	69.2	67.5	65.7	64.2	62.6	61.0	59.5
97.5°	117.8	116.7	115.4	114.1	112.8	111.5	110.3	109.2	108.0	106.8	105.6
100°	148.9	148.1	147.0	145.9	144.8	143.7	142.5	141.1	139.8	138.5	137.1
102.5°	184.3	183.7	182.2	180.7	179.3	177.7	176.6	175.8	175.0	174.2	173.4
105°	237.9	237.9	235.9	233.9	231.9	229.8	228.6	228.1	227.7	227.2	226.8
107.5°	294.5	293.8	293.0	292.2	291.3	290.5	290.0	289.7	289.4	289.2	288.9
110°	332.5	331.6	331.2	330.7	330.3	329.8	329.4	328.9	328.5	328.1	327.6



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	370.6	369.5	369.5	369.4	369.3	369.2	369.0	368.7	368.5	368.2	367.9
115°	429.7	429.4	429.9	430.3	430.8	431.2	431.1	430.4	429.8	429.1	428.4
117.5°	488.7	488.7	489.3	489.9	490.5	491.0	491.1	490.7	490.2	489.8	489.3
120°	528.0	528.3	529.4	530.5	531.6	532.7	532.6	531.3	529.9	528.6	527.3
122.5°	567.9	568.6	569.2	569.7	570.3	570.9	570.7	569.7	568.7	567.7	566.7
125°	627.1	628.0	628.4	628.9	629.3	629.9	629.7	629.0	628.3	627.7	627.0
127.5°	685.6	686.9	687.4	687.9	688.3	688.8	688.4	686.9	685.5	684.1	682.7
130°	723.9	724.8	725.5	726.1	726.8	727.5	726.9	725.1	723.4	721.5	719.7
132.5°	761.6	762.7	763.2	763.7	764.2	764.7	764.1	762.2	760.4	758.6	756.9
135°	817.7	818.5	818.8	819.0	819.2	819.4	818.9	817.5	816.2	814.9	813.5
137.5°	872.6	873.5	873.0	872.4	871.8	871.2	870.4	869.3	868.2	867.1	866.0
140°	908.1	908.3	908.1	907.8	907.6	907.4	906.7	905.5	904.4	903.3	902.2
142.5°	941.9	942.1	941.7	941.3	940.9	940.5	939.8	938.7	937.6	936.3	935.2
145°	991.7	991.9	991.3	990.6	989.9	989.3	988.7	988.3	987.7	987.3	986.8
147.5°	1038.5	1038.5	1037.8	1037.2	1036.6	1036.0	1035.3	1034.5	1033.7	1032.9	1032.1
150°	1067.5	1067.5	1067.1	1066.6	1066.2	1065.7	1065.3	1064.8	1064.4	1064.0	1063.5
152.5°	1093.7	1093.4	1093.1	1092.8	1092.6	1092.3	1091.8	1091.2	1090.6	1089.9	1089.3
155°	1132.0	1131.0	1130.8	1130.5	1130.3	1130.1	1130.0	1130.0	1130.0	1130.0	1130.0
157.5°	1165.3	1164.3	1164.2	1164.0	1163.8	1163.6	1163.7	1163.9	1164.2	1164.5	1164.7
160°	1185.6	1184.5	1184.5	1184.5	1184.5	1184.5	1184.7	1185.2	1185.6	1186.0	1186.5
162.5°	1205.0	1203.9	1203.7	1203.5	1203.3	1203.2	1203.4	1204.0	1204.6	1205.2	1205.9
165°	1229.1	1227.8	1227.8	1227.8	1227.8	1227.8	1228.2	1228.8	1229.5	1230.1	1230.8
167.5°	1249.0	1247.6	1247.4	1247.2	1247.1	1246.9	1247.2	1248.1	1249.0	1249.9	1250.8
170°	1259.6	1258.1	1258.1	1258.1	1258.1	1258.1	1258.5	1259.4	1260.3	1261.2	1262.1
172.5°	1268.3	1266.9	1266.9	1266.9	1266.9	1266.9	1267.4	1268.3	1269.2	1270.1	1270.9
175°	1277.6	1276.2	1276.2	1276.2	1276.2	1276.2	1276.7	1277.6	1278.4	1279.3	1280.2
177.5°	1281.9	1280.8	1280.8	1280.8	1280.8	1280.8	1281.2	1281.9	1282.6	1283.3	1284.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1241.8	1246.5	1252.4	1261.3	1268.1	1273.9	1275.3	1277.0	1281.2	1288.4	1293.8
5°	1249.9	1262.0	1281.6	1300.6	1321.3	1338.2	1354.0	1365.1	1375.7	1398.0	1415.9
7.5°	1247.4	1274.4	1305.0	1339.3	1373.8	1407.3	1438.5	1466.2	1493.9	1526.3	1563.2
10°	1245.7	1277.4	1318.6	1362.5	1410.6	1457.6	1503.2	1538.5	1579.8	1616.8	1663.9
12.5°	1237.6	1283.3	1332.6	1388.8	1447.8	1502.1	1562.0	1610.9	1658.1	1711.5	1766.3
15°	1227.2	1282.6	1345.0	1419.6	1509.4	1575.1	1636.4	1721.5	1779.7	1837.9	1916.0
17.5°	1208.0	1275.8	1353.7	1450.6	1525.6	1613.7	1706.0	1773.2	1851.6	1933.5	2004.4
20°	1192.8	1271.5	1358.8	1454.0	1549.6	1645.4	1734.7	1815.0	1896.0	1990.6	2048.8
22.5°	1177.6	1255.5	1346.2	1447.2	1550.0	1650.8	1752.0	1846.3	1937.4	2033.0	2107.2
25°	1145.2	1237.7	1336.1	1439.2	1540.7	1651.7	1772.2	1877.4	1990.0	2088.4	2158.8
27.5°	1112.4	1197.2	1295.2	1399.7	1512.6	1643.8	1785.5	1905.2	2018.0	2088.4	2110.5
30°	1082.8	1172.7	1262.5	1368.9	1491.0	1637.4	1788.1	1925.0	2017.6	2048.2	2025.5
32.5°	1052.8	1134.2	1223.2	1332.0	1461.8	1621.7	1791.5	1913.2	1968.9	1945.5	1852.9
35°	999.8	1073.3	1159.4	1268.4	1417.4	1613.2	1777.6	1860.0	1846.2	1714.0	1539.6
37.5°	943.1	1003.0	1082.8	1196.7	1371.6	1578.7	1717.5	1729.6	1610.6	1407.8	1206.2
40°	898.3	952.2	1034.2	1153.2	1336.1	1544.9	1657.0	1607.8	1423.3	1197.5	1029.5
42.5°	854.7	900.2	979.2	1107.4	1302.2	1498.8	1566.9	1459.8	1246.9	1033.4	880.5
45°	780.9	823.7	903.0	1034.7	1232.9	1410.6	1401.6	1215.5	1002.5	830.6	703.7
47.5°	710.9	748.3	822.7	957.2	1151.7	1278.4	1194.4	996.3	815.6	677.7	587.2
50°	661.5	698.4	772.4	905.1	1086.5	1179.0	1059.0	868.2	702.7	588.4	516.5
52.5°	614.1	650.3	717.9	847.2	1007.8	1063.2	934.2	757.3	619.4	520.8	459.0
55°	547.8	575.2	636.0	759.7	879.8	892.5	761.8	613.8	500.2	431.4	389.1
57.5°	480.2	503.8	563.9	662.5	746.7	740.1	616.3	488.2	411.6	360.6	329.9
60°	436.2	459.5	512.3	596.9	660.4	638.1	524.5	421.4	355.8	318.3	294.0
62.5°	395.2	413.3	462.8	524.6	570.3	545.1	448.4	363.0	311.0	279.3	260.1
65°	335.8	350.5	390.2	422.4	447.8	423.5	343.2	283.9	246.4	224.2	211.0
67.5°	279.2	288.7	313.8	325.4	343.3	316.6	258.0	218.3	197.0	178.2	169.1
70°	243.8	250.6	263.9	273.4	278.1	250.6	207.2	178.1	160.2	146.9	141.2
72.5°	208.2	214.2	216.9	224.7	222.3	196.5	166.6	143.5	130.6	121.6	114.1
75°	159.2	161.8	159.2	155.9	149.1	131.1	110.5	98.9	89.4	85.1	82.5
77.5°	116.0	115.1	111.6	106.5	94.8	83.5	72.4	68.6	64.4	62.2	61.2
80°	89.4	87.3	84.0	76.1	66.0	58.2	55.5	52.9	51.3	48.7	48.1
82.5°	66.6	65.2	60.0	53.3	46.3	42.5	40.3	39.4	37.8	36.4	36.3
85°	35.4	33.8	28.0	24.3	23.2	22.2	21.7	21.7	19.6	19.0	19.0
87.5°	12.1	10.0	10.0	9.2	9.7	9.4	10.4	10.2	10.3	10.9	10.3
90°	3.2	5.5	7.8	10.0	12.5	15.5	18.4	21.3	24.2	25.0	26.0
92.5°	26.0	27.5	29.0	30.5	32.1	33.7	35.3	37.1	38.7	39.4	40.2
95°	61.0	62.6	64.2	65.7	67.5	69.2	71.0	72.8	74.6	75.5	76.3
97.5°	106.8	108.0	109.2	110.3	111.5	112.8	114.1	115.4	116.7	117.8	118.8
100°	138.5	139.8	141.1	142.5	143.7	144.8	145.9	147.0	148.1	148.9	149.6
102.5°	174.2	175.0	175.8	176.6	177.7	179.3	180.7	182.2	183.7	184.3	185.0
105°	227.2	227.7	228.1	228.6	229.8	231.9	233.9	235.9	237.9	237.9	237.9
107.5°	289.2	289.4	289.7	290.0	290.5	291.3	292.2	293.0	293.8	294.5	295.2
110°	328.1	328.5	328.9	329.4	329.8	330.3	330.7	331.2	331.6	332.5	333.5



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	368.2	368.5	368.7	369.0	369.2	369.3	369.4	369.5	369.5	370.6	371.7
115°	429.1	429.8	430.4	431.1	431.2	430.8	430.3	429.9	429.4	429.7	429.9
117.5°	489.8	490.2	490.7	491.1	491.0	490.5	489.9	489.3	488.7	488.7	488.6
120°	528.6	529.9	531.3	532.6	532.7	531.6	530.5	529.4	528.3	528.0	527.8
122.5°	567.7	568.7	569.7	570.7	570.9	570.3	569.7	569.2	568.6	567.9	567.3
125°	627.7	628.3	629.0	629.7	629.9	629.3	628.9	628.4	628.0	627.1	626.2
127.5°	684.1	685.5	686.9	688.4	688.8	688.3	687.9	687.4	686.9	685.6	684.4
130°	721.5	723.4	725.1	726.9	727.5	726.8	726.1	725.5	724.8	723.9	723.0
132.5°	758.6	760.4	762.2	764.1	764.7	764.2	763.7	763.2	762.7	761.6	760.5
135°	814.9	816.2	817.5	818.9	819.4	819.2	819.0	818.8	818.5	817.7	816.8
137.5°	867.1	868.2	869.3	870.4	871.2	871.8	872.4	873.0	873.5	872.6	871.7
140°	903.3	904.4	905.5	906.7	907.4	907.6	907.8	908.1	908.3	908.1	907.8
142.5°	936.3	937.6	938.7	939.8	940.5	940.9	941.3	941.7	942.1	941.9	941.7
145°	987.3	987.7	988.3	988.7	989.3	989.9	990.6	991.3	991.9	991.7	991.5
147.5°	1032.9	1033.7	1034.5	1035.3	1036.0	1036.6	1037.2	1037.8	1038.5	1038.5	1038.5
150°	1064.0	1064.4	1064.8	1065.3	1065.7	1066.2	1066.6	1067.1	1067.5	1067.5	1067.5
152.5°	1089.9	1090.6	1091.2	1091.8	1092.3	1092.6	1092.8	1093.1	1093.4	1093.7	1094.1
155°	1130.0	1130.0	1130.0	1130.0	1130.1	1130.3	1130.5	1130.8	1131.0	1132.0	1132.9
157.5°	1164.5	1164.2	1163.9	1163.7	1163.6	1163.8	1164.0	1164.2	1164.3	1165.3	1166.2
160°	1186.0	1185.6	1185.2	1184.7	1184.5	1184.5	1184.5	1184.5	1184.5	1185.6	1186.7
162.5°	1205.2	1204.6	1204.0	1203.4	1203.2	1203.3	1203.5	1203.7	1203.9	1205.0	1206.1
165°	1230.1	1229.5	1228.8	1228.2	1227.8	1227.8	1227.8	1227.8	1227.8	1229.1	1230.5
167.5°	1249.9	1249.0	1248.1	1247.2	1246.9	1247.1	1247.2	1247.4	1247.6	1249.0	1250.3
170°	1261.2	1260.3	1259.4	1258.5	1258.1	1258.1	1258.1	1258.1	1258.1	1259.6	1261.2
172.5°	1270.1	1269.2	1268.3	1267.4	1266.9	1266.9	1266.9	1266.9	1266.9	1268.3	1269.7
175°	1279.3	1278.4	1277.6	1276.7	1276.2	1276.2	1276.2	1276.2	1276.2	1277.6	1278.9
177.5°	1283.3	1282.6	1281.9	1281.2	1280.8	1280.8	1280.8	1280.8	1280.8	1281.9	1283.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1	1235.1
2.5°	1302.7	1302.7	1304.4	1310.8	1311.6	1317.2	1315.5
5°	1431.8	1441.8	1445.5	1461.4	1470.9	1475.1	1466.6
7.5°	1589.5	1617.9	1631.3	1647.9	1662.6	1667.1	1655.5
10°	1704.6	1734.1	1759.1	1774.3	1788.7	1798.2	1810.3
12.5°	1815.8	1852.2	1875.8	1897.4	1912.2	1924.2	1926.2
15°	1936.7	1991.7	2033.5	2064.1	2079.4	2087.4	2084.2
17.5°	2058.6	2109.6	2139.3	2170.6	2191.8	2192.9	2193.5
20°	2127.6	2177.3	2211.6	2234.8	2258.7	2257.7	2262.9
22.5°	2173.6	2212.8	2239.1	2256.0	2264.2	2260.2	2261.2
25°	2195.2	2206.9	2202.1	2175.1	2168.3	2143.4	2147.7
27.5°	2084.0	2029.0	1972.1	1899.0	1841.2	1795.1	1797.5
30°	1933.0	1835.7	1724.6	1631.6	1548.1	1524.8	1475.1
32.5°	1721.9	1576.0	1445.9	1359.2	1287.5	1268.1	1224.8
35°	1364.1	1222.3	1088.6	1008.2	976.5	932.1	931.6
37.5°	1060.3	935.5	864.7	804.5	772.8	746.0	743.4
40°	891.9	794.7	741.2	697.9	666.7	646.6	641.9
42.5°	774.4	695.7	645.7	618.8	594.8	584.4	576.7
45°	632.4	579.5	544.6	520.3	509.2	501.2	497.0
47.5°	529.0	493.5	469.7	453.5	444.5	436.2	438.4
50°	472.7	443.6	426.2	410.8	403.9	398.1	398.7
52.5°	427.4	401.3	387.2	376.2	367.6	363.5	361.4
55°	362.7	346.3	332.0	324.1	319.3	313.6	311.9
57.5°	309.4	296.7	285.1	276.1	274.9	269.3	270.0
60°	273.9	263.3	253.8	249.0	245.3	240.5	242.2
62.5°	244.7	235.8	227.1	223.2	219.5	216.0	216.8
65°	200.4	191.9	186.6	184.5	182.9	181.4	179.8
67.5°	159.7	154.5	151.2	146.6	143.4	142.9	141.3
70°	134.3	127.4	121.6	115.8	114.2	113.7	114.2
72.5°	107.7	103.3	101.7	98.9	98.6	97.1	98.2
75°	80.9	79.3	78.3	76.1	76.1	76.1	76.1
77.5°	59.7	58.7	58.1	57.7	57.1	56.4	56.2
80°	46.6	45.9	44.9	44.9	44.4	44.9	44.4
82.5°	35.1	35.0	33.9	33.9	33.4	33.1	33.4
85°	18.0	17.5	18.5	17.5	18.0	17.0	18.0
87.5°	10.4	10.6	10.3	10.4	10.1	11.0	10.3
90°	26.9	27.8	28.5	28.9	29.4	29.8	30.2
92.5°	40.9	41.6	41.8	41.5	41.3	41.0	40.7
95°	77.3	78.2	78.7	78.7	78.7	78.7	78.7
97.5°	119.9	120.9	121.3	121.3	121.2	121.1	121.0
100°	150.2	150.9	151.5	151.9	152.3	152.8	153.2
102.5°	185.7	186.3	186.6	186.5	186.4	186.4	186.3
105°	237.9	237.9	238.1	238.5	239.0	239.4	239.9
107.5°	295.9	296.6	296.8	296.6	296.3	296.0	295.8
110°	334.4	335.3	335.5	335.0	334.6	334.2	333.7



TEST NUMBER: P332319-840

CATALOG NUMBER: S123RDIP-S775D1025U840-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	372.7	373.9	374.4	374.3	374.2	374.1	374.0
115°	430.1	430.3	430.3	430.1	429.9	429.7	429.4
117.5°	488.6	488.6	488.2	487.6	487.0	486.4	485.6
120°	527.6	527.4	526.9	526.5	526.1	525.6	525.2
122.5°	566.8	566.2	565.6	565.0	564.3	563.7	563.1
125°	625.3	624.4	623.5	622.7	621.8	620.9	620.0
127.5°	683.2	681.9	680.8	679.7	678.6	677.6	676.6
130°	722.1	721.2	719.9	718.4	716.8	715.3	713.7
132.5°	759.5	758.4	757.3	756.1	754.9	753.7	752.5
135°	815.9	815.0	814.3	813.9	813.3	812.9	812.5
137.5°	870.8	869.8	868.9	868.1	867.2	866.4	865.6
140°	907.6	907.4	906.5	904.9	903.3	901.8	900.2
142.5°	941.5	941.2	940.5	939.3	938.1	936.9	935.6
145°	991.3	991.0	990.5	989.6	988.7	987.7	986.8
147.5°	1038.5	1038.5	1037.8	1036.5	1035.1	1033.8	1032.5
150°	1067.5	1067.5	1066.8	1065.5	1064.2	1062.8	1061.5
152.5°	1094.4	1094.8	1094.4	1093.2	1092.1	1090.9	1089.7
155°	1133.8	1134.6	1134.3	1132.8	1131.1	1129.5	1128.0
157.5°	1167.1	1168.1	1167.9	1166.7	1165.4	1164.2	1162.9
160°	1187.8	1188.9	1189.0	1188.2	1187.3	1186.4	1185.5
162.5°	1207.2	1208.3	1208.1	1206.7	1205.3	1203.9	1202.4
165°	1231.8	1233.1	1233.0	1231.5	1229.9	1228.4	1226.8
167.5°	1251.7	1253.1	1253.1	1251.7	1250.3	1249.0	1247.6
170°	1262.7	1264.4	1264.4	1262.7	1261.2	1259.6	1258.1
172.5°	1271.1	1272.4	1272.4	1270.8	1269.3	1267.7	1266.1
175°	1280.2	1281.6	1281.4	1279.9	1278.3	1276.8	1275.2
177.5°	1284.0	1285.2	1285.1	1283.8	1282.5	1281.3	1280.0
180°	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2	1283.2

(END OF REPORT)