

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P998804

Luminaire Tested: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P998804
REPORT IS A COMBINATION OF REPORTS P984550 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5037.0 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	96	92	89	93	90	87	84	78	76	73	67	65	64	57	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47
3	84	75	68	62	78	70	64	59	61	57	53	53	50	47	46	43	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	40	41	38	36
5	71	60	52	46	66	56	49	44	49	44	40	43	39	35	37	34	31
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	31	28	31	28	25
8	57	45	37	32	53	42	35	30	37	32	28	33	29	25	29	25	23
9	53	41	33	28	49	39	32	27	34	29	25	31	26	23	27	23	21
10	50	38	30	26	46	36	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21015	21015	21015	21015
5°	21065	22407	21146	17826
10°	20820	24460	20951	14697
15°	20316	25800	20597	12380
20°	19999	24224	19999	10760
25°	19360	20811	19448	9622
30°	18312	16359	18661	8716
35°	17383	11312	17674	7975
40°	16315	8542	16501	7384
45°	14998	7019	15244	6746
50°	13860	6160	13884	6174
55°	12561	5249	12644	5555
60°	11179	4385	11334	4849
65°	9940	3566	10121	4141
70°	8705	2799	8926	3340
75°	7306	2031	7591	2421
80°	5700	1287	6108	1438
85°	3743	649	4040	480

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21722 cd/sqm

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.4	2.5
10°-20°	368.0	7.3
20°-30°	534.1	10.6
30°-40°	563.1	11.2
40°-50°	498.3	9.9
50°-60°	397.9	7.9
60°-70°	270.2	5.4
70°-80°	138.3	2.7
80°-90°	33.9	0.7
90°-100°	23.7	0.5
100°-110°	88.3	1.8
110°-120°	234.3	4.7
120°-130°	388.6	7.7
130°-140°	412.7	8.2
140°-150°	383.6	7.6
150°-160°	308.4	6.1
160°-170°	198.7	3.9
170°-180°	68.4	1.4
0°-30°	1028.6	20.4
0°-40°	1591.7	31.6
0°-60°	2487.8	49.4
0°-90°	2930.3	58.2
90°-120°	346.3	6.9
90°-150°	1531.2	30.4
90°-180°	2107.0	41.8
0°-180°	5037.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1329	1483	1334	1180	1329	126
15°	1248	1822	1265	874	1248	352
25°	1121	1518	1126	702	1121	513
35°	915	826	931	583	915	573
45°	687	498	698	479	687	533
55°	471	350	474	370	471	421
65°	280	215	285	250	280	278
75°	131	106	136	126	131	140
85°	26	28	29	20	26	31
90°	0	14	0	14	0	3
95°	34	22	34	22	34	40
105°	158	40	158	40	158	169
115°	299	43	299	43	299	294
125°	423	445	423	445	423	377
135°	523	540	523	540	523	404
145°	607	616	607	616	607	380
155°	668	669	668	669	668	308
165°	704	702	704	702	704	199
175°	720	716	720	716	720	69
180°	719	719	719	719	719	

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1334.7	1337.8	1342.9	1343.9	1354.1	1362.3	1371.4	1371.4	1374.5	1373.5	1365.3
5°	1328.6	1337.8	1351.0	1362.3	1380.6	1388.8	1401.0	1410.2	1418.4	1424.5	1423.5
7.5°	1318.4	1334.7	1354.1	1375.5	1400.0	1414.3	1431.6	1448.0	1459.2	1469.4	1476.5
10°	1301.0	1328.6	1355.1	1383.7	1415.3	1434.7	1455.1	1476.5	1493.9	1513.3	1531.6
12.5°	1277.6	1317.4	1350.0	1387.8	1426.5	1448.0	1480.6	1496.9	1530.6	1579.6	1592.9
15°	1248.0	1302.0	1332.7	1380.6	1431.6	1449.0	1493.9	1520.4	1589.8	1620.4	1657.2
17.5°	1220.4	1280.6	1321.4	1376.5	1426.5	1460.2	1504.1	1558.2	1616.3	1660.2	1701.0
20°	1198.0	1256.1	1305.1	1366.3	1429.6	1472.5	1518.4	1583.7	1646.9	1691.8	1723.5
22.5°	1146.9	1221.4	1278.6	1346.9	1423.5	1482.7	1526.5	1598.0	1666.3	1693.9	1721.4
25°	1121.4	1185.7	1252.0	1329.6	1419.4	1489.8	1527.6	1607.2	1667.4	1677.6	1683.7
27.5°	1074.5	1146.9	1224.5	1313.3	1418.4	1477.6	1525.5	1598.0	1645.9	1638.8	1620.4
30°	1016.3	1105.1	1190.8	1286.7	1404.1	1468.4	1513.3	1579.6	1604.1	1567.4	1534.7
32.5°	973.5	1057.1	1152.0	1263.3	1387.8	1449.0	1492.9	1544.9	1550.0	1483.7	1428.6
35°	915.3	1008.2	1115.3	1232.7	1360.2	1415.3	1456.1	1487.8	1463.3	1370.4	1305.1
37.5°	863.3	955.1	1069.4	1188.8	1322.5	1376.5	1409.2	1414.3	1354.1	1272.5	1176.5
40°	806.1	901.0	1020.4	1145.9	1280.6	1327.6	1348.0	1332.7	1245.9	1151.0	1039.8
42.5°	749.0	842.9	971.4	1100.0	1227.6	1267.4	1275.5	1233.7	1127.6	1016.3	887.8
45°	686.7	784.7	913.3	1042.9	1166.3	1188.8	1189.8	1129.6	1004.1	887.8	768.4
47.5°	635.7	726.5	854.1	983.7	1087.8	1103.1	1096.9	1027.6	890.8	760.2	656.1
50°	579.6	666.3	792.9	920.4	1009.2	1013.3	998.0	899.0	765.3	645.9	563.3
52.5°	519.4	607.1	723.5	845.9	925.5	919.4	889.8	783.7	658.2	559.2	495.9
55°	471.4	549.0	658.2	777.6	833.7	816.3	783.7	675.5	576.5	492.9	437.8
57.5°	418.4	486.7	593.9	698.0	730.6	714.3	681.6	580.6	488.8	425.5	388.8
60°	368.4	430.6	524.5	611.2	636.7	619.4	581.6	490.8	424.5	371.4	343.9
62.5°	322.5	376.5	455.1	534.7	544.9	527.6	494.9	421.4	364.3	322.5	302.0
65°	279.6	330.6	393.9	454.1	463.3	444.9	411.2	358.2	310.2	283.7	264.3
67.5°	237.8	278.6	334.7	378.6	383.7	366.3	338.8	295.9	266.3	237.8	223.5
70°	201.0	231.6	275.5	311.2	313.3	296.9	282.7	243.9	221.4	201.0	189.8
72.5°	165.3	186.7	220.4	246.9	248.0	237.8	224.5	200.0	180.6	166.3	155.1
75°	130.6	149.0	169.4	192.9	191.8	183.7	173.5	158.2	141.8	132.7	127.6
77.5°	100.0	111.2	127.6	142.9	142.9	138.8	132.7	121.4	111.2	102.0	96.9
80°	71.4	78.6	91.8	96.9	99.0	98.0	92.9	84.7	80.6	73.5	71.4
82.5°	45.9	51.0	57.1	62.2	65.3	63.3	62.2	58.2	52.0	50.0	48.0
85°	26.5	28.6	31.6	34.7	35.7	34.7	36.7	33.7	30.6	30.6	29.6
87.5°	11.2	12.2	14.3	14.3	15.3	15.3	14.3	15.3	15.3	14.3	13.3
90°	0.5	1.8	3.0	4.3	5.6	6.2	6.7	7.6	8.5	9.5	10.4
92.5°	13.0	12.5	12.1	11.6	11.1	10.9	11.1	11.4	11.8	12.1	12.5
95°	33.8	30.0	26.2	22.3	18.5	16.6	17.0	17.8	18.7	19.5	20.3
97.5°	60.8	51.3	41.9	32.4	22.9	18.2	19.1	21.0	22.8	24.7	26.5
100°	92.0	76.2	60.4	44.5	28.7	20.8	21.8	23.7	25.7	27.6	29.6
102.5°	126.4	126.2	125.9	125.7	125.4	125.3	114.8	93.8	72.7	51.7	30.7
105°	158.1	161.6	165.0	168.5	172.0	173.7	157.9	126.4	94.8	63.3	31.7
107.5°	195.0	197.9	200.8	203.7	206.6	208.0	188.5	149.6	110.7	71.7	32.8
110°	230.4	232.8	235.2	237.7	240.1	241.3	224.6	191.2	157.8	124.4	91.0

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	263.6	265.7	267.8	269.9	272.0	273.0	272.0	270.1	268.1	266.2	264.2
115°	299.0	301.0	302.9	304.9	306.8	307.8	309.2	312.1	315.0	317.9	320.8
117.5°	329.7	332.0	334.3	336.6	338.9	340.1	341.1	343.0	345.0	346.9	348.9
120°	364.0	365.7	367.5	369.2	370.9	371.8	372.8	374.9	377.0	379.0	381.1
122.5°	393.1	394.9	396.8	398.6	400.5	401.4	402.6	404.9	407.2	409.5	411.8
125°	422.7	424.2	425.7	427.2	428.7	429.5	430.6	432.8	435.0	437.2	439.4
127.5°	449.8	451.4	453.0	454.7	456.3	457.1	458.0	459.7	461.4	463.2	464.9
130°	475.3	477.1	479.0	480.8	482.7	483.6	484.2	485.5	486.8	488.0	489.3
132.5°	501.3	502.8	504.3	505.8	507.3	508.0	508.6	509.9	511.2	512.4	513.7
135°	523.1	524.9	526.8	528.6	530.5	531.4	531.9	533.0	534.0	535.1	536.1
137.5°	546.0	547.4	548.8	550.1	551.5	552.2	552.8	553.9	555.1	556.2	557.4
140°	568.3	569.2	570.2	571.1	572.0	572.5	573.1	574.4	575.7	576.9	578.2
142.5°	587.1	587.9	588.7	589.5	590.3	590.7	591.5	593.0	594.5	596.0	597.5
145°	606.8	606.7	606.6	606.5	606.4	606.3	607.3	609.2	611.2	613.1	615.1
147.5°	624.0	623.6	623.3	622.9	622.6	622.4	623.4	625.4	627.3	629.3	631.3
150°	640.6	639.8	639.0	638.2	637.4	637.0	637.9	639.8	641.6	643.5	645.3
152.5°	654.7	653.8	652.8	651.9	651.0	650.5	651.4	653.1	654.8	656.6	658.3
155°	668.2	667.2	666.1	665.1	664.0	663.5	664.2	665.6	666.9	668.3	669.7
157.5°	679.1	678.2	677.2	676.3	675.4	674.9	675.4	676.5	677.5	678.6	679.6
160°	688.5	687.8	687.1	686.4	685.7	685.3	685.7	686.4	687.1	687.8	688.5
162.5°	696.8	696.1	695.4	694.7	694.0	693.7	694.0	694.6	695.1	695.7	696.3
165°	704.1	703.4	702.7	702.0	701.3	700.9	701.1	701.4	701.8	702.1	702.5
167.5°	709.8	709.1	708.4	707.7	707.0	706.7	706.9	707.2	707.5	707.9	708.2
170°	714.5	713.8	713.1	712.4	711.7	711.3	711.4	711.7	711.9	712.2	712.4
172.5°	717.6	716.9	716.2	715.5	714.8	714.5	714.6	714.8	715.1	715.3	715.5
175°	720.2	719.4	718.6	717.7	716.9	716.5	716.6	716.9	717.1	717.4	717.6
177.5°	721.2	720.4	719.6	718.8	718.0	717.6	717.7	717.8	717.9	718.0	718.1
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1379.6	1380.6	1382.7	1392.9	1398.0	1399.0	1394.9	1404.1	1407.2	1404.1	1402.0
5°	1444.9	1451.0	1463.3	1476.5	1475.5	1476.5	1482.7	1488.8	1490.8	1482.7	1485.7
7.5°	1502.1	1514.3	1527.6	1548.0	1548.0	1558.2	1562.3	1567.4	1579.6	1573.5	1571.4
10°	1567.4	1583.7	1608.2	1640.8	1641.8	1652.1	1662.3	1678.6	1683.7	1679.6	1681.6
12.5°	1649.0	1680.6	1682.7	1718.4	1734.7	1736.7	1753.1	1750.0	1760.2	1760.2	1777.6
15°	1684.7	1733.7	1761.2	1795.9	1806.1	1793.9	1807.2	1821.4	1822.5	1822.5	1821.4
17.5°	1749.0	1768.4	1795.9	1814.3	1818.4	1818.4	1819.4	1825.5	1821.4	1813.3	1819.4
20°	1762.3	1770.4	1780.6	1778.6	1780.6	1770.4	1760.2	1750.0	1751.0	1745.9	1761.2
22.5°	1737.8	1735.7	1712.3	1696.9	1696.9	1676.5	1657.2	1648.0	1638.8	1641.8	1646.9
25°	1676.5	1644.9	1616.3	1593.9	1588.8	1556.1	1529.6	1521.4	1506.1	1518.4	1520.4
27.5°	1578.6	1542.9	1496.9	1477.6	1451.0	1437.8	1419.4	1394.9	1363.3	1381.6	1378.6
30°	1473.5	1420.4	1382.7	1335.7	1293.9	1290.8	1256.1	1215.3	1199.0	1199.0	1208.2
32.5°	1356.1	1285.7	1230.6	1164.3	1123.5	1106.1	1064.3	1023.5	1032.7	1002.0	1013.3
35°	1219.4	1126.5	1057.1	992.9	962.3	941.8	887.8	865.3	840.8	826.5	853.1
37.5°	1088.8	981.6	892.9	822.5	811.2	774.5	737.8	723.5	709.2	715.3	714.3
40°	929.6	834.7	755.1	700.0	680.6	663.3	638.8	621.4	612.2	617.4	618.4
42.5°	785.7	706.1	646.9	608.2	591.8	579.6	567.4	553.1	550.0	550.0	554.1
45°	674.5	609.2	569.4	537.8	528.6	519.4	510.2	504.1	502.0	498.0	501.0
47.5°	585.7	533.7	509.2	485.7	475.5	473.5	465.3	462.2	458.2	457.1	458.2
50°	511.2	478.6	456.1	442.9	435.7	432.7	428.6	422.5	420.4	425.5	423.5
52.5°	459.2	428.6	416.3	403.1	399.0	394.9	388.8	389.8	388.8	386.7	386.7
55°	407.1	387.8	375.5	365.3	364.3	360.2	355.1	353.1	352.0	350.0	353.1
57.5°	365.3	350.0	338.8	329.6	325.5	325.5	320.4	316.3	316.3	315.3	316.3
60°	323.5	308.2	301.0	291.8	288.8	287.8	284.7	282.7	279.6	279.6	279.6
62.5°	284.7	272.5	264.3	256.1	257.1	252.0	248.0	245.9	245.9	246.9	246.9
65°	248.0	239.8	229.6	222.5	220.4	219.4	217.3	216.3	213.3	215.3	215.3
67.5°	214.3	203.1	196.9	193.9	190.8	189.8	187.8	185.7	184.7	183.7	185.7
70°	180.6	171.4	166.3	164.3	161.2	160.2	159.2	156.1	157.1	158.2	159.2
72.5°	150.0	141.8	140.8	134.7	134.7	134.7	130.6	132.7	131.6	129.6	131.6
75°	118.4	114.3	112.2	109.2	110.2	109.2	108.2	105.1	105.1	106.1	107.1
77.5°	93.9	89.8	88.8	85.7	83.7	85.7	83.7	82.7	82.7	83.7	83.7
80°	69.4	67.3	64.3	64.3	64.3	63.3	63.3	63.3	62.2	61.2	62.2
82.5°	45.9	45.9	44.9	43.9	44.9	42.9	43.9	43.9	43.9	43.9	43.9
85°	29.6	28.6	28.6	27.6	27.6	27.6	28.6	26.5	26.5	27.6	27.6
87.5°	13.3	13.3	13.3	14.3	13.3	13.3	13.3	14.3	13.3	13.3	13.3
90°	11.0	11.6	12.1	12.7	13.0	13.1	13.3	13.6	13.8	14.0	13.8
92.5°	12.7	12.9	13.2	13.4	13.5	13.6	13.7	13.8	13.9	14.0	13.9
95°	20.9	21.5	22.0	22.6	22.9	22.8	22.7	22.6	22.5	22.4	22.5
97.5°	26.9	27.2	27.6	27.9	28.1	28.2	28.3	28.4	28.5	28.6	28.5
100°	30.5	31.5	32.4	33.3	33.8	33.9	34.1	34.4	34.6	34.8	34.6
102.5°	32.0	33.2	34.5	35.8	36.4	36.6	36.9	37.3	37.6	38.0	37.6
105°	33.0	34.2	35.5	36.8	37.4	37.6	38.1	38.6	39.0	39.5	39.0
107.5°	34.1	35.3	36.6	37.9	38.5	38.7	39.2	39.7	40.1	40.6	40.1
110°	79.4	67.9	56.3	44.8	39.0	39.2	39.7	40.2	40.6	41.1	40.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	214.4	164.6	114.7	64.9	40.0	40.2	40.5	40.9	41.2	41.6	41.2
115°	267.3	213.8	160.3	106.8	80.1	75.9	67.6	59.3	50.9	42.6	50.9
117.5°	332.4	315.9	299.4	282.9	274.6	259.5	229.2	198.9	168.6	138.3	168.6
120°	382.5	383.9	385.3	386.7	387.4	379.6	364.0	348.4	332.8	317.2	332.8
122.5°	412.5	413.2	413.9	414.6	414.9	415.0	415.1	415.2	415.4	415.5	415.4
125°	440.2	441.0	441.8	442.6	443.0	443.2	443.5	443.9	444.2	444.6	444.2
127.5°	466.1	467.2	468.4	469.5	470.1	470.2	470.3	470.4	470.5	470.6	470.5
130°	490.6	491.8	493.1	494.4	495.0	494.9	494.8	494.7	494.6	494.5	494.6
132.5°	514.7	515.8	516.8	517.9	518.4	518.3	518.2	518.1	518.0	517.9	518.0
135°	537.3	538.4	539.6	540.7	541.3	541.2	541.0	540.7	540.5	540.3	540.5
137.5°	558.6	559.7	560.9	562.0	562.6	562.4	562.1	561.8	561.4	561.1	561.4
140°	579.2	580.3	581.3	582.4	582.9	582.6	582.0	581.5	580.9	580.3	580.9
142.5°	598.4	599.3	600.2	601.1	601.6	601.3	600.7	600.2	599.6	599.0	599.6
145°	615.9	616.7	617.6	618.4	618.8	618.5	617.9	617.4	616.8	616.2	616.8
147.5°	631.9	632.5	633.0	633.6	633.9	633.7	633.2	632.7	632.3	631.8	632.3
150°	646.0	646.7	647.4	648.1	648.4	648.1	647.5	647.0	646.4	645.8	646.4
152.5°	659.0	659.7	660.4	661.1	661.4	661.0	660.2	659.4	658.6	657.8	658.6
155°	670.4	671.1	671.8	672.5	672.9	672.4	671.5	670.6	669.6	668.7	669.6
157.5°	680.4	681.2	682.1	682.9	683.3	682.8	681.9	681.0	680.0	679.1	680.0
160°	689.2	689.9	690.6	691.3	691.6	691.2	690.4	689.5	688.7	687.9	688.7
162.5°	697.1	697.9	698.7	699.5	699.9	699.4	698.3	697.3	696.2	695.2	696.2
165°	703.3	704.1	704.9	705.7	706.1	705.7	704.9	704.1	703.3	702.5	703.3
167.5°	709.0	709.8	710.7	711.5	711.9	711.4	710.3	709.3	708.2	707.2	708.2
170°	713.2	714.0	714.8	715.6	716.0	715.5	714.4	713.4	712.3	711.3	712.3
172.5°	716.3	717.1	717.9	718.7	719.1	718.6	717.6	716.5	715.5	714.5	715.5
175°	718.4	719.2	720.0	720.8	721.2	720.6	719.5	718.3	717.2	716.0	717.2
177.5°	718.9	719.7	720.5	721.3	721.7	721.2	720.2	719.1	718.1	717.1	718.1
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1407.2	1400.0	1393.9	1394.9	1400.0	1395.9	1385.7	1372.5	1367.4	1361.2	1367.4
5°	1491.8	1485.7	1473.5	1474.5	1471.4	1467.4	1451.0	1430.6	1430.6	1414.3	1412.3
7.5°	1575.5	1566.3	1558.2	1556.1	1544.9	1536.7	1522.5	1493.9	1482.7	1463.3	1452.0
10°	1669.4	1662.3	1653.1	1641.8	1635.7	1621.4	1598.0	1556.1	1535.7	1509.2	1489.8
12.5°	1764.3	1763.3	1742.9	1720.4	1719.4	1696.9	1680.6	1624.5	1596.9	1561.2	1515.3
15°	1824.5	1819.4	1808.2	1796.9	1800.0	1775.5	1738.8	1672.5	1654.1	1611.2	1562.3
17.5°	1823.5	1823.5	1820.4	1818.4	1815.3	1808.2	1787.8	1743.9	1714.3	1660.2	1614.3
20°	1765.3	1778.6	1781.6	1780.6	1790.8	1795.9	1794.9	1767.4	1743.9	1695.9	1649.0
22.5°	1649.0	1679.6	1692.9	1701.0	1722.5	1733.7	1760.2	1750.0	1743.9	1708.2	1668.4
25°	1540.8	1551.0	1590.8	1592.9	1622.5	1650.0	1676.5	1693.9	1716.3	1703.1	1669.4
27.5°	1401.0	1424.5	1453.1	1474.5	1480.6	1536.7	1580.6	1613.3	1664.3	1668.4	1657.2
30°	1242.9	1254.1	1301.0	1329.6	1362.3	1403.1	1466.3	1522.5	1568.4	1610.2	1624.5
32.5°	1050.0	1095.9	1123.5	1158.2	1186.7	1259.2	1336.7	1409.2	1462.3	1532.7	1563.3
35°	873.5	909.2	956.1	970.4	1022.5	1083.7	1184.7	1277.6	1358.2	1429.6	1491.8
37.5°	727.6	756.1	806.1	828.6	859.2	937.8	1022.5	1137.8	1234.7	1322.5	1400.0
40°	627.6	649.0	686.7	693.9	719.4	790.8	859.2	967.4	1095.9	1214.3	1299.0
42.5°	559.2	569.4	594.9	604.1	620.4	668.4	729.6	831.6	951.0	1073.5	1192.9
45°	510.2	517.4	532.7	540.8	561.2	582.7	632.7	714.3	808.2	931.6	1060.2
47.5°	466.3	475.5	481.6	486.7	498.0	521.4	554.1	614.3	704.1	817.4	941.8
50°	429.6	432.7	443.9	444.9	452.0	467.3	498.0	534.7	606.1	698.0	818.4
52.5°	392.9	395.9	403.1	410.2	413.3	425.5	445.9	476.5	529.6	602.0	709.2
55°	356.1	360.2	367.3	372.5	375.5	385.7	398.0	427.6	469.4	520.4	608.2
57.5°	319.4	328.6	330.6	333.7	338.8	350.0	361.2	378.6	411.2	458.2	522.5
60°	284.7	287.8	294.9	298.0	303.1	309.2	323.5	336.7	360.2	396.9	455.1
62.5°	249.0	256.1	259.2	262.2	266.3	273.5	282.7	296.9	317.3	346.9	392.9
65°	218.4	219.4	225.5	229.6	233.7	238.8	248.0	261.2	273.5	301.0	334.7
67.5°	188.8	190.8	192.9	196.9	202.0	207.1	215.3	222.5	237.8	256.1	282.7
70°	160.2	160.2	165.3	168.4	167.3	173.5	179.6	187.8	199.0	216.3	237.8
72.5°	134.7	133.7	137.8	138.8	140.8	144.9	149.0	157.1	163.3	176.5	192.9
75°	107.1	109.2	111.2	111.2	114.3	117.3	121.4	125.5	132.7	140.8	153.1
77.5°	84.7	84.7	86.7	87.8	90.8	89.8	93.9	98.0	103.1	110.2	119.4
80°	62.2	64.3	64.3	64.3	65.3	66.3	70.4	73.5	76.5	81.6	85.7
82.5°	43.9	43.9	45.9	45.9	45.9	48.0	48.0	49.0	51.0	54.1	57.1
85°	27.6	27.6	27.6	28.6	27.6	28.6	30.6	29.6	30.6	32.7	32.7
87.5°	13.3	13.3	13.3	13.3	13.3	14.3	13.3	14.3	15.3	15.3	15.3
90°	13.6	13.3	13.1	13.0	12.7	12.1	11.6	11.0	10.4	9.5	8.5
92.5°	13.8	13.7	13.6	13.5	13.4	13.2	12.9	12.7	12.5	12.1	11.8
95°	22.6	22.7	22.8	22.9	22.6	22.0	21.5	20.9	20.3	19.5	18.7
97.5°	28.4	28.3	28.2	28.1	27.9	27.6	27.2	26.9	26.5	24.7	22.8
100°	34.4	34.1	33.9	33.8	33.3	32.4	31.5	30.5	29.6	27.6	25.7
102.5°	37.3	36.9	36.6	36.4	35.8	34.5	33.2	32.0	30.7	51.7	72.7
105°	38.6	38.1	37.6	37.4	36.8	35.5	34.2	33.0	31.7	63.3	94.8
107.5°	39.7	39.2	38.7	38.5	37.9	36.6	35.3	34.1	32.8	71.7	110.7
110°	40.2	39.7	39.2	39.0	44.8	56.3	67.9	79.4	91.0	124.4	157.8



TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	40.9	40.5	40.2	40.0	64.9	114.7	164.6	214.4	264.2	266.2	268.1
115°	59.3	67.6	75.9	80.1	106.8	160.3	213.8	267.3	320.8	317.9	315.0
117.5°	198.9	229.2	259.5	274.6	282.9	299.4	315.9	332.4	348.9	346.9	345.0
120°	348.4	364.0	379.6	387.4	386.7	385.3	383.9	382.5	381.1	379.0	377.0
122.5°	415.2	415.1	415.0	414.9	414.6	413.9	413.2	412.5	411.8	409.5	407.2
125°	443.9	443.5	443.2	443.0	442.6	441.8	441.0	440.2	439.4	437.2	435.0
127.5°	470.4	470.3	470.2	470.1	469.5	468.4	467.2	466.1	464.9	463.2	461.4
130°	494.7	494.8	494.9	495.0	494.4	493.1	491.8	490.6	489.3	488.0	486.8
132.5°	518.1	518.2	518.3	518.4	517.9	516.8	515.8	514.7	513.7	512.4	511.2
135°	540.7	541.0	541.2	541.3	540.7	539.6	538.4	537.3	536.1	535.1	534.0
137.5°	561.8	562.1	562.4	562.6	562.0	560.9	559.7	558.6	557.4	556.2	555.1
140°	581.5	582.0	582.6	582.9	582.4	581.3	580.3	579.2	578.2	576.9	575.7
142.5°	600.2	600.7	601.3	601.6	601.1	600.2	599.3	598.4	597.5	596.0	594.5
145°	617.4	617.9	618.5	618.8	618.4	617.6	616.7	615.9	615.1	613.1	611.2
147.5°	632.7	633.2	633.7	633.9	633.6	633.0	632.5	631.9	631.3	629.3	627.3
150°	647.0	647.5	648.1	648.4	648.1	647.4	646.7	646.0	645.3	643.5	641.6
152.5°	659.4	660.2	661.0	661.4	661.1	660.4	659.7	659.0	658.3	656.6	654.8
155°	670.6	671.5	672.4	672.9	672.5	671.8	671.1	670.4	669.7	668.3	666.9
157.5°	681.0	681.9	682.8	683.3	682.9	682.1	681.2	680.4	679.6	678.6	677.5
160°	689.5	690.4	691.2	691.6	691.3	690.6	689.9	689.2	688.5	687.8	687.1
162.5°	697.3	698.3	699.4	699.9	699.5	698.7	697.9	697.1	696.3	695.7	695.1
165°	704.1	704.9	705.7	706.1	705.7	704.9	704.1	703.3	702.5	702.1	701.8
167.5°	709.3	710.3	711.4	711.9	711.5	710.7	709.8	709.0	708.2	707.9	707.5
170°	713.4	714.4	715.5	716.0	715.6	714.8	714.0	713.2	712.4	712.2	711.9
172.5°	716.5	717.6	718.6	719.1	718.7	717.9	717.1	716.3	715.5	715.3	715.1
175°	718.3	719.5	720.6	721.2	720.8	720.0	719.2	718.4	717.6	717.4	717.1
177.5°	719.1	720.2	721.2	721.7	721.3	720.5	719.7	718.9	718.1	718.0	717.9
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1362.3	1357.2	1354.1	1356.1	1350.0	1334.7	1334.7	1339.8	1333.7	1327.6	1318.4
5°	1400.0	1389.8	1383.7	1382.7	1368.4	1343.9	1338.8	1333.7	1320.4	1306.1	1290.8
7.5°	1436.7	1418.4	1408.2	1401.0	1380.6	1349.0	1335.7	1324.5	1303.1	1281.6	1262.3
10°	1467.4	1440.8	1428.6	1417.4	1390.8	1351.0	1329.6	1309.2	1281.6	1254.1	1229.6
12.5°	1491.8	1461.2	1445.9	1429.6	1396.9	1344.9	1318.4	1285.7	1258.2	1221.4	1196.9
15°	1532.7	1469.4	1455.1	1439.8	1406.1	1334.7	1302.0	1265.3	1227.6	1178.6	1152.0
17.5°	1565.3	1480.6	1479.6	1446.9	1403.1	1330.6	1280.6	1232.7	1191.8	1142.9	1101.0
20°	1584.7	1498.0	1481.6	1448.0	1392.9	1303.1	1251.0	1198.0	1154.1	1094.9	1053.1
22.5°	1601.0	1522.5	1479.6	1438.8	1371.4	1293.9	1217.4	1167.4	1107.1	1042.9	1003.1
25°	1607.2	1527.6	1482.7	1435.7	1356.1	1267.4	1180.6	1126.5	1059.2	1001.0	946.9
27.5°	1608.2	1526.5	1471.4	1422.5	1334.7	1232.7	1143.9	1086.7	1012.3	944.9	890.8
30°	1598.0	1515.3	1465.3	1412.3	1314.3	1201.0	1099.0	1035.7	956.1	888.8	832.7
32.5°	1567.4	1492.9	1452.0	1393.9	1287.8	1157.2	1056.1	985.7	902.0	835.7	781.6
35°	1516.3	1465.3	1420.4	1366.3	1253.1	1116.3	1013.3	930.6	845.9	782.7	731.6
37.5°	1453.1	1425.5	1383.7	1330.6	1213.3	1079.6	965.3	873.5	788.8	727.6	677.6
40°	1367.4	1374.5	1333.7	1285.7	1166.3	1029.6	903.1	815.3	735.7	678.6	629.6
42.5°	1274.5	1304.1	1280.6	1234.7	1114.3	974.5	857.1	760.2	682.7	623.5	582.7
45°	1174.5	1225.5	1211.2	1177.6	1060.2	916.3	791.8	698.0	629.6	572.5	536.7
47.5°	1065.3	1137.8	1137.8	1113.3	1000.0	858.2	735.7	639.8	572.5	531.6	496.9
50°	954.1	1035.7	1049.0	1032.7	932.7	791.8	667.4	580.6	522.5	482.7	457.1
52.5°	837.8	932.7	957.1	949.0	861.2	728.6	611.2	526.5	473.5	438.8	416.3
55°	726.5	836.7	863.3	866.3	784.7	659.2	549.0	474.5	423.5	400.0	380.6
57.5°	621.4	727.6	757.1	762.2	707.1	595.9	490.8	425.5	379.6	360.2	344.9
60°	531.6	620.4	659.2	670.4	622.5	522.5	436.7	373.5	338.8	320.4	306.1
62.5°	458.2	529.6	570.4	573.5	552.0	458.2	380.6	327.6	298.0	281.6	274.5
65°	386.7	451.0	475.5	487.8	470.4	396.9	328.6	284.7	261.2	246.9	239.8
67.5°	329.6	370.4	390.8	407.1	389.8	334.7	279.6	243.9	226.5	212.2	208.2
70°	270.4	304.1	319.4	335.7	320.4	278.6	238.8	206.1	190.8	179.6	174.5
72.5°	216.3	242.9	257.1	267.3	258.2	223.5	190.8	168.4	157.1	149.0	145.9
75°	171.4	189.8	198.0	205.1	201.0	174.5	154.1	135.7	125.5	118.4	116.3
77.5°	130.6	143.9	153.1	155.1	150.0	132.7	115.3	104.1	95.9	91.8	89.8
80°	92.9	101.0	106.1	109.2	104.1	96.9	84.7	76.5	69.4	64.3	63.3
82.5°	62.2	66.3	70.4	69.4	67.3	61.2	54.1	50.0	46.9	42.9	42.9
85°	35.7	36.7	38.8	39.8	38.8	34.7	30.6	28.6	26.5	23.5	23.5
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.3	11.2	11.2	10.2	9.2
90°	7.6	6.7	6.2	5.6	4.3	3.0	1.8	0.5	1.8	3.0	4.3
92.5°	11.4	11.1	10.9	11.1	11.6	12.1	12.5	13.0	12.5	12.1	11.6
95°	17.8	17.0	16.6	18.5	22.3	26.2	30.0	33.8	30.0	26.2	22.3
97.5°	21.0	19.1	18.2	22.9	32.4	41.9	51.3	60.8	51.3	41.9	32.4
100°	23.7	21.8	20.8	28.7	44.5	60.4	76.2	92.0	76.2	60.4	44.5
102.5°	93.8	114.8	125.3	125.4	125.7	125.9	126.2	126.4	126.2	125.9	125.7
105°	126.4	157.9	173.7	172.0	168.5	165.0	161.6	158.1	161.6	165.0	168.5
107.5°	149.6	188.5	208.0	206.6	203.7	200.8	197.9	195.0	197.9	200.8	203.7
110°	191.2	224.6	241.3	240.1	237.7	235.2	232.8	230.4	232.8	235.2	237.7

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	270.1	272.0	273.0	272.0	269.9	267.8	265.7	263.6	265.7	267.8	269.9
115°	312.1	309.2	307.8	306.8	304.9	302.9	301.0	299.0	301.0	302.9	304.9
117.5°	343.0	341.1	340.1	338.9	336.6	334.3	332.0	329.7	332.0	334.3	336.6
120°	374.9	372.8	371.8	370.9	369.2	367.5	365.7	364.0	365.7	367.5	369.2
122.5°	404.9	402.6	401.4	400.5	398.6	396.8	394.9	393.1	394.9	396.8	398.6
125°	432.8	430.6	429.5	428.7	427.2	425.7	424.2	422.7	424.2	425.7	427.2
127.5°	459.7	458.0	457.1	456.3	454.7	453.0	451.4	449.8	451.4	453.0	454.7
130°	485.5	484.2	483.6	482.7	480.8	479.0	477.1	475.3	477.1	479.0	480.8
132.5°	509.9	508.6	508.0	507.3	505.8	504.3	502.8	501.3	502.8	504.3	505.8
135°	533.0	531.9	531.4	530.5	528.6	526.8	524.9	523.1	524.9	526.8	528.6
137.5°	553.9	552.8	552.2	551.5	550.1	548.8	547.4	546.0	547.4	548.8	550.1
140°	574.4	573.1	572.5	572.0	571.1	570.2	569.2	568.3	569.2	570.2	571.1
142.5°	593.0	591.5	590.7	590.3	589.5	588.7	587.9	587.1	587.9	588.7	589.5
145°	609.2	607.3	606.3	606.4	606.5	606.6	606.7	606.8	606.7	606.6	606.5
147.5°	625.4	623.4	622.4	622.6	622.9	623.3	623.6	624.0	623.6	623.3	622.9
150°	639.8	637.9	637.0	637.4	638.2	639.0	639.8	640.6	639.8	639.0	638.2
152.5°	653.1	651.4	650.5	651.0	651.9	652.8	653.8	654.7	653.8	652.8	651.9
155°	665.6	664.2	663.5	664.0	665.1	666.1	667.2	668.2	667.2	666.1	665.1
157.5°	676.5	675.4	674.9	675.4	676.3	677.2	678.2	679.1	678.2	677.2	676.3
160°	686.4	685.7	685.3	685.7	686.4	687.1	687.8	688.5	687.8	687.1	686.4
162.5°	694.6	694.0	693.7	694.0	694.7	695.4	696.1	696.8	696.1	695.4	694.7
165°	701.4	701.1	700.9	701.3	702.0	702.7	703.4	704.1	703.4	702.7	702.0
167.5°	707.2	706.9	706.7	707.0	707.7	708.4	709.1	709.8	709.1	708.4	707.7
170°	711.7	711.4	711.3	711.7	712.4	713.1	713.8	714.5	713.8	713.1	712.4
172.5°	714.8	714.6	714.5	714.8	715.5	716.2	716.9	717.6	716.9	716.2	715.5
175°	716.9	716.6	716.5	716.9	717.7	718.6	719.4	720.2	719.4	718.6	717.7
177.5°	717.8	717.7	717.6	718.0	718.8	719.6	720.4	721.2	720.4	719.6	718.8
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1313.3	1318.4	1317.4	1307.2	1295.9	1286.7	1269.4	1271.4	1265.3	1266.3	1272.5
5°	1280.6	1280.6	1276.5	1262.3	1243.9	1233.7	1214.3	1209.2	1196.9	1195.9	1194.9
7.5°	1245.9	1240.8	1235.7	1215.3	1192.9	1176.5	1150.0	1143.9	1131.6	1123.5	1119.4
10°	1205.1	1198.0	1187.8	1164.3	1136.7	1116.3	1088.8	1080.6	1057.1	1046.9	1040.8
12.5°	1160.2	1156.1	1139.8	1120.4	1075.5	1053.1	1013.3	1021.4	998.0	977.6	974.5
15°	1115.3	1100.0	1090.8	1059.2	1005.1	994.9	963.3	946.9	925.5	909.2	909.2
17.5°	1071.4	1048.0	1027.6	993.9	954.1	925.5	902.0	893.9	867.4	851.0	848.0
20°	1013.3	986.7	981.6	933.7	906.1	874.5	852.0	831.6	812.2	805.1	800.0
22.5°	958.2	927.6	919.4	878.6	851.0	819.4	796.9	782.7	768.4	763.3	754.1
25°	899.0	880.6	868.4	824.5	793.9	764.3	749.0	738.8	725.5	724.5	718.4
27.5°	841.8	824.5	812.2	770.4	748.0	720.4	708.2	696.9	689.8	686.7	683.7
30°	792.9	773.5	759.2	728.6	701.0	678.6	668.4	661.2	657.1	652.0	651.0
32.5°	738.8	727.6	708.2	684.7	663.3	641.8	635.7	630.6	624.5	622.5	621.4
35°	692.9	677.6	665.3	638.8	629.6	611.2	604.1	600.0	591.8	589.8	587.8
37.5°	648.0	633.7	620.4	604.1	586.7	576.5	572.5	566.3	562.2	563.3	561.2
40°	603.1	591.8	581.6	564.3	554.1	549.0	540.8	534.7	532.7	533.7	532.7
42.5°	559.2	549.0	542.9	529.6	519.4	514.3	509.2	503.1	506.1	506.1	509.2
45°	519.4	510.2	506.1	495.9	489.8	481.6	476.5	475.5	479.6	478.6	478.6
47.5°	478.6	475.5	470.4	461.2	453.1	448.0	446.9	446.9	451.0	453.1	452.0
50°	446.9	440.8	434.7	427.6	421.4	419.4	416.3	418.4	422.5	422.5	424.5
52.5°	407.1	403.1	401.0	394.9	390.8	390.8	390.8	391.8	394.9	398.0	396.9
55°	372.5	369.4	367.3	364.3	359.2	360.2	359.2	361.2	364.3	367.3	369.4
57.5°	335.7	334.7	332.7	327.6	327.6	326.5	329.6	330.6	335.7	337.8	340.8
60°	303.1	300.0	300.0	295.9	295.9	295.9	299.0	302.0	306.1	307.1	309.2
62.5°	268.4	268.4	267.3	264.3	264.3	267.3	268.4	272.5	274.5	274.5	277.6
65°	235.7	234.7	233.7	234.7	235.7	235.7	238.8	240.8	242.9	243.9	244.9
67.5°	203.1	202.0	204.1	203.1	205.1	209.2	208.2	211.2	214.3	214.3	215.3
70°	172.5	174.5	173.5	175.5	174.5	176.5	179.6	180.6	180.6	181.6	184.7
72.5°	143.9	143.9	143.9	142.9	143.9	145.9	148.0	149.0	151.0	152.0	155.1
75°	116.3	116.3	114.3	116.3	116.3	118.4	120.4	120.4	120.4	122.4	125.5
77.5°	87.8	88.8	87.8	89.8	89.8	90.8	92.9	91.8	93.9	94.9	95.9
80°	64.3	63.3	63.3	63.3	64.3	64.3	66.3	67.3	67.3	70.4	68.4
82.5°	40.8	41.8	40.8	41.8	41.8	42.9	41.8	42.9	43.9	45.9	44.9
85°	23.5	22.4	22.4	23.5	22.4	22.4	23.5	22.4	23.5	22.4	23.5
87.5°	9.2	8.2	8.2	8.2	8.2	7.1	7.1	6.1	6.1	6.1	5.1
90°	5.6	6.2	6.7	7.6	8.5	9.5	10.4	11.0	11.6	12.1	12.7
92.5°	11.1	10.9	11.1	11.4	11.8	12.1	12.5	12.7	12.9	13.2	13.4
95°	18.5	16.6	17.0	17.8	18.7	19.5	20.3	20.9	21.5	22.0	22.6
97.5°	22.9	18.2	19.1	21.0	22.8	24.7	26.5	26.9	27.2	27.6	27.9
100°	28.7	20.8	21.8	23.7	25.7	27.6	29.6	30.5	31.5	32.4	33.3
102.5°	125.4	125.3	114.8	93.8	72.7	51.7	30.7	32.0	33.2	34.5	35.8
105°	172.0	173.7	157.9	126.4	94.8	63.3	31.7	33.0	34.2	35.5	36.8
107.5°	206.6	208.0	188.5	149.6	110.7	71.7	32.8	34.1	35.3	36.6	37.9
110°	240.1	241.3	224.6	191.2	157.8	124.4	91.0	79.4	67.9	56.3	44.8

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	272.0	273.0	272.0	270.1	268.1	266.2	264.2	214.4	164.6	114.7	64.9
115°	306.8	307.8	309.2	312.1	315.0	317.9	320.8	267.3	213.8	160.3	106.8
117.5°	338.9	340.1	341.1	343.0	345.0	346.9	348.9	332.4	315.9	299.4	282.9
120°	370.9	371.8	372.8	374.9	377.0	379.0	381.1	382.5	383.9	385.3	386.7
122.5°	400.5	401.4	402.6	404.9	407.2	409.5	411.8	412.5	413.2	413.9	414.6
125°	428.7	429.5	430.6	432.8	435.0	437.2	439.4	440.2	441.0	441.8	442.6
127.5°	456.3	457.1	458.0	459.7	461.4	463.2	464.9	466.1	467.2	468.4	469.5
130°	482.7	483.6	484.2	485.5	486.8	488.0	489.3	490.6	491.8	493.1	494.4
132.5°	507.3	508.0	508.6	509.9	511.2	512.4	513.7	514.7	515.8	516.8	517.9
135°	530.5	531.4	531.9	533.0	534.0	535.1	536.1	537.3	538.4	539.6	540.7
137.5°	551.5	552.2	552.8	553.9	555.1	556.2	557.4	558.6	559.7	560.9	562.0
140°	572.0	572.5	573.1	574.4	575.7	576.9	578.2	579.2	580.3	581.3	582.4
142.5°	590.3	590.7	591.5	593.0	594.5	596.0	597.5	598.4	599.3	600.2	601.1
145°	606.4	606.3	607.3	609.2	611.2	613.1	615.1	615.9	616.7	617.6	618.4
147.5°	622.6	622.4	623.4	625.4	627.3	629.3	631.3	631.9	632.5	633.0	633.6
150°	637.4	637.0	637.9	639.8	641.6	643.5	645.3	646.0	646.7	647.4	648.1
152.5°	651.0	650.5	651.4	653.1	654.8	656.6	658.3	659.0	659.7	660.4	661.1
155°	664.0	663.5	664.2	665.6	666.9	668.3	669.7	670.4	671.1	671.8	672.5
157.5°	675.4	674.9	675.4	676.5	677.5	678.6	679.6	680.4	681.2	682.1	682.9
160°	685.7	685.3	685.7	686.4	687.1	687.8	688.5	689.2	689.9	690.6	691.3
162.5°	694.0	693.7	694.0	694.6	695.1	695.7	696.3	697.1	697.9	698.7	699.5
165°	701.3	700.9	701.1	701.4	701.8	702.1	702.5	703.3	704.1	704.9	705.7
167.5°	707.0	706.7	706.9	707.2	707.5	707.9	708.2	709.0	709.8	710.7	711.5
170°	711.7	711.3	711.4	711.7	711.9	712.2	712.4	713.2	714.0	714.8	715.6
172.5°	714.8	714.5	714.6	714.8	715.1	715.3	715.5	716.3	717.1	717.9	718.7
175°	716.9	716.5	716.6	716.9	717.1	717.4	717.6	718.4	719.2	720.0	720.8
177.5°	718.0	717.6	717.7	717.8	717.9	718.0	718.1	718.9	719.7	720.5	721.3
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1265.3	1268.4	1261.2	1259.2	1261.2	1254.1	1256.1	1258.2	1258.2	1261.2	1263.3
5°	1191.8	1187.8	1180.6	1178.6	1176.5	1179.6	1177.6	1180.6	1181.6	1188.8	1189.8
7.5°	1119.4	1113.3	1107.1	1101.0	1099.0	1093.9	1099.0	1099.0	1106.1	1104.1	1109.2
10°	1033.7	1032.7	1024.5	1021.4	1017.4	1009.2	1020.4	1017.4	1022.5	1031.6	1033.7
12.5°	970.4	959.2	964.3	950.0	955.1	946.9	948.0	948.0	956.1	957.1	955.1
15°	910.2	901.0	887.8	881.6	878.6	874.5	887.8	888.8	882.7	896.9	891.8
17.5°	849.0	849.0	836.7	833.7	825.5	829.6	827.6	828.6	826.5	836.7	841.8
20°	795.9	790.8	786.7	787.8	777.6	775.5	773.5	775.5	782.7	789.8	791.8
22.5°	753.1	750.0	739.8	741.8	733.7	736.7	734.7	739.8	740.8	740.8	748.0
25°	712.2	708.2	709.2	705.1	702.0	702.0	699.0	702.0	706.1	708.2	709.2
27.5°	681.6	678.6	673.5	670.4	672.5	667.4	671.4	674.5	674.5	672.5	674.5
30°	644.9	646.9	646.9	636.7	640.8	638.8	641.8	643.9	643.9	644.9	642.9
32.5°	620.4	614.3	613.3	612.2	612.2	608.2	608.2	611.2	612.2	613.3	616.3
35°	587.8	587.8	582.7	585.7	581.6	582.7	581.6	582.7	584.7	581.6	584.7
37.5°	558.2	559.2	557.1	559.2	560.2	558.2	556.1	560.2	558.2	558.2	556.1
40°	532.7	531.6	532.7	532.7	532.7	533.7	531.6	531.6	531.6	529.6	527.6
42.5°	511.2	505.1	507.1	508.2	505.1	505.1	506.1	505.1	508.2	502.0	502.0
45°	480.6	478.6	479.6	479.6	481.6	478.6	480.6	481.6	478.6	477.6	475.5
47.5°	453.1	455.1	453.1	455.1	455.1	457.1	453.1	454.1	455.1	451.0	448.0
50°	425.5	425.5	428.6	427.6	428.6	426.5	426.5	425.5	426.5	424.5	421.4
52.5°	400.0	396.9	402.0	401.0	400.0	399.0	398.0	399.0	396.9	394.9	394.9
55°	368.4	368.4	371.4	372.5	372.5	370.4	368.4	369.4	368.4	367.3	366.3
57.5°	342.9	338.8	340.8	341.8	341.8	338.8	340.8	338.8	338.8	339.8	336.7
60°	310.2	310.2	308.2	311.2	311.2	309.2	309.2	310.2	308.2	307.1	306.1
62.5°	275.5	276.5	279.6	280.6	281.6	279.6	277.6	278.6	278.6	275.5	276.5
65°	245.9	248.0	252.0	251.0	249.0	250.0	248.0	249.0	245.9	246.9	243.9
67.5°	217.3	216.3	217.3	217.3	219.4	218.4	216.3	216.3	215.3	218.4	215.3
70°	186.7	186.7	186.7	186.7	187.8	188.8	186.7	184.7	185.7	183.7	182.7
72.5°	155.1	156.1	155.1	157.1	154.1	156.1	156.1	155.1	154.1	154.1	154.1
75°	125.5	127.6	124.5	125.5	124.5	126.5	125.5	125.5	123.5	122.4	123.5
77.5°	95.9	96.9	94.9	95.9	94.9	95.9	95.9	94.9	94.9	94.9	94.9
80°	68.4	69.4	68.4	67.3	66.3	68.4	66.3	67.3	68.4	67.3	69.4
82.5°	43.9	43.9	42.9	43.9	41.8	41.8	42.9	42.9	41.8	43.9	41.8
85°	21.4	21.4	23.5	21.4	20.4	20.4	20.4	21.4	20.4	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	13.0	13.1	13.3	13.6	13.8	14.0	13.8	13.6	13.3	13.1	13.0
92.5°	13.5	13.6	13.7	13.8	13.9	14.0	13.9	13.8	13.7	13.6	13.5
95°	22.9	22.8	22.7	22.6	22.5	22.4	22.5	22.6	22.7	22.8	22.9
97.5°	28.1	28.2	28.3	28.4	28.5	28.6	28.5	28.4	28.3	28.2	28.1
100°	33.8	33.9	34.1	34.4	34.6	34.8	34.6	34.4	34.1	33.9	33.8
102.5°	36.4	36.6	36.9	37.3	37.6	38.0	37.6	37.3	36.9	36.6	36.4
105°	37.4	37.6	38.1	38.6	39.0	39.5	39.0	38.6	38.1	37.6	37.4
107.5°	38.5	38.7	39.2	39.7	40.1	40.6	40.1	39.7	39.2	38.7	38.5
110°	39.0	39.2	39.7	40.2	40.6	41.1	40.6	40.2	39.7	39.2	39.0

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	40.0	40.2	40.5	40.9	41.2	41.6	41.2	40.9	40.5	40.2	40.0
115°	80.1	75.9	67.6	59.3	50.9	42.6	50.9	59.3	67.6	75.9	80.1
117.5°	274.6	259.5	229.2	198.9	168.6	138.3	168.6	198.9	229.2	259.5	274.6
120°	387.4	379.6	364.0	348.4	332.8	317.2	332.8	348.4	364.0	379.6	387.4
122.5°	414.9	415.0	415.1	415.2	415.4	415.5	415.4	415.2	415.1	415.0	414.9
125°	443.0	443.2	443.5	443.9	444.2	444.6	444.2	443.9	443.5	443.2	443.0
127.5°	470.1	470.2	470.3	470.4	470.5	470.6	470.5	470.4	470.3	470.2	470.1
130°	495.0	494.9	494.8	494.7	494.6	494.5	494.6	494.7	494.8	494.9	495.0
132.5°	518.4	518.3	518.2	518.1	518.0	517.9	518.0	518.1	518.2	518.3	518.4
135°	541.3	541.2	541.0	540.7	540.5	540.3	540.5	540.7	541.0	541.2	541.3
137.5°	562.6	562.4	562.1	561.8	561.4	561.1	561.4	561.8	562.1	562.4	562.6
140°	582.9	582.6	582.0	581.5	580.9	580.3	580.9	581.5	582.0	582.6	582.9
142.5°	601.6	601.3	600.7	600.2	599.6	599.0	599.6	600.2	600.7	601.3	601.6
145°	618.8	618.5	617.9	617.4	616.8	616.2	616.8	617.4	617.9	618.5	618.8
147.5°	633.9	633.7	633.2	632.7	632.3	631.8	632.3	632.7	633.2	633.7	633.9
150°	648.4	648.1	647.5	647.0	646.4	645.8	646.4	647.0	647.5	648.1	648.4
152.5°	661.4	661.0	660.2	659.4	658.6	657.8	658.6	659.4	660.2	661.0	661.4
155°	672.9	672.4	671.5	670.6	669.6	668.7	669.6	670.6	671.5	672.4	672.9
157.5°	683.3	682.8	681.9	681.0	680.0	679.1	680.0	681.0	681.9	682.8	683.3
160°	691.6	691.2	690.4	689.5	688.7	687.9	688.7	689.5	690.4	691.2	691.6
162.5°	699.9	699.4	698.3	697.3	696.2	695.2	696.2	697.3	698.3	699.4	699.9
165°	706.1	705.7	704.9	704.1	703.3	702.5	703.3	704.1	704.9	705.7	706.1
167.5°	711.9	711.4	710.3	709.3	708.2	707.2	708.2	709.3	710.3	711.4	711.9
170°	716.0	715.5	714.4	713.4	712.3	711.3	712.3	713.4	714.4	715.5	716.0
172.5°	719.1	718.6	717.6	716.5	715.5	714.5	715.5	716.5	717.6	718.6	719.1
175°	721.2	720.6	719.5	718.3	717.2	716.0	717.2	718.3	719.5	720.6	721.2
177.5°	721.7	721.2	720.2	719.1	718.1	717.1	718.1	719.1	720.2	721.2	721.7
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6	1327.6
2.5°	1260.2	1268.4	1265.3	1254.1	1267.4	1267.4	1276.5	1276.5	1287.8	1291.8	1298.0
5°	1188.8	1194.9	1200.0	1194.9	1204.1	1218.4	1226.5	1233.7	1249.0	1255.1	1264.3
7.5°	1112.3	1123.5	1128.6	1128.6	1143.9	1160.2	1176.5	1186.7	1208.2	1216.3	1225.5
10°	1037.8	1051.0	1061.2	1060.2	1085.7	1095.9	1116.3	1139.8	1161.2	1173.5	1186.7
12.5°	959.2	966.3	980.6	1001.0	1007.1	1025.5	1049.0	1078.6	1117.4	1128.6	1148.0
15°	893.9	913.3	924.5	933.7	948.0	965.3	990.8	1019.4	1058.2	1082.7	1103.1
17.5°	838.8	864.3	871.4	869.4	887.8	914.3	943.9	965.3	1000.0	1029.6	1049.0
20°	793.9	804.1	816.3	821.4	835.7	864.3	892.9	917.4	945.9	969.4	991.8
22.5°	749.0	757.1	767.4	776.5	787.8	804.1	831.6	862.3	889.8	912.3	937.8
25°	712.2	717.4	726.5	733.7	745.9	757.1	776.5	810.2	842.9	856.1	878.6
27.5°	676.5	680.6	686.7	694.9	701.0	712.2	729.6	757.1	790.8	804.1	834.7
30°	644.9	648.0	654.1	658.2	661.2	674.5	687.8	709.2	734.7	753.1	775.5
32.5°	615.3	618.4	624.5	625.5	629.6	636.7	649.0	668.4	690.8	706.1	725.5
35°	582.7	584.7	590.8	592.9	595.9	602.0	611.2	625.5	645.9	657.1	674.5
37.5°	557.1	556.1	560.2	563.3	567.4	570.4	573.5	587.8	603.1	613.3	626.5
40°	529.6	527.6	528.6	532.7	534.7	538.8	538.8	553.1	563.3	571.4	581.6
42.5°	502.0	501.0	499.0	501.0	503.1	504.1	505.1	515.3	525.5	532.7	543.9
45°	474.5	473.5	471.4	472.5	472.5	474.5	477.6	481.6	488.8	494.9	501.0
47.5°	449.0	446.9	443.9	442.9	444.9	444.9	444.9	449.0	456.1	458.2	464.3
50°	422.5	419.4	415.3	413.3	413.3	412.2	414.3	415.3	421.4	423.5	428.6
52.5°	393.9	391.8	387.8	383.7	384.7	382.7	383.7	384.7	386.7	389.8	392.9
55°	365.3	361.2	358.2	357.1	354.1	354.1	351.0	355.1	354.1	355.1	359.2
57.5°	337.8	333.7	328.6	326.5	323.5	322.5	320.4	319.4	320.4	323.5	326.5
60°	305.1	303.1	300.0	296.9	294.9	291.8	289.8	289.8	288.8	288.8	289.8
62.5°	273.5	272.5	268.4	267.3	265.3	263.3	260.2	258.2	258.2	260.2	261.2
65°	242.9	241.8	238.8	237.8	232.7	230.6	229.6	228.6	226.5	226.5	226.5
67.5°	214.3	211.2	211.2	206.1	202.0	200.0	198.0	196.9	196.9	196.9	198.0
70°	182.7	182.7	179.6	176.5	172.5	173.5	170.4	167.3	167.3	165.3	166.3
72.5°	152.0	151.0	148.0	146.9	143.9	140.8	138.8	140.8	137.8	136.7	137.8
75°	122.4	121.4	119.4	117.3	118.4	115.3	112.2	111.2	111.2	109.2	109.2
77.5°	93.9	95.9	91.8	90.8	88.8	86.7	85.7	84.7	84.7	84.7	86.7
80°	65.3	66.3	66.3	64.3	65.3	62.2	62.2	62.2	59.2	60.2	61.2
82.5°	41.8	41.8	40.8	41.8	40.8	40.8	39.8	39.8	38.8	38.8	39.8
85°	23.5	22.4	21.4	23.5	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.2	8.2	8.2
90°	12.7	12.1	11.6	11.0	10.4	9.5	8.5	7.6	6.7	6.2	5.6
92.5°	13.4	13.2	12.9	12.7	12.5	12.1	11.8	11.4	11.1	10.9	11.1
95°	22.6	22.0	21.5	20.9	20.3	19.5	18.7	17.8	17.0	16.6	18.5
97.5°	27.9	27.6	27.2	26.9	26.5	24.7	22.8	21.0	19.1	18.2	22.9
100°	33.3	32.4	31.5	30.5	29.6	27.6	25.7	23.7	21.8	20.8	28.7
102.5°	35.8	34.5	33.2	32.0	30.7	51.7	72.7	93.8	114.8	125.3	125.4
105°	36.8	35.5	34.2	33.0	31.7	63.3	94.8	126.4	157.9	173.7	172.0
107.5°	37.9	36.6	35.3	34.1	32.8	71.7	110.7	149.6	188.5	208.0	206.6
110°	44.8	56.3	67.9	79.4	91.0	124.4	157.8	191.2	224.6	241.3	240.1

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	64.9	114.7	164.6	214.4	264.2	266.2	268.1	270.1	272.0	273.0	272.0
115°	106.8	160.3	213.8	267.3	320.8	317.9	315.0	312.1	309.2	307.8	306.8
117.5°	282.9	299.4	315.9	332.4	348.9	346.9	345.0	343.0	341.1	340.1	338.9
120°	386.7	385.3	383.9	382.5	381.1	379.0	377.0	374.9	372.8	371.8	370.9
122.5°	414.6	413.9	413.2	412.5	411.8	409.5	407.2	404.9	402.6	401.4	400.5
125°	442.6	441.8	441.0	440.2	439.4	437.2	435.0	432.8	430.6	429.5	428.7
127.5°	469.5	468.4	467.2	466.1	464.9	463.2	461.4	459.7	458.0	457.1	456.3
130°	494.4	493.1	491.8	490.6	489.3	488.0	486.8	485.5	484.2	483.6	482.7
132.5°	517.9	516.8	515.8	514.7	513.7	512.4	511.2	509.9	508.6	508.0	507.3
135°	540.7	539.6	538.4	537.3	536.1	535.1	534.0	533.0	531.9	531.4	530.5
137.5°	562.0	560.9	559.7	558.6	557.4	556.2	555.1	553.9	552.8	552.2	551.5
140°	582.4	581.3	580.3	579.2	578.2	576.9	575.7	574.4	573.1	572.5	572.0
142.5°	601.1	600.2	599.3	598.4	597.5	596.0	594.5	593.0	591.5	590.7	590.3
145°	618.4	617.6	616.7	615.9	615.1	613.1	611.2	609.2	607.3	606.3	606.4
147.5°	633.6	633.0	632.5	631.9	631.3	629.3	627.3	625.4	623.4	622.4	622.6
150°	648.1	647.4	646.7	646.0	645.3	643.5	641.6	639.8	637.9	637.0	637.4
152.5°	661.1	660.4	659.7	659.0	658.3	656.6	654.8	653.1	651.4	650.5	651.0
155°	672.5	671.8	671.1	670.4	669.7	668.3	666.9	665.6	664.2	663.5	664.0
157.5°	682.9	682.1	681.2	680.4	679.6	678.6	677.5	676.5	675.4	674.9	675.4
160°	691.3	690.6	689.9	689.2	688.5	687.8	687.1	686.4	685.7	685.3	685.7
162.5°	699.5	698.7	697.9	697.1	696.3	695.7	695.1	694.6	694.0	693.7	694.0
165°	705.7	704.9	704.1	703.3	702.5	702.1	701.8	701.4	701.1	700.9	701.3
167.5°	711.5	710.7	709.8	709.0	708.2	707.9	707.5	707.2	706.9	706.7	707.0
170°	715.6	714.8	714.0	713.2	712.4	712.2	711.9	711.7	711.4	711.3	711.7
172.5°	718.7	717.9	717.1	716.3	715.5	715.3	715.1	714.8	714.6	714.5	714.8
175°	720.8	720.0	719.2	718.4	717.6	717.4	717.1	716.9	716.6	716.5	716.9
177.5°	721.3	720.5	719.7	718.9	718.1	718.0	717.9	717.8	717.7	717.6	718.0
180°	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1327.6	1327.6	1327.6	1327.6
2.5°	1303.1	1303.1	1318.4	1334.7
5°	1274.5	1281.6	1306.1	1328.6
7.5°	1246.9	1259.2	1289.8	1318.4
10°	1213.3	1229.6	1267.4	1301.0
12.5°	1180.6	1195.9	1239.8	1277.6
15°	1134.7	1154.1	1201.0	1248.0
17.5°	1088.8	1108.2	1165.3	1220.4
20°	1034.7	1060.2	1124.5	1198.0
22.5°	984.7	1016.3	1087.8	1146.9
25°	929.6	978.6	1044.9	1121.4
27.5°	880.6	929.6	996.9	1074.5
30°	825.5	875.5	944.9	1016.3
32.5°	772.5	818.4	885.7	973.5
35°	717.4	761.2	826.5	915.3
37.5°	667.4	710.2	781.6	863.3
40°	618.4	663.3	724.5	806.1
42.5°	572.5	612.2	667.4	749.0
45°	530.6	559.2	610.2	686.7
47.5°	486.7	512.2	559.2	635.7
50°	445.9	467.3	508.2	579.6
52.5°	406.1	424.5	462.2	519.4
55°	370.4	387.8	415.3	471.4
57.5°	333.7	346.9	373.5	418.4
60°	298.0	310.2	331.6	368.4
62.5°	262.2	272.5	292.9	322.5
65°	230.6	238.8	254.1	279.6
67.5°	200.0	205.1	217.3	237.8
70°	170.4	174.5	184.7	201.0
72.5°	138.8	142.9	154.1	165.3
75°	112.2	113.3	121.4	130.6
77.5°	87.8	86.7	92.9	100.0
80°	60.2	63.3	68.4	71.4
82.5°	40.8	41.8	43.9	45.9
85°	22.4	23.5	23.5	26.5
87.5°	9.2	10.2	10.2	11.2
90°	4.3	3.0	1.8	0.5
92.5°	11.6	12.1	12.5	13.0
95°	22.3	26.2	30.0	33.8
97.5°	32.4	41.9	51.3	60.8
100°	44.5	60.4	76.2	92.0
102.5°	125.7	125.9	126.2	126.4
105°	168.5	165.0	161.6	158.1
107.5°	203.7	200.8	197.9	195.0
110°	237.7	235.2	232.8	230.4



TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	269.9	267.8	265.7	263.6
115°	304.9	302.9	301.0	299.0
117.5°	336.6	334.3	332.0	329.7
120°	369.2	367.5	365.7	364.0
122.5°	398.6	396.8	394.9	393.1
125°	427.2	425.7	424.2	422.7
127.5°	454.7	453.0	451.4	449.8
130°	480.8	479.0	477.1	475.3
132.5°	505.8	504.3	502.8	501.3
135°	528.6	526.8	524.9	523.1
137.5°	550.1	548.8	547.4	546.0
140°	571.1	570.2	569.2	568.3
142.5°	589.5	588.7	587.9	587.1
145°	606.5	606.6	606.7	606.8
147.5°	622.9	623.3	623.6	624.0
150°	638.2	639.0	639.8	640.6
152.5°	651.9	652.8	653.8	654.7
155°	665.1	666.1	667.2	668.2
157.5°	676.3	677.2	678.2	679.1
160°	686.4	687.1	687.8	688.5
162.5°	694.7	695.4	696.1	696.8
165°	702.0	702.7	703.4	704.1
167.5°	707.7	708.4	709.1	709.8
170°	712.4	713.1	713.8	714.5
172.5°	715.5	716.2	716.9	717.6
175°	717.7	718.6	719.4	720.2
177.5°	718.8	719.6	720.4	721.2
180°	718.6	718.6	718.6	718.6

TEST NUMBER: P998804

CATALOG NUMBER: SA2XXDIP-B675D530UB2750-4F0-XX-W2A-A_4000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.16	18.05	18.05	18.96	20.11	14.65	15.55	15.54	16.45	17.61
	3H	17.97	18.77	18.87	19.69	20.87	16.00	16.80	16.90	17.72	18.89
	4H	18.14	18.90	19.06	19.82	21.01	16.46	17.22	17.38	18.14	19.33
	6H	18.19	18.89	19.12	19.81	21.01	16.77	17.47	17.70	18.40	19.60
	8H	18.17	18.83	19.11	19.78	20.98	16.85	17.52	17.79	18.46	19.66
	12H	18.13	18.76	19.07	19.70	20.93	16.90	17.53	17.84	18.47	19.69
4H	2H	17.20	17.96	18.13	18.88	20.07	15.10	15.86	16.02	16.78	17.97
	3H	18.19	18.82	19.12	19.77	20.97	16.56	17.20	17.50	18.15	19.35
	4H	18.46	19.04	19.41	19.99	21.21	17.10	17.68	18.04	18.62	19.85
	6H	18.60	19.09	19.55	20.06	21.29	17.48	17.98	18.44	18.95	20.17
	8H	18.60	19.06	19.55	20.02	21.26	17.59	18.06	18.55	19.02	20.26
	12H	18.56	18.98	19.54	19.96	21.20	17.65	18.07	18.63	19.05	20.29
8H	4H	18.48	18.94	19.44	19.90	21.14	17.24	17.71	18.20	18.67	19.91
	6H	18.66	19.04	19.64	20.04	21.28	17.68	18.06	18.67	19.07	20.31
	8H	18.69	19.02	19.68	20.02	21.28	17.83	18.17	18.83	19.16	20.42
	12H	18.67	18.97	19.67	19.96	21.26	17.93	18.22	18.92	19.21	20.51
12H	4H	18.43	18.85	19.41	19.83	21.08	17.22	17.64	18.20	18.62	19.86
	6H	18.63	18.97	19.63	19.97	21.22	17.68	18.02	18.67	19.01	20.27
	8H	18.67	18.97	19.67	19.95	21.26	17.84	18.14	18.84	19.12	20.43