

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999473

Luminaire Tested: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999473
REPORT IS A COMBINATION OF REPORTS P988024 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5360.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	100	100	100	100		89	89	89	89		67	67	67		47	47	47		29	29	29
1	91	87	84	81		81	77	75	72		59	57	55		42	41	40		26	25	25
2	83	77	71	66		74	68	63	59		52	49	46		37	35	34		23	22	21
3	76	68	61	56		67	60	55	50		46	42	39		33	31	29		21	20	19
4	70	60	53	47		62	53	47	43		41	37	34		30	27	25		19	18	16
5	64	53	46	40		57	48	41	37		37	32	29		27	24	22		17	16	14
6	59	48	40	35		52	43	36	32		33	29	25		24	21	19		16	14	13
7	55	43	36	31		48	39	32	28		30	26	22		22	19	17		14	13	12
8	51	39	32	27		45	35	29	25		27	23	20		20	17	15		13	12	10
9	47	36	29	24		42	32	26	22		25	21	18		18	16	14		12	11	10
10	44	33	26	21		39	29	23	19		23	19	16		17	14	12		11	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9984	9984	9984	9984
5°	10008	10604	10043	8472
10°	9898	11209	9968	6996
15°	9683	11212	9847	5256
20°	9425	9268	9629	4336
25°	9110	5791	9307	3688
30°	8712	3709	8948	3175
35°	8225	2850	8491	2718
40°	7683	2395	8011	2377
45°	7102	2038	7399	1996
50°	6509	1733	6813	1726
55°	5851	1506	6166	1486
60°	5268	1148	5547	1134
65°	4721	865	5002	980
70°	4119	690	4443	798
75°	3479	528	3798	605
80°	2762	359	2978	395
85°	1921	186	2105	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9134 cd/sqm

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	1.1
10°-20°	167.0	3.1
20°-30°	214.9	4.0
30°-40°	203.9	3.8
40°-50°	174.7	3.3
50°-60°	133.1	2.5
60°-70°	83.9	1.6
70°-80°	41.9	0.8
80°-90°	13.3	0.2
90°-100°	48.0	0.9
100°-110°	178.9	3.3
110°-120°	474.6	8.9
120°-130°	787.1	14.7
130°-140°	836.1	15.6
140°-150°	777.0	14.5
150°-160°	624.7	11.7
160°-170°	402.5	7.5
170°-180°	138.5	2.6
0°-30°	441.7	8.2
0°-40°	645.6	12.0
0°-60°	953.4	17.8
0°-90°	1092.6	20.4
90°-120°	701.5	13.1
90°-150°	3101.6	57.9
90°-180°	4267.0	79.6
0°-180°	5360.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	631	631	631	631	631	
5°	631	702	633	561	631	60
15°	595	792	605	371	595	167
25°	528	422	539	269	528	242
35°	433	208	447	199	433	271
45°	325	145	339	142	325	251
55°	220	100	231	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	67
85°	14	8	15	8	14	15
90°	1	28	1	28	1	5
95°	68	45	68	45	68	81
105°	320	80	320	80	320	342
115°	606	86	606	86	606	596
125°	856	901	856	901	856	764
135°	1060	1094	1060	1094	1060	819
145°	1229	1248	1229	1248	1229	769
155°	1354	1354	1354	1354	1354	624
165°	1426	1423	1426	1423	1426	403
175°	1459	1450	1459	1450	1459	139
180°	1456	1456	1456	1456	1456	

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	634.7	637.3	638.6	640.4	644.3	647.0	650.9	651.8	651.3	653.1	648.3
5°	631.2	636.9	642.1	646.5	653.5	657.9	662.7	668.4	669.8	676.3	672.4
7.5°	626.4	634.7	642.1	650.9	661.4	667.1	674.6	683.3	687.3	695.2	697.4
10°	618.5	630.3	643.0	652.2	666.7	676.8	683.8	697.8	707.0	718.8	717.1
12.5°	605.8	621.1	638.2	653.5	672.4	679.0	692.1	706.6	718.4	729.4	739.0
15°	594.8	612.3	631.2	650.0	671.5	683.8	696.9	715.8	728.5	747.8	756.1
17.5°	579.9	602.3	624.6	645.6	671.1	685.1	701.3	719.7	738.6	757.0	763.6
20°	564.6	588.7	612.8	641.3	670.2	683.8	700.4	723.2	741.6	756.1	756.1
22.5°	546.1	575.5	603.1	630.3	661.9	681.6	698.7	725.4	738.6	741.6	729.8
25°	527.7	557.1	587.3	621.1	657.0	674.6	693.9	718.8	723.2	711.0	680.3
27.5°	505.8	538.7	572.9	609.3	647.0	668.9	686.4	703.1	694.7	661.9	614.1
30°	483.5	519.0	557.5	592.2	637.8	657.9	672.8	677.6	651.3	597.9	536.1
32.5°	460.2	494.9	535.6	577.3	623.3	642.6	652.2	639.5	591.3	523.8	448.4
35°	433.1	472.1	514.6	558.0	603.6	618.0	623.7	592.6	530.8	443.6	368.6
37.5°	408.5	447.5	493.1	537.4	581.6	589.5	583.8	535.2	456.7	370.4	297.2
40°	379.6	421.2	465.9	515.5	551.8	554.0	540.0	476.9	379.6	298.5	253.3
42.5°	352.8	394.9	439.6	490.0	517.7	510.2	491.4	408.5	316.9	257.3	220.9
45°	325.2	365.1	413.3	458.0	477.8	460.2	431.7	343.6	266.1	221.4	193.3
47.5°	298.5	335.8	383.5	426.5	430.0	410.3	376.5	288.0	230.6	194.6	171.8
50°	272.2	309.5	354.2	389.7	386.2	359.0	320.8	250.3	200.3	171.8	153.0
52.5°	245.9	279.6	323.0	351.1	336.2	309.9	272.2	212.1	174.9	149.9	135.4
55°	219.6	251.2	288.4	311.6	288.0	257.7	231.0	181.9	151.7	131.5	120.5
57.5°	197.7	222.7	256.9	270.9	242.4	218.7	195.5	156.5	131.5	117.0	104.3
60°	173.6	196.4	224.4	232.7	203.4	184.1	164.4	132.4	112.6	99.9	91.6
62.5°	153.0	171.8	193.3	193.3	167.4	153.0	138.1	110.9	94.7	84.6	80.7
65°	132.8	146.4	161.7	160.0	138.1	125.4	113.5	91.6	79.3	72.3	68.4
67.5°	113.1	123.6	133.7	127.6	111.8	100.8	89.9	74.1	65.7	60.9	55.7
70°	95.1	103.4	108.7	103.0	87.2	78.0	70.1	59.6	53.0	46.9	43.8
72.5°	79.8	83.3	85.0	78.0	64.9	59.6	53.9	46.5	40.8	37.7	36.8
75°	62.2	65.3	64.0	58.7	47.8	43.8	39.4	34.2	32.9	31.1	30.2
77.5°	48.7	48.7	46.5	41.6	34.2	31.1	29.4	26.7	25.4	25.0	24.1
80°	34.6	34.2	32.9	27.6	23.2	21.5	21.5	19.7	19.3	18.4	18.4
82.5°	22.8	22.8	21.0	16.7	15.3	14.9	14.5	13.6	13.6	13.1	13.1
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.3	7.9	8.3	7.9	7.9
87.5°	6.1	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	1.1	3.7	6.2	8.8	11.3	12.6	13.5	15.4	17.3	19.2	21.1
92.5°	26.3	25.4	24.4	23.5	22.6	22.1	22.5	23.2	23.9	24.6	25.3
95°	68.5	60.8	53.0	45.3	37.6	33.7	34.5	36.2	37.8	39.5	41.1
97.5°	123.2	104.0	84.8	65.7	46.5	36.9	38.8	42.5	46.2	50.0	53.7
100°	186.4	154.3	122.3	90.2	58.1	42.1	44.1	48.1	52.0	56.0	60.0
102.5°	255.9	255.4	255.0	254.5	254.0	253.8	232.5	189.9	147.3	104.7	62.1
105°	320.2	327.2	334.2	341.3	348.3	351.8	319.9	256.0	192.1	128.2	64.3
107.5°	395.0	400.8	406.7	412.5	418.4	421.3	381.9	303.0	224.1	145.3	66.4
110°	466.6	471.5	476.4	481.3	486.2	488.7	454.9	387.2	319.6	251.9	184.3

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	534.0	538.2	542.4	546.7	550.9	553.0	551.0	547.0	543.1	539.1	535.1
115°	605.6	609.6	613.6	617.5	621.5	623.5	626.4	632.3	638.2	644.0	649.9
117.5°	667.8	672.5	677.2	681.9	686.6	688.9	690.9	694.9	698.8	702.8	706.8
120°	737.3	740.8	744.3	747.8	751.3	753.1	755.2	759.4	763.7	767.9	772.1
122.5°	796.3	800.0	803.8	807.5	811.2	813.1	815.4	820.1	824.8	829.5	834.2
125°	856.3	859.3	862.4	865.4	868.5	870.0	872.2	876.7	881.1	885.6	890.0
127.5°	911.1	914.4	917.6	920.9	924.2	925.8	927.6	931.1	934.6	938.1	941.6
130°	962.7	966.5	970.2	974.0	977.7	979.6	980.9	983.4	986.0	988.5	991.1
132.5°	1015.4	1018.4	1021.5	1024.5	1027.6	1029.1	1030.4	1032.9	1035.5	1038.0	1040.6
135°	1059.6	1063.4	1067.1	1070.9	1074.6	1076.5	1077.5	1079.6	1081.7	1083.8	1085.9
137.5°	1106.0	1108.8	1111.6	1114.4	1117.2	1118.6	1119.8	1122.1	1124.4	1126.8	1129.1
140°	1151.2	1153.1	1155.0	1156.9	1158.8	1159.7	1161.0	1163.6	1166.1	1168.7	1171.3
142.5°	1189.2	1190.8	1192.4	1194.1	1195.7	1196.5	1198.0	1201.1	1204.1	1207.2	1210.2
145°	1229.2	1229.0	1228.7	1228.5	1228.2	1228.1	1230.1	1234.1	1238.0	1242.0	1246.0
147.5°	1263.9	1263.2	1262.5	1261.8	1261.1	1260.8	1262.8	1266.8	1270.7	1274.7	1278.7
150°	1297.7	1296.1	1294.4	1292.8	1291.1	1290.3	1292.2	1295.9	1299.6	1303.4	1307.1
152.5°	1326.1	1324.2	1322.4	1320.5	1318.6	1317.7	1319.5	1323.0	1326.5	1330.0	1333.5
155°	1353.5	1351.4	1349.3	1347.2	1345.1	1344.0	1345.4	1348.2	1351.0	1353.8	1356.6
157.5°	1375.6	1373.7	1371.9	1370.0	1368.1	1367.2	1368.2	1370.3	1372.4	1374.5	1376.6
160°	1394.6	1393.2	1391.8	1390.3	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6
162.5°	1411.4	1410.0	1408.6	1407.2	1405.8	1405.1	1405.7	1406.9	1408.0	1409.2	1410.4
165°	1426.2	1424.8	1423.4	1421.9	1420.5	1419.8	1420.2	1420.9	1421.6	1422.3	1423.0
167.5°	1437.7	1436.3	1434.9	1433.5	1432.1	1431.4	1431.8	1432.5	1433.2	1433.9	1434.6
170°	1447.2	1445.8	1444.4	1443.0	1441.6	1440.9	1441.1	1441.6	1442.1	1442.5	1443.0
172.5°	1453.5	1452.1	1450.7	1449.3	1447.9	1447.2	1447.4	1447.9	1448.4	1448.8	1449.3
175°	1458.8	1457.2	1455.5	1453.9	1452.2	1451.4	1451.6	1452.1	1452.6	1453.0	1453.5
177.5°	1460.9	1459.3	1457.6	1456.0	1454.3	1453.5	1453.6	1453.9	1454.1	1454.4	1454.6
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	653.1	654.0	655.3	661.4	662.3	664.1	663.2	663.2	663.6	662.7	663.2
5°	681.1	682.5	689.0	696.5	698.2	696.5	698.7	701.7	701.7	701.7	700.9
7.5°	707.4	712.3	719.7	730.7	732.9	735.1	739.0	736.4	737.3	741.2	739.9
10°	732.9	739.9	748.2	757.4	762.2	765.3	767.1	771.0	780.2	769.7	773.6
12.5°	757.0	767.1	775.8	785.9	789.4	793.4	794.7	798.2	798.2	797.7	800.8
15°	772.8	782.0	789.9	796.4	797.3	796.4	795.5	796.0	797.3	792.0	795.1
17.5°	776.3	777.1	779.8	777.1	777.6	768.4	763.1	761.8	749.5	750.0	760.0
20°	759.2	744.3	740.3	725.9	717.1	693.4	692.5	686.0	660.1	668.0	666.2
22.5°	712.3	686.8	653.1	636.4	628.1	603.1	583.8	570.3	561.0	551.8	547.9
25°	650.5	609.3	561.5	528.6	523.8	500.6	465.1	448.4	428.7	422.5	433.1
27.5°	570.7	517.2	463.3	412.9	403.7	382.7	364.7	352.8	330.1	328.7	329.6
30°	462.4	408.5	363.4	330.5	307.7	298.1	286.2	277.5	268.3	271.8	272.6
32.5°	380.0	328.7	286.7	269.1	258.6	252.5	242.4	236.7	232.7	231.4	231.0
35°	302.0	267.8	249.0	231.9	225.7	221.4	213.9	211.3	207.8	208.2	208.2
37.5°	258.6	230.1	216.1	207.3	201.6	199.4	194.6	192.0	189.8	188.9	190.2
40°	223.1	203.4	194.6	186.7	181.9	181.0	178.4	175.3	172.7	173.1	174.5
42.5°	197.2	185.8	175.3	169.2	165.7	164.4	162.2	160.0	160.0	158.7	158.2
45°	176.6	167.4	158.7	153.0	150.8	149.0	146.4	146.0	144.2	144.6	145.1
47.5°	158.2	150.8	144.2	138.5	136.3	135.9	133.2	131.5	131.5	131.1	130.6
50°	141.6	134.1	128.4	125.4	122.3	121.4	121.0	120.5	119.7	119.7	120.1
52.5°	128.0	120.5	116.2	113.5	111.8	110.9	110.9	110.5	110.5	110.5	110.0
55°	113.1	106.9	103.4	102.6	101.7	101.3	100.8	99.9	99.5	100.4	99.5
57.5°	99.1	96.9	93.8	92.9	90.7	90.7	89.4	88.5	87.7	88.5	88.5
60°	88.1	85.0	83.3	80.7	78.9	77.1	75.0	74.5	73.6	73.2	72.8
62.5°	76.7	74.1	69.7	65.7	63.1	61.4	60.5	60.0	60.0	59.6	59.6
65°	64.0	57.9	55.7	54.4	53.9	53.5	52.6	52.2	52.6	52.2	52.6
67.5°	50.0	49.1	47.8	46.9	46.5	46.0	46.0	45.6	45.6	45.6	45.6
70°	43.4	41.2	40.8	39.9	39.9	39.4	39.4	39.4	39.4	39.0	39.9
72.5°	35.9	34.6	34.2	33.8	33.8	33.8	33.3	33.3	33.3	32.9	33.3
75°	29.4	28.9	28.1	28.1	27.6	28.1	27.6	27.6	27.2	27.6	27.6
77.5°	23.7	23.2	22.8	22.8	22.4	22.4	22.4	22.4	22.4	22.4	22.8
80°	18.0	17.5	17.1	17.5	17.1	17.5	17.1	17.1	17.5	17.1	17.1
82.5°	13.1	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	3.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.9
90°	22.3	23.4	24.6	25.7	26.3	26.5	27.0	27.5	27.9	28.4	27.9
92.5°	25.8	26.2	26.7	27.2	27.4	27.5	27.7	28.0	28.2	28.4	28.2
95°	42.3	43.4	44.6	45.7	46.3	46.2	46.0	45.7	45.5	45.3	45.5
97.5°	54.4	55.1	55.8	56.5	56.9	57.0	57.2	57.5	57.7	57.9	57.7
100°	61.9	63.8	65.7	67.6	68.5	68.7	69.2	69.7	70.1	70.6	70.1
102.5°	64.7	67.3	69.8	72.4	73.7	74.1	74.8	75.5	76.2	76.9	76.2
105°	66.9	69.4	72.0	74.5	75.8	76.3	77.2	78.1	79.1	80.0	79.1
107.5°	69.0	71.5	74.1	76.6	77.9	78.4	79.3	80.3	81.2	82.2	81.2
110°	160.9	137.5	114.1	90.7	79.0	79.5	80.4	81.3	82.3	83.2	82.3

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	434.2	333.3	232.4	131.5	81.1	81.5	82.2	82.9	83.6	84.3	83.6
115°	541.5	433.1	324.8	216.4	162.2	153.8	136.9	120.1	103.2	86.4	103.2
117.5°	673.3	639.8	606.3	572.8	556.1	525.4	464.1	402.8	341.5	280.2	341.5
120°	774.9	777.7	780.5	783.3	784.7	768.9	737.3	705.7	674.1	642.5	674.1
122.5°	835.6	837.0	838.4	839.8	840.5	840.6	840.9	841.1	841.4	841.6	841.4
125°	891.6	893.3	894.9	896.6	897.4	897.8	898.5	899.2	899.9	900.6	899.9
127.5°	944.0	946.3	948.7	951.0	952.2	952.3	952.5	952.8	953.0	953.2	953.0
130°	993.7	996.3	998.8	1001.4	1002.7	1002.6	1002.4	1002.1	1001.9	1001.7	1001.9
132.5°	1042.7	1044.8	1046.9	1049.0	1050.1	1050.0	1049.8	1049.5	1049.3	1049.1	1049.3
135°	1088.3	1090.6	1093.0	1095.3	1096.5	1096.3	1095.8	1095.3	1094.9	1094.4	1094.9
137.5°	1131.5	1133.8	1136.2	1138.5	1139.7	1139.3	1138.6	1137.9	1137.2	1136.5	1137.2
140°	1173.4	1175.5	1177.6	1179.7	1180.7	1180.1	1179.0	1177.8	1176.7	1175.5	1176.7
142.5°	1212.1	1214.0	1215.9	1217.8	1218.7	1218.1	1216.9	1215.8	1214.6	1213.4	1214.6
145°	1247.6	1249.3	1250.9	1252.6	1253.4	1252.8	1251.6	1250.5	1249.3	1248.1	1249.3
147.5°	1279.9	1281.1	1282.2	1283.4	1284.0	1283.5	1282.6	1281.6	1280.7	1279.7	1280.7
150°	1308.5	1309.9	1311.4	1312.8	1313.5	1312.9	1311.7	1310.6	1309.4	1308.2	1309.4
152.5°	1334.9	1336.3	1337.7	1339.1	1339.8	1339.0	1337.3	1335.7	1334.0	1332.4	1334.0
155°	1358.0	1359.4	1360.9	1362.3	1363.0	1362.1	1360.2	1358.3	1356.4	1354.5	1356.4
157.5°	1378.2	1379.9	1381.5	1383.2	1384.0	1383.1	1381.2	1379.3	1377.5	1375.6	1377.5
160°	1396.0	1397.4	1398.8	1400.2	1400.9	1400.1	1398.4	1396.8	1395.1	1393.5	1395.1
162.5°	1412.0	1413.6	1415.3	1416.9	1417.7	1416.6	1414.5	1412.4	1410.3	1408.2	1410.3
165°	1424.6	1426.3	1427.9	1429.6	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1424.6
167.5°	1436.2	1437.9	1439.5	1441.2	1442.0	1440.9	1438.8	1436.7	1434.6	1432.5	1434.6
170°	1444.6	1446.3	1447.9	1449.6	1450.4	1449.3	1447.2	1445.1	1443.0	1440.9	1443.0
172.5°	1450.9	1452.6	1454.2	1455.9	1456.7	1455.6	1453.5	1451.4	1449.3	1447.2	1449.3
175°	1455.1	1456.8	1458.4	1460.1	1460.9	1459.7	1457.4	1455.1	1452.7	1450.4	1452.7
177.5°	1456.2	1457.9	1459.5	1461.2	1462.0	1460.9	1458.8	1456.7	1454.6	1452.5	1454.6
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	664.9	661.9	661.0	661.9	661.0	661.4	658.4	647.0	650.0	645.2	647.8
5°	702.6	700.0	694.3	693.4	692.5	691.7	687.3	677.2	673.3	666.7	666.2
7.5°	738.6	738.6	734.2	731.1	727.2	724.1	718.4	703.5	697.4	689.5	685.1
10°	774.1	762.7	767.5	764.4	754.8	753.0	742.5	733.7	721.9	714.0	707.0
12.5°	799.5	796.0	791.6	789.0	786.3	780.6	773.6	751.3	745.1	729.4	721.5
15°	798.6	796.4	797.7	797.7	796.9	795.5	789.9	773.6	763.1	747.8	734.2
17.5°	755.7	761.4	767.1	771.0	779.8	783.7	789.0	779.3	772.8	759.6	745.1
20°	680.7	694.7	711.4	714.9	722.8	746.0	756.5	764.9	767.5	763.1	751.3
22.5°	576.4	588.2	628.6	627.7	639.1	666.7	697.4	722.4	742.1	753.0	748.6
25°	451.5	468.1	489.6	505.8	543.1	584.3	622.4	662.3	696.5	726.7	734.2
27.5°	341.5	363.4	380.5	401.9	420.8	469.4	518.5	580.8	620.7	678.1	707.9
30°	276.1	286.2	303.3	313.4	322.6	359.9	415.5	476.9	547.0	613.2	664.5
32.5°	235.8	242.8	255.5	259.9	269.6	294.6	329.6	385.7	458.0	538.3	605.8
35°	211.7	219.2	221.8	225.7	233.6	249.4	273.5	314.3	379.6	458.0	538.7
37.5°	191.1	195.1	202.5	205.1	207.8	219.6	235.8	264.3	307.7	372.1	461.6
40°	176.6	178.8	182.8	185.0	186.7	195.1	209.5	228.8	260.8	309.9	392.3
42.5°	161.3	163.9	166.6	169.2	171.4	178.0	186.7	205.1	226.6	263.9	323.5
45°	146.4	148.2	151.2	153.0	156.0	161.3	169.2	181.9	201.2	224.9	273.1
47.5°	132.8	135.0	136.3	138.5	140.7	146.4	153.9	162.2	178.0	201.2	236.3
50°	120.5	123.2	124.9	125.4	127.1	132.4	138.5	147.7	157.8	175.8	206.4
52.5°	111.8	112.2	113.5	115.3	114.8	117.9	123.6	130.6	141.1	155.6	178.0
55°	101.7	103.0	103.9	104.3	104.3	106.9	110.0	116.6	124.9	136.8	155.6
57.5°	89.0	90.3	92.9	93.8	95.1	96.4	97.7	102.1	109.1	120.5	135.9
60°	75.8	76.7	79.3	81.1	82.0	85.5	87.2	90.7	94.7	103.0	117.5
62.5°	60.9	61.8	63.1	64.9	66.6	71.9	76.3	79.8	82.8	88.5	100.4
65°	53.0	53.5	54.4	54.8	55.2	57.4	61.4	66.2	71.9	76.3	83.3
67.5°	46.0	46.5	46.9	47.8	48.2	48.7	50.4	51.7	57.4	63.6	68.8
70°	39.4	40.3	40.8	40.8	41.2	42.1	43.0	44.7	46.5	49.5	56.1
72.5°	33.3	33.8	34.6	34.6	34.6	35.5	36.4	37.3	38.1	39.9	42.5
75°	27.6	28.5	28.5	28.5	28.9	28.9	29.8	30.7	31.6	32.9	33.8
77.5°	22.8	22.8	22.8	22.8	23.2	23.2	23.7	24.5	25.0	25.4	26.3
80°	17.1	17.5	17.5	17.5	18.0	18.0	18.0	18.8	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.1	12.7	13.1	13.1	13.6	13.1	13.6	14.0
85°	7.9	7.9	7.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.8
87.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.4	3.9	3.9
90°	27.5	27.0	26.5	26.3	25.7	24.6	23.4	22.3	21.1	19.2	17.3
92.5°	28.0	27.7	27.5	27.4	27.2	26.7	26.2	25.8	25.3	24.6	23.9
95°	45.7	46.0	46.2	46.3	45.7	44.6	43.4	42.3	41.1	39.5	37.8
97.5°	57.5	57.2	57.0	56.9	56.5	55.8	55.1	54.4	53.7	50.0	46.2
100°	69.7	69.2	68.7	68.5	67.6	65.7	63.8	61.9	60.0	56.0	52.0
102.5°	75.5	74.8	74.1	73.7	72.4	69.8	67.3	64.7	62.1	104.7	147.3
105°	78.1	77.2	76.3	75.8	74.5	72.0	69.4	66.9	64.3	128.2	192.1
107.5°	80.3	79.3	78.4	77.9	76.6	74.1	71.5	69.0	66.4	145.3	224.1
110°	81.3	80.4	79.5	79.0	90.7	114.1	137.5	160.9	184.3	251.9	319.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	82.9	82.2	81.5	81.1	131.5	232.4	333.3	434.2	535.1	539.1	543.1
115°	120.1	136.9	153.8	162.2	216.4	324.8	433.1	541.5	649.9	644.0	638.2
117.5°	402.8	464.1	525.4	556.1	572.8	606.3	639.8	673.3	706.8	702.8	698.8
120°	705.7	737.3	768.9	784.7	783.3	780.5	777.7	774.9	772.1	767.9	763.7
122.5°	841.1	840.9	840.6	840.5	839.8	838.4	837.0	835.6	834.2	829.5	824.8
125°	899.2	898.5	897.8	897.4	896.6	894.9	893.3	891.6	890.0	885.6	881.1
127.5°	952.8	952.5	952.3	952.2	951.0	948.7	946.3	944.0	941.6	938.1	934.6
130°	1002.1	1002.4	1002.6	1002.7	1001.4	998.8	996.3	993.7	991.1	988.5	986.0
132.5°	1049.5	1049.8	1050.0	1050.1	1049.0	1046.9	1044.8	1042.7	1040.6	1038.0	1035.5
135°	1095.3	1095.8	1096.3	1096.5	1095.3	1093.0	1090.6	1088.3	1085.9	1083.8	1081.7
137.5°	1137.9	1138.6	1139.3	1139.7	1138.5	1136.2	1133.8	1131.5	1129.1	1126.8	1124.4
140°	1177.8	1179.0	1180.1	1180.7	1179.7	1177.6	1175.5	1173.4	1171.3	1168.7	1166.1
142.5°	1215.8	1216.9	1218.1	1218.7	1217.8	1215.9	1214.0	1212.1	1210.2	1207.2	1204.1
145°	1250.5	1251.6	1252.8	1253.4	1252.6	1250.9	1249.3	1247.6	1246.0	1242.0	1238.0
147.5°	1281.6	1282.6	1283.5	1284.0	1283.4	1282.2	1281.1	1279.9	1278.7	1274.7	1270.7
150°	1310.6	1311.7	1312.9	1313.5	1312.8	1311.4	1309.9	1308.5	1307.1	1303.4	1299.6
152.5°	1335.7	1337.3	1339.0	1339.8	1339.1	1337.7	1336.3	1334.9	1333.5	1330.0	1326.5
155°	1358.3	1360.2	1362.1	1363.0	1362.3	1360.9	1359.4	1358.0	1356.6	1353.8	1351.0
157.5°	1379.3	1381.2	1383.1	1384.0	1383.2	1381.5	1379.9	1378.2	1376.6	1374.5	1372.4
160°	1396.8	1398.4	1400.1	1400.9	1400.2	1398.8	1397.4	1396.0	1394.6	1393.2	1391.8
162.5°	1412.4	1414.5	1416.6	1417.7	1416.9	1415.3	1413.6	1412.0	1410.4	1409.2	1408.0
165°	1426.3	1427.9	1429.6	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1422.3	1421.6
167.5°	1436.7	1438.8	1440.9	1442.0	1441.2	1439.5	1437.9	1436.2	1434.6	1433.9	1433.2
170°	1445.1	1447.2	1449.3	1450.4	1449.6	1447.9	1446.3	1444.6	1443.0	1442.5	1442.1
172.5°	1451.4	1453.5	1455.6	1456.7	1455.9	1454.2	1452.6	1450.9	1449.3	1448.8	1448.4
175°	1455.1	1457.4	1459.7	1460.9	1460.1	1458.4	1456.8	1455.1	1453.5	1453.0	1452.6
177.5°	1456.7	1458.8	1460.9	1462.0	1461.2	1459.5	1457.9	1456.2	1454.6	1454.4	1454.1
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	643.9	641.7	641.7	640.4	640.4	633.4	633.4	635.6	632.9	629.9	625.5
5°	660.5	655.7	654.4	652.7	647.0	638.2	634.7	633.4	628.1	621.5	614.1
7.5°	676.3	668.4	664.5	660.5	653.1	640.8	633.8	629.0	621.1	611.0	601.4
10°	691.7	681.6	671.5	666.7	656.2	640.8	630.7	622.9	611.5	597.9	584.3
12.5°	705.7	684.7	682.9	673.3	657.9	640.4	625.0	613.6	599.2	583.4	567.6
15°	718.0	696.5	686.0	677.2	657.0	635.1	618.9	604.9	585.6	567.6	548.3
17.5°	724.1	700.9	693.9	679.4	658.8	630.3	608.4	591.3	570.3	548.8	526.9
20°	730.2	703.1	691.7	681.6	653.5	621.1	596.6	576.8	553.6	528.2	504.1
22.5°	733.3	703.1	689.5	675.5	648.3	611.0	582.1	558.9	531.7	505.8	476.9
25°	728.0	700.4	684.2	669.8	639.1	598.7	565.4	539.1	510.2	480.8	451.5
27.5°	714.9	694.3	675.5	660.5	626.4	583.0	547.9	518.1	488.3	455.4	425.6
30°	690.4	681.1	666.2	649.6	612.3	568.9	527.3	496.6	463.7	430.9	399.7
32.5°	652.2	660.1	650.5	636.0	595.7	549.7	505.4	474.3	438.3	402.8	374.3
35°	605.8	633.8	628.6	618.5	578.1	529.1	484.8	447.1	411.1	375.2	346.7
37.5°	554.9	597.4	601.8	595.7	558.0	508.0	459.4	422.5	385.7	349.3	320.4
40°	485.2	550.5	564.6	567.2	536.9	482.6	431.7	395.8	359.4	323.9	288.9
42.5°	421.2	503.6	521.2	532.1	510.2	457.6	406.3	366.4	330.5	298.5	263.4
45°	361.2	447.1	475.6	489.6	480.0	429.1	376.1	338.8	305.9	276.6	242.8
47.5°	299.4	385.7	425.6	448.0	448.0	400.2	347.1	310.3	278.8	253.8	224.0
50°	258.2	330.1	371.3	400.6	408.5	370.8	320.8	284.9	255.1	227.9	205.1
52.5°	220.0	284.5	318.7	349.3	372.1	339.3	291.5	259.0	229.7	204.3	186.3
55°	190.2	238.4	269.6	303.3	328.7	307.3	263.0	231.4	206.0	185.0	169.6
57.5°	161.7	203.8	229.2	259.0	286.2	270.0	234.5	207.3	185.0	166.6	153.0
60°	137.6	171.8	191.5	214.8	248.5	237.1	207.8	182.8	164.8	148.2	136.8
62.5°	117.0	144.2	160.9	177.5	208.2	202.9	180.1	160.9	145.5	131.5	121.9
65°	96.0	118.3	131.5	146.0	170.5	172.7	154.3	140.7	126.7	114.4	105.6
67.5°	77.6	95.1	106.9	119.2	138.9	145.1	132.4	121.0	109.1	99.1	91.2
70°	62.7	75.0	83.7	93.4	109.6	117.0	110.5	102.6	92.9	84.6	77.6
72.5°	49.5	57.4	62.7	70.1	83.3	90.7	90.3	83.3	76.3	70.6	64.9
75°	36.4	42.5	46.9	51.7	62.2	69.3	71.0	67.9	60.9	56.5	52.2
77.5°	27.6	31.1	33.3	36.8	44.3	50.4	53.0	52.2	47.3	43.8	40.8
80°	21.0	21.9	22.8	24.1	30.2	35.9	37.7	37.3	34.6	33.3	29.8
82.5°	14.9	15.3	15.8	16.2	18.4	23.2	25.0	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.8	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	3.9	3.9	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	15.4	13.5	12.6	11.3	8.8	6.2	3.7	1.1	3.7	6.2	8.8
92.5°	23.2	22.5	22.1	22.6	23.5	24.4	25.4	26.3	25.4	24.4	23.5
95°	36.2	34.5	33.7	37.6	45.3	53.0	60.8	68.5	60.8	53.0	45.3
97.5°	42.5	38.8	36.9	46.5	65.7	84.8	104.0	123.2	104.0	84.8	65.7
100°	48.1	44.1	42.1	58.1	90.2	122.3	154.3	186.4	154.3	122.3	90.2
102.5°	189.9	232.5	253.8	254.0	254.5	255.0	255.4	255.9	255.4	255.0	254.5
105°	256.0	319.9	351.8	348.3	341.3	334.2	327.2	320.2	327.2	334.2	341.3
107.5°	303.0	381.9	421.3	418.4	412.5	406.7	400.8	395.0	400.8	406.7	412.5
110°	387.2	454.9	488.7	486.2	481.3	476.4	471.5	466.6	471.5	476.4	481.3

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	547.0	551.0	553.0	550.9	546.7	542.4	538.2	534.0	538.2	542.4	546.7
115°	632.3	626.4	623.5	621.5	617.5	613.6	609.6	605.6	609.6	613.6	617.5
117.5°	694.9	690.9	688.9	686.6	681.9	677.2	672.5	667.8	672.5	677.2	681.9
120°	759.4	755.2	753.1	751.3	747.8	744.3	740.8	737.3	740.8	744.3	747.8
122.5°	820.1	815.4	813.1	811.2	807.5	803.8	800.0	796.3	800.0	803.8	807.5
125°	876.7	872.2	870.0	868.5	865.4	862.4	859.3	856.3	859.3	862.4	865.4
127.5°	931.1	927.6	925.8	924.2	920.9	917.6	914.4	911.1	914.4	917.6	920.9
130°	983.4	980.9	979.6	977.7	974.0	970.2	966.5	962.7	966.5	970.2	974.0
132.5°	1032.9	1030.4	1029.1	1027.6	1024.5	1021.5	1018.4	1015.4	1018.4	1021.5	1024.5
135°	1079.6	1077.5	1076.5	1074.6	1070.9	1067.1	1063.4	1059.6	1063.4	1067.1	1070.9
137.5°	1122.1	1119.8	1118.6	1117.2	1114.4	1111.6	1108.8	1106.0	1108.8	1111.6	1114.4
140°	1163.6	1161.0	1159.7	1158.8	1156.9	1155.0	1153.1	1151.2	1153.1	1155.0	1156.9
142.5°	1201.1	1198.0	1196.5	1195.7	1194.1	1192.4	1190.8	1189.2	1190.8	1192.4	1194.1
145°	1234.1	1230.1	1228.1	1228.2	1228.5	1228.7	1229.0	1229.2	1229.0	1228.7	1228.5
147.5°	1266.8	1262.8	1260.8	1261.1	1261.8	1262.5	1263.2	1263.9	1263.2	1262.5	1261.8
150°	1295.9	1292.2	1290.3	1291.1	1292.8	1294.4	1296.1	1297.7	1296.1	1294.4	1292.8
152.5°	1323.0	1319.5	1317.7	1318.6	1320.5	1322.4	1324.2	1326.1	1324.2	1322.4	1320.5
155°	1348.2	1345.4	1344.0	1345.1	1347.2	1349.3	1351.4	1353.5	1351.4	1349.3	1347.2
157.5°	1370.3	1368.2	1367.2	1368.1	1370.0	1371.9	1373.7	1375.6	1373.7	1371.9	1370.0
160°	1390.3	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6	1393.2	1391.8	1390.3
162.5°	1406.9	1405.7	1405.1	1405.8	1407.2	1408.6	1410.0	1411.4	1410.0	1408.6	1407.2
165°	1420.9	1420.2	1419.8	1420.5	1421.9	1423.4	1424.8	1426.2	1424.8	1423.4	1421.9
167.5°	1432.5	1431.8	1431.4	1432.1	1433.5	1434.9	1436.3	1437.7	1436.3	1434.9	1433.5
170°	1441.6	1441.1	1440.9	1441.6	1443.0	1444.4	1445.8	1447.2	1445.8	1444.4	1443.0
172.5°	1447.9	1447.4	1447.2	1447.9	1449.3	1450.7	1452.1	1453.5	1452.1	1450.7	1449.3
175°	1452.1	1451.6	1451.4	1452.2	1453.9	1455.5	1457.2	1458.8	1457.2	1455.5	1453.9
177.5°	1453.9	1453.6	1453.5	1454.3	1456.0	1457.6	1459.3	1460.9	1459.3	1457.6	1456.0
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	623.7	624.2	625.5	621.5	615.4	612.8	604.9	603.6	602.3	602.3	603.6
5°	609.7	607.9	608.4	600.9	592.2	586.9	576.0	577.7	572.0	568.5	569.4
7.5°	594.4	589.5	589.1	579.5	568.5	558.9	547.5	544.8	539.6	533.4	530.8
10°	575.1	571.6	565.0	554.0	540.0	532.1	516.8	507.6	506.3	497.1	493.5
12.5°	555.4	549.2	542.6	527.3	511.5	498.8	487.4	477.3	470.3	462.4	457.2
15°	532.6	525.1	517.7	501.4	483.0	470.3	453.2	438.3	417.7	401.5	392.3
17.5°	507.6	499.2	489.2	471.2	453.2	435.7	404.1	386.6	372.1	362.5	356.8
20°	481.7	472.5	462.4	444.5	413.3	382.7	365.1	351.5	342.8	333.1	326.1
22.5°	454.5	444.9	433.9	405.9	373.0	351.5	337.9	325.2	312.5	307.3	303.8
25°	429.1	420.3	406.3	368.2	342.3	322.6	307.3	298.9	292.4	285.3	278.8
27.5°	402.8	386.6	366.9	334.9	318.7	298.5	287.5	281.4	270.0	265.2	262.1
30°	371.3	353.3	334.4	311.6	292.8	278.8	268.7	258.6	252.0	247.2	242.0
32.5°	339.3	322.2	310.3	286.7	272.6	258.2	248.5	242.4	232.7	229.7	227.5
35°	311.6	297.2	286.7	267.4	254.2	241.1	234.1	224.9	218.7	213.0	209.5
37.5°	284.5	276.6	265.6	249.4	235.4	224.9	215.2	212.1	203.8	200.8	197.2
40°	265.6	253.8	244.6	230.6	218.7	207.3	201.2	194.2	188.5	183.7	182.3
42.5°	242.8	234.1	228.8	213.5	201.2	194.6	187.2	179.3	174.9	170.9	166.1
45°	225.7	217.8	210.4	198.1	187.2	178.8	172.3	167.0	159.5	157.8	150.3
47.5°	207.8	199.9	194.2	181.9	171.8	163.9	159.1	152.1	146.0	142.0	138.5
50°	189.8	183.2	178.0	167.4	158.7	150.3	143.8	136.8	134.1	127.6	125.4
52.5°	172.7	168.3	162.6	152.5	143.8	136.8	129.7	124.0	120.1	116.6	114.0
55°	158.2	151.2	148.6	137.6	130.2	122.7	116.6	113.1	108.3	106.1	103.9
57.5°	142.0	138.1	133.7	125.4	117.0	110.0	105.6	100.4	97.7	95.1	93.4
60°	128.0	122.3	118.8	111.8	104.3	97.7	93.8	89.9	86.3	84.2	80.7
62.5°	111.8	107.4	105.2	97.7	91.6	85.5	82.0	78.0	75.4	71.4	67.1
65°	97.7	94.2	91.6	85.5	79.8	74.1	70.6	65.7	62.2	60.0	59.6
67.5°	85.5	82.8	78.9	73.2	67.5	63.1	59.2	55.2	54.8	53.9	53.9
70°	71.9	69.3	67.1	60.9	56.1	51.3	50.4	49.1	47.8	47.3	46.5
72.5°	60.0	57.9	55.2	50.0	45.1	43.8	43.0	42.1	40.8	40.3	39.9
75°	48.7	45.6	43.8	39.0	37.7	36.8	35.9	34.6	33.8	33.3	32.4
77.5°	37.3	34.2	34.2	31.6	30.7	29.4	28.5	27.6	27.2	26.3	26.3
80°	26.3	26.3	25.4	24.1	22.8	22.4	21.0	20.6	20.2	20.6	19.7
82.5°	19.3	17.5	17.5	16.7	15.8	15.3	14.5	14.5	14.0	14.0	14.0
85°	11.0	11.0	10.5	9.6	9.2	9.2	8.8	8.8	8.3	8.3	7.9
87.5°	4.4	3.9	4.4	3.9	3.9	3.5	3.5	3.5	3.1	3.5	3.1
90°	11.3	12.6	13.5	15.4	17.3	19.2	21.1	22.3	23.4	24.6	25.7
92.5°	22.6	22.1	22.5	23.2	23.9	24.6	25.3	25.8	26.2	26.7	27.2
95°	37.6	33.7	34.5	36.2	37.8	39.5	41.1	42.3	43.4	44.6	45.7
97.5°	46.5	36.9	38.8	42.5	46.2	50.0	53.7	54.4	55.1	55.8	56.5
100°	58.1	42.1	44.1	48.1	52.0	56.0	60.0	61.9	63.8	65.7	67.6
102.5°	254.0	253.8	232.5	189.9	147.3	104.7	62.1	64.7	67.3	69.8	72.4
105°	348.3	351.8	319.9	256.0	192.1	128.2	64.3	66.9	69.4	72.0	74.5
107.5°	418.4	421.3	381.9	303.0	224.1	145.3	66.4	69.0	71.5	74.1	76.6
110°	486.2	488.7	454.9	387.2	319.6	251.9	184.3	160.9	137.5	114.1	90.7

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	550.9	553.0	551.0	547.0	543.1	539.1	535.1	434.2	333.3	232.4	131.5
115°	621.5	623.5	626.4	632.3	638.2	644.0	649.9	541.5	433.1	324.8	216.4
117.5°	686.6	688.9	690.9	694.9	698.8	702.8	706.8	673.3	639.8	606.3	572.8
120°	751.3	753.1	755.2	759.4	763.7	767.9	772.1	774.9	777.7	780.5	783.3
122.5°	811.2	813.1	815.4	820.1	824.8	829.5	834.2	835.6	837.0	838.4	839.8
125°	868.5	870.0	872.2	876.7	881.1	885.6	890.0	891.6	893.3	894.9	896.6
127.5°	924.2	925.8	927.6	931.1	934.6	938.1	941.6	944.0	946.3	948.7	951.0
130°	977.7	979.6	980.9	983.4	986.0	988.5	991.1	993.7	996.3	998.8	1001.4
132.5°	1027.6	1029.1	1030.4	1032.9	1035.5	1038.0	1040.6	1042.7	1044.8	1046.9	1049.0
135°	1074.6	1076.5	1077.5	1079.6	1081.7	1083.8	1085.9	1088.3	1090.6	1093.0	1095.3
137.5°	1117.2	1118.6	1119.8	1122.1	1124.4	1126.8	1129.1	1131.5	1133.8	1136.2	1138.5
140°	1158.8	1159.7	1161.0	1163.6	1166.1	1168.7	1171.3	1173.4	1175.5	1177.6	1179.7
142.5°	1195.7	1196.5	1198.0	1201.1	1204.1	1207.2	1210.2	1212.1	1214.0	1215.9	1217.8
145°	1228.2	1228.1	1230.1	1234.1	1238.0	1242.0	1246.0	1247.6	1249.3	1250.9	1252.6
147.5°	1261.1	1260.8	1262.8	1266.8	1270.7	1274.7	1278.7	1279.9	1281.1	1282.2	1283.4
150°	1291.1	1290.3	1292.2	1295.9	1299.6	1303.4	1307.1	1308.5	1309.9	1311.4	1312.8
152.5°	1318.6	1317.7	1319.5	1323.0	1326.5	1330.0	1333.5	1334.9	1336.3	1337.7	1339.1
155°	1345.1	1344.0	1345.4	1348.2	1351.0	1353.8	1356.6	1358.0	1359.4	1360.9	1362.3
157.5°	1368.1	1367.2	1368.2	1370.3	1372.4	1374.5	1376.6	1378.2	1379.9	1381.5	1383.2
160°	1388.9	1388.2	1388.9	1390.3	1391.8	1393.2	1394.6	1396.0	1397.4	1398.8	1400.2
162.5°	1405.8	1405.1	1405.7	1406.9	1408.0	1409.2	1410.4	1412.0	1413.6	1415.3	1416.9
165°	1420.5	1419.8	1420.2	1420.9	1421.6	1422.3	1423.0	1424.6	1426.3	1427.9	1429.6
167.5°	1432.1	1431.4	1431.8	1432.5	1433.2	1433.9	1434.6	1436.2	1437.9	1439.5	1441.2
170°	1441.6	1440.9	1441.1	1441.6	1442.1	1442.5	1443.0	1444.6	1446.3	1447.9	1449.6
172.5°	1447.9	1447.2	1447.4	1447.9	1448.4	1448.8	1449.3	1450.9	1452.6	1454.2	1455.9
175°	1452.2	1451.4	1451.6	1452.1	1452.6	1453.0	1453.5	1455.1	1456.8	1458.4	1460.1
177.5°	1454.3	1453.5	1453.6	1453.9	1454.1	1454.4	1454.6	1456.2	1457.9	1459.5	1461.2
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	603.6	602.7	600.1	600.9	599.6	599.6	598.7	598.7	598.7	600.9	599.6
5°	570.7	567.6	564.6	563.2	561.9	560.6	560.6	560.2	564.1	563.2	566.7
7.5°	529.9	529.1	522.9	522.9	520.7	519.8	522.0	522.5	522.9	523.8	526.0
10°	493.5	491.4	482.6	483.5	482.2	480.4	481.7	480.8	483.9	484.8	483.9
12.5°	450.6	446.6	437.0	432.2	426.9	423.0	427.8	424.3	436.6	440.1	449.7
15°	393.6	386.2	379.6	379.6	374.8	371.3	373.4	377.4	380.0	384.0	385.7
17.5°	355.5	352.4	347.1	344.1	342.8	341.5	341.5	343.2	348.9	348.5	352.0
20°	323.0	321.3	318.7	314.7	313.4	312.5	312.5	312.5	316.5	320.0	322.2
22.5°	300.7	299.4	297.6	292.4	289.7	288.9	291.0	292.4	295.4	298.1	300.2
25°	278.3	275.3	272.2	270.4	269.1	269.1	270.0	270.4	271.8	273.1	275.7
27.5°	259.9	257.7	253.3	248.5	248.5	247.2	248.1	249.0	252.0	256.4	258.6
30°	239.3	238.9	237.1	235.4	233.6	232.7	234.5	235.8	236.3	238.4	238.4
32.5°	224.4	221.4	218.3	216.5	215.7	215.2	215.7	217.4	217.4	220.0	223.1
35°	209.5	207.8	204.7	201.6	200.8	198.6	200.3	202.1	205.1	206.4	207.8
37.5°	193.3	191.1	189.8	188.9	187.2	187.6	186.3	188.9	191.5	191.1	192.0
40°	181.0	177.1	173.1	172.7	172.3	171.8	171.8	172.3	174.0	175.8	178.4
42.5°	165.2	163.9	160.4	156.9	156.0	155.2	154.3	156.0	159.5	162.6	163.9
45°	149.0	147.3	146.4	143.8	142.0	141.6	140.7	142.9	146.0	147.3	148.2
47.5°	134.1	133.7	131.1	131.5	130.2	130.6	130.2	131.5	131.5	132.8	133.7
50°	124.0	122.7	121.4	120.5	119.2	119.2	118.8	119.2	121.0	122.7	122.3
52.5°	114.0	111.8	111.3	110.9	110.0	110.9	109.6	110.0	111.8	112.6	112.2
55°	102.1	101.7	100.8	99.9	99.5	99.1	99.1	99.1	100.8	102.1	102.6
57.5°	92.9	90.7	89.0	89.0	87.2	86.8	87.7	88.1	89.4	90.3	91.2
60°	80.2	79.3	76.7	75.4	72.8	72.3	72.3	74.1	76.3	79.3	80.2
62.5°	66.6	65.3	64.9	64.9	64.9	64.9	64.9	64.9	64.9	65.3	65.3
65°	59.2	59.6	59.2	58.7	59.2	59.2	58.7	58.7	58.7	59.2	59.6
67.5°	53.0	52.6	53.0	52.6	52.2	52.2	51.7	52.2	52.6	53.0	53.0
70°	46.0	46.0	45.6	46.0	45.6	45.1	44.7	44.7	45.6	46.0	46.0
72.5°	39.4	39.4	39.0	39.0	38.1	38.1	38.6	38.1	38.1	39.4	39.4
75°	32.9	32.4	32.0	32.0	31.6	31.6	31.6	31.1	32.0	32.0	32.4
77.5°	25.9	25.9	25.9	25.4	25.4	25.0	25.0	25.4	25.4	25.4	25.9
80°	19.7	19.7	19.7	19.3	18.8	18.8	18.8	18.8	18.8	19.3	18.8
82.5°	13.6	13.6	13.6	13.6	13.6	13.1	13.1	13.1	13.6	13.6	13.1
85°	8.3	7.9	8.3	8.3	7.9	8.3	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	26.3	26.5	27.0	27.5	27.9	28.4	27.9	27.5	27.0	26.5	26.3
92.5°	27.4	27.5	27.7	28.0	28.2	28.4	28.2	28.0	27.7	27.5	27.4
95°	46.3	46.2	46.0	45.7	45.5	45.3	45.5	45.7	46.0	46.2	46.3
97.5°	56.9	57.0	57.2	57.5	57.7	57.9	57.7	57.5	57.2	57.0	56.9
100°	68.5	68.7	69.2	69.7	70.1	70.6	70.1	69.7	69.2	68.7	68.5
102.5°	73.7	74.1	74.8	75.5	76.2	76.9	76.2	75.5	74.8	74.1	73.7
105°	75.8	76.3	77.2	78.1	79.1	80.0	79.1	78.1	77.2	76.3	75.8
107.5°	77.9	78.4	79.3	80.3	81.2	82.2	81.2	80.3	79.3	78.4	77.9
110°	79.0	79.5	80.4	81.3	82.3	83.2	82.3	81.3	80.4	79.5	79.0

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	81.1	81.5	82.2	82.9	83.6	84.3	83.6	82.9	82.2	81.5	81.1
115°	162.2	153.8	136.9	120.1	103.2	86.4	103.2	120.1	136.9	153.8	162.2
117.5°	556.1	525.4	464.1	402.8	341.5	280.2	341.5	402.8	464.1	525.4	556.1
120°	784.7	768.9	737.3	705.7	674.1	642.5	674.1	705.7	737.3	768.9	784.7
122.5°	840.5	840.6	840.9	841.1	841.4	841.6	841.4	841.1	840.9	840.6	840.5
125°	897.4	897.8	898.5	899.2	899.9	900.6	899.9	899.2	898.5	897.8	897.4
127.5°	952.2	952.3	952.5	952.8	953.0	953.2	953.0	952.8	952.5	952.3	952.2
130°	1002.7	1002.6	1002.4	1002.1	1001.9	1001.7	1001.9	1002.1	1002.4	1002.6	1002.7
132.5°	1050.1	1050.0	1049.8	1049.5	1049.3	1049.1	1049.3	1049.5	1049.8	1050.0	1050.1
135°	1096.5	1096.3	1095.8	1095.3	1094.9	1094.4	1094.9	1095.3	1095.8	1096.3	1096.5
137.5°	1139.7	1139.3	1138.6	1137.9	1137.2	1136.5	1137.2	1137.9	1138.6	1139.3	1139.7
140°	1180.7	1180.1	1179.0	1177.8	1176.7	1175.5	1176.7	1177.8	1179.0	1180.1	1180.7
142.5°	1218.7	1218.1	1216.9	1215.8	1214.6	1213.4	1214.6	1215.8	1216.9	1218.1	1218.7
145°	1253.4	1252.8	1251.6	1250.5	1249.3	1248.1	1249.3	1250.5	1251.6	1252.8	1253.4
147.5°	1284.0	1283.5	1282.6	1281.6	1280.7	1279.7	1280.7	1281.6	1282.6	1283.5	1284.0
150°	1313.5	1312.9	1311.7	1310.6	1309.4	1308.2	1309.4	1310.6	1311.7	1312.9	1313.5
152.5°	1339.8	1339.0	1337.3	1335.7	1334.0	1332.4	1334.0	1335.7	1337.3	1339.0	1339.8
155°	1363.0	1362.1	1360.2	1358.3	1356.4	1354.5	1356.4	1358.3	1360.2	1362.1	1363.0
157.5°	1384.0	1383.1	1381.2	1379.3	1377.5	1375.6	1377.5	1379.3	1381.2	1383.1	1384.0
160°	1400.9	1400.1	1398.4	1396.8	1395.1	1393.5	1395.1	1396.8	1398.4	1400.1	1400.9
162.5°	1417.7	1416.6	1414.5	1412.4	1410.3	1408.2	1410.3	1412.4	1414.5	1416.6	1417.7
165°	1430.4	1429.6	1427.9	1426.3	1424.6	1423.0	1424.6	1426.3	1427.9	1429.6	1430.4
167.5°	1442.0	1440.9	1438.8	1436.7	1434.6	1432.5	1434.6	1436.7	1438.8	1440.9	1442.0
170°	1450.4	1449.3	1447.2	1445.1	1443.0	1440.9	1443.0	1445.1	1447.2	1449.3	1450.4
172.5°	1456.7	1455.6	1453.5	1451.4	1449.3	1447.2	1449.3	1451.4	1453.5	1455.6	1456.7
175°	1460.9	1459.7	1457.4	1455.1	1452.7	1450.4	1452.7	1455.1	1457.4	1459.7	1460.9
177.5°	1462.0	1460.9	1458.8	1456.7	1454.6	1452.5	1454.6	1456.7	1458.8	1460.9	1462.0
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	600.9	603.1	602.3	597.4	602.3	603.6	606.2	608.8	610.6	613.2	615.4
5°	563.2	567.6	570.3	567.6	576.4	577.7	583.8	587.3	592.6	597.0	600.5
7.5°	527.7	531.2	536.5	537.4	542.6	548.8	557.5	566.3	574.6	579.0	583.0
10°	489.6	495.7	503.6	501.9	509.8	519.4	528.6	542.6	549.7	557.5	564.6
12.5°	451.5	455.4	465.9	469.4	480.8	488.3	501.0	509.8	527.3	536.5	542.6
15°	384.8	401.1	414.2	430.0	444.9	458.9	470.3	486.1	501.4	508.5	518.5
17.5°	354.6	362.1	369.9	377.8	397.1	422.1	442.3	459.4	472.5	481.7	493.5
20°	323.0	330.5	339.3	346.7	358.5	376.5	401.5	430.9	446.6	456.3	467.7
22.5°	300.7	307.7	313.4	320.0	329.2	342.3	361.2	397.6	418.6	430.4	440.5
25°	276.6	285.3	291.5	296.3	303.8	318.2	333.6	354.2	391.9	401.1	415.1
27.5°	259.9	262.6	269.6	277.0	284.5	292.4	308.1	325.7	351.1	371.3	388.4
30°	240.2	246.8	253.3	256.4	263.0	274.4	284.0	302.9	322.6	338.4	359.0
32.5°	225.3	229.2	233.6	241.1	247.2	255.1	264.7	280.5	297.2	307.3	323.0
35°	208.6	211.3	220.5	223.5	229.7	237.6	247.2	259.5	277.5	285.3	296.7
37.5°	192.9	199.0	201.6	208.6	214.3	222.2	229.2	243.3	255.1	264.3	274.8
40°	180.6	183.2	188.0	194.2	199.0	205.1	213.9	224.0	236.7	244.1	253.3
42.5°	165.7	167.9	174.0	177.5	185.4	191.1	196.4	208.6	220.0	225.7	234.9
45°	149.5	154.7	158.7	165.7	170.1	177.1	183.7	192.4	202.9	209.5	214.8
47.5°	135.4	140.7	144.6	151.2	158.2	161.3	168.3	177.5	187.2	192.4	199.9
50°	124.0	125.8	133.2	136.3	143.8	149.9	154.7	162.6	173.1	176.2	182.3
52.5°	113.1	114.4	119.2	123.2	129.7	135.0	141.1	148.6	157.4	162.2	167.0
55°	103.4	104.3	106.5	110.9	115.3	121.9	127.6	134.6	142.0	147.3	151.7
57.5°	92.5	94.2	96.0	98.6	103.0	109.1	115.3	121.9	128.0	131.5	137.2
60°	79.8	82.4	85.5	88.5	91.6	96.0	103.0	109.1	114.8	117.9	122.3
62.5°	66.2	71.4	74.1	77.6	80.2	84.2	89.4	96.4	100.4	104.3	107.8
65°	59.6	60.0	60.5	64.0	68.8	72.8	77.6	82.8	89.0	91.6	94.2
67.5°	53.0	53.5	54.4	54.8	56.5	60.9	66.2	71.9	76.7	78.5	81.1
70°	46.5	46.5	48.2	48.7	49.1	49.5	53.9	59.6	64.0	66.2	69.3
72.5°	39.4	39.9	40.8	41.2	42.1	43.0	44.3	47.3	52.6	54.8	58.3
75°	32.4	32.9	33.3	33.8	35.1	35.5	36.8	38.6	40.8	43.4	45.6
77.5°	25.9	25.9	26.3	27.2	28.1	28.5	29.8	30.7	31.6	32.9	34.6
80°	19.3	19.7	19.7	20.6	20.6	21.0	21.5	22.8	23.7	24.5	25.4
82.5°	13.1	14.0	14.0	14.0	14.5	14.9	15.3	15.3	16.2	16.7	18.0
85°	7.9	8.3	8.3	8.3	7.9	8.8	8.8	9.2	9.2	9.2	9.6
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	3.9	3.9
90°	25.7	24.6	23.4	22.3	21.1	19.2	17.3	15.4	13.5	12.6	11.3
92.5°	27.2	26.7	26.2	25.8	25.3	24.6	23.9	23.2	22.5	22.1	22.6
95°	45.7	44.6	43.4	42.3	41.1	39.5	37.8	36.2	34.5	33.7	37.6
97.5°	56.5	55.8	55.1	54.4	53.7	50.0	46.2	42.5	38.8	36.9	46.5
100°	67.6	65.7	63.8	61.9	60.0	56.0	52.0	48.1	44.1	42.1	58.1
102.5°	72.4	69.8	67.3	64.7	62.1	104.7	147.3	189.9	232.5	253.8	254.0
105°	74.5	72.0	69.4	66.9	64.3	128.2	192.1	256.0	319.9	351.8	348.3
107.5°	76.6	74.1	71.5	69.0	66.4	145.3	224.1	303.0	381.9	421.3	418.4
110°	90.7	114.1	137.5	160.9	184.3	251.9	319.6	387.2	454.9	488.7	486.2

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	131.5	232.4	333.3	434.2	535.1	539.1	543.1	547.0	551.0	553.0	550.9
115°	216.4	324.8	433.1	541.5	649.9	644.0	638.2	632.3	626.4	623.5	621.5
117.5°	572.8	606.3	639.8	673.3	706.8	702.8	698.8	694.9	690.9	688.9	686.6
120°	783.3	780.5	777.7	774.9	772.1	767.9	763.7	759.4	755.2	753.1	751.3
122.5°	839.8	838.4	837.0	835.6	834.2	829.5	824.8	820.1	815.4	813.1	811.2
125°	896.6	894.9	893.3	891.6	890.0	885.6	881.1	876.7	872.2	870.0	868.5
127.5°	951.0	948.7	946.3	944.0	941.6	938.1	934.6	931.1	927.6	925.8	924.2
130°	1001.4	998.8	996.3	993.7	991.1	988.5	986.0	983.4	980.9	979.6	977.7
132.5°	1049.0	1046.9	1044.8	1042.7	1040.6	1038.0	1035.5	1032.9	1030.4	1029.1	1027.6
135°	1095.3	1093.0	1090.6	1088.3	1085.9	1083.8	1081.7	1079.6	1077.5	1076.5	1074.6
137.5°	1138.5	1136.2	1133.8	1131.5	1129.1	1126.8	1124.4	1122.1	1119.8	1118.6	1117.2
140°	1179.7	1177.6	1175.5	1173.4	1171.3	1168.7	1166.1	1163.6	1161.0	1159.7	1158.8
142.5°	1217.8	1215.9	1214.0	1212.1	1210.2	1207.2	1204.1	1201.1	1198.0	1196.5	1195.7
145°	1252.6	1250.9	1249.3	1247.6	1246.0	1242.0	1238.0	1234.1	1230.1	1228.1	1228.2
147.5°	1283.4	1282.2	1281.1	1279.9	1278.7	1274.7	1270.7	1266.8	1262.8	1260.8	1261.1
150°	1312.8	1311.4	1309.9	1308.5	1307.1	1303.4	1299.6	1295.9	1292.2	1290.3	1291.1
152.5°	1339.1	1337.7	1336.3	1334.9	1333.5	1330.0	1326.5	1323.0	1319.5	1317.7	1318.6
155°	1362.3	1360.9	1359.4	1358.0	1356.6	1353.8	1351.0	1348.2	1345.4	1344.0	1345.1
157.5°	1383.2	1381.5	1379.9	1378.2	1376.6	1374.5	1372.4	1370.3	1368.2	1367.2	1368.1
160°	1400.2	1398.8	1397.4	1396.0	1394.6	1393.2	1391.8	1390.3	1388.9	1388.2	1388.9
162.5°	1416.9	1415.3	1413.6	1412.0	1410.4	1409.2	1408.0	1406.9	1405.7	1405.1	1405.8
165°	1429.6	1427.9	1426.3	1424.6	1423.0	1422.3	1421.6	1420.9	1420.2	1419.8	1420.5
167.5°	1441.2	1439.5	1437.9	1436.2	1434.6	1433.9	1433.2	1432.5	1431.8	1431.4	1432.1
170°	1449.6	1447.9	1446.3	1444.6	1443.0	1442.5	1442.1	1441.6	1441.1	1440.9	1441.6
172.5°	1455.9	1454.2	1452.6	1450.9	1449.3	1448.8	1448.4	1447.9	1447.4	1447.2	1447.9
175°	1460.1	1458.4	1456.8	1455.1	1453.5	1453.0	1452.6	1452.1	1451.6	1451.4	1452.2
177.5°	1461.2	1459.5	1457.9	1456.2	1454.6	1454.4	1454.1	1453.9	1453.6	1453.5	1454.3
180°	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6	1455.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	630.7	630.7	630.7	630.7
2.5°	619.3	618.0	625.9	634.7
5°	606.6	608.8	618.9	631.2
7.5°	593.5	598.3	610.1	626.4
10°	575.1	583.8	601.8	618.5
12.5°	557.1	568.9	586.0	605.8
15°	536.9	550.1	571.1	594.8
17.5°	514.6	529.5	554.0	579.9
20°	490.9	510.6	536.5	564.6
22.5°	464.6	488.3	515.0	546.1
25°	439.2	465.1	491.8	527.7
27.5°	414.2	439.6	469.4	505.8
30°	389.2	412.5	444.5	483.5
32.5°	362.5	386.6	420.3	460.2
35°	337.9	362.1	393.6	433.1
37.5°	311.6	337.5	367.8	408.5
40°	281.0	311.2	340.6	379.6
42.5°	255.5	287.5	316.0	352.8
45°	235.4	265.6	289.3	325.2
47.5°	216.5	241.1	265.2	298.5
50°	198.6	217.4	242.4	272.2
52.5°	180.1	196.4	217.8	245.9
55°	163.5	178.8	198.1	219.6
57.5°	148.2	159.1	178.4	197.7
60°	131.1	142.5	157.4	173.6
62.5°	116.6	125.4	139.4	153.0
65°	101.3	109.6	120.1	132.8
67.5°	87.2	94.7	103.0	113.1
70°	74.5	80.2	86.3	95.1
72.5°	60.9	67.1	72.8	79.8
75°	50.0	52.6	57.4	62.2
77.5°	38.6	42.1	44.7	48.7
80°	27.6	30.7	31.6	34.6
82.5°	18.4	20.2	21.9	22.8
85°	10.5	11.4	13.1	13.6
87.5°	3.9	4.4	5.3	6.1
90°	8.8	6.2	3.7	1.1
92.5°	23.5	24.4	25.4	26.3
95°	45.3	53.0	60.8	68.5
97.5°	65.7	84.8	104.0	123.2
100°	90.2	122.3	154.3	186.4
102.5°	254.5	255.0	255.4	255.9
105°	341.3	334.2	327.2	320.2
107.5°	412.5	406.7	400.8	395.0
110°	481.3	476.4	471.5	466.6

TEST NUMBER: P999473

CATALOG NUMBER: SA2XXRDIP-B290D1080UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	546.7	542.4	538.2	534.0
115°	617.5	613.6	609.6	605.6
117.5°	681.9	677.2	672.5	667.8
120°	747.8	744.3	740.8	737.3
122.5°	807.5	803.8	800.0	796.3
125°	865.4	862.4	859.3	856.3
127.5°	920.9	917.6	914.4	911.1
130°	974.0	970.2	966.5	962.7
132.5°	1024.5	1021.5	1018.4	1015.4
135°	1070.9	1067.1	1063.4	1059.6
137.5°	1114.4	1111.6	1108.8	1106.0
140°	1156.9	1155.0	1153.1	1151.2
142.5°	1194.1	1192.4	1190.8	1189.2
145°	1228.5	1228.7	1229.0	1229.2
147.5°	1261.8	1262.5	1263.2	1263.9
150°	1292.8	1294.4	1296.1	1297.7
152.5°	1320.5	1322.4	1324.2	1326.1
155°	1347.2	1349.3	1351.4	1353.5
157.5°	1370.0	1371.9	1373.7	1375.6
160°	1390.3	1391.8	1393.2	1394.6
162.5°	1407.2	1408.6	1410.0	1411.4
165°	1421.9	1423.4	1424.8	1426.2
167.5°	1433.5	1434.9	1436.3	1437.7
170°	1443.0	1444.4	1445.8	1447.2
172.5°	1449.3	1450.7	1452.1	1453.5
175°	1453.9	1455.5	1457.2	1458.8
177.5°	1456.0	1457.6	1459.3	1460.9
180°	1455.6	1455.6	1455.6	1455.6

(END OF REPORT)