

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999631

Luminaire Tested: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999631
REPORT IS A COMBINATION OF REPORTS P988184 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4724.0 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	31	31	23
1	92	88	84	81	82	78	75	73	60	58	57	44	42	41	28	28	27	27	27	20
2	84	77	72	67	75	69	64	60	53	50	47	39	37	35	25	24	23	23	23	17
3	77	68	61	56	68	61	55	51	47	43	40	35	32	30	23	21	20	20	20	15
4	70	61	53	48	62	54	48	43	42	38	35	31	28	26	21	19	18	18	18	14
5	65	54	46	41	57	48	42	37	38	33	30	28	25	23	19	17	16	16	16	12
6	60	48	41	35	53	43	37	32	34	30	26	25	22	20	17	15	14	14	14	11
7	55	44	36	31	49	39	33	28	31	26	23	23	20	18	16	14	13	13	13	10
8	51	40	32	27	45	36	29	25	28	24	20	21	18	16	15	13	11	11	11	9
9	48	36	29	24	42	33	27	22	26	21	18	19	17	14	14	12	10	10	10	8
10	44	33	26	22	40	30	24	20	24	19	16	18	15	13	13	11	10	10	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9984	9984	9984	9984
5°	10008	10604	10043	8472
10°	9898	11209	9968	6996
15°	9683	11212	9847	5256
20°	9425	9268	9629	4336
25°	9110	5791	9307	3688
30°	8712	3709	8948	3175
35°	8225	2850	8491	2718
40°	7683	2395	8011	2377
45°	7102	2038	7399	1996
50°	6509	1733	6813	1726
55°	5851	1506	6166	1486
60°	5268	1148	5547	1134
65°	4721	865	5002	980
70°	4119	690	4443	798
75°	3479	528	3798	605
80°	2762	359	2978	395
85°	1921	186	2105	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 9134 cd/sqm

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	1.3
10°-20°	167.0	3.5
20°-30°	214.9	4.5
30°-40°	203.9	4.3
40°-50°	174.7	3.7
50°-60°	133.1	2.8
60°-70°	83.9	1.8
70°-80°	41.9	0.9
80°-90°	12.9	0.3
90°-100°	40.9	0.9
100°-110°	152.3	3.2
110°-120°	403.9	8.5
120°-130°	669.8	14.2
130°-140°	711.5	15.1
140°-150°	661.3	14.0
150°-160°	531.6	11.3
160°-170°	342.6	7.3
170°-180°	117.9	2.5
0°-30°	441.7	9.4
0°-40°	645.6	13.7
0°-60°	953.4	20.2
0°-90°	1092.2	23.1
90°-120°	597.0	12.6
90°-150°	2639.7	55.9
90°-180°	3632.0	76.9
0°-180°	4724.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	631	631	631	631	631	
5°	631	702	633	561	631	60
15°	595	792	605	371	595	167
25°	528	422	539	269	528	242
35°	433	208	447	199	433	271
45°	325	145	339	142	325	251
55°	220	100	231	99	220	198
65°	133	52	141	59	133	132
75°	62	28	68	32	62	67
85°	14	8	15	8	14	15
90°	1	24	1	24	1	4
95°	58	38	58	38	58	69
105°	272	68	272	68	272	291
115°	515	74	515	74	515	507
125°	729	766	729	766	729	650
135°	902	931	902	931	902	697
145°	1046	1062	1046	1062	1046	654
155°	1152	1153	1152	1153	1152	531
165°	1214	1211	1214	1211	1214	343
175°	1242	1234	1242	1234	1242	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	634.7	637.3	638.6	640.4	644.3	647.0	650.9	651.8	651.3	653.1	648.3
5°	631.2	636.9	642.1	646.5	653.5	657.9	662.7	668.4	669.8	676.3	672.4
7.5°	626.4	634.7	642.1	650.9	661.4	667.1	674.6	683.3	687.3	695.2	697.4
10°	618.5	630.3	643.0	652.2	666.7	676.8	683.8	697.8	707.0	718.8	717.1
12.5°	605.8	621.1	638.2	653.5	672.4	679.0	692.1	706.6	718.4	729.4	739.0
15°	594.8	612.3	631.2	650.0	671.5	683.8	696.9	715.8	728.5	747.8	756.1
17.5°	579.9	602.3	624.6	645.6	671.1	685.1	701.3	719.7	738.6	757.0	763.6
20°	564.6	588.7	612.8	641.3	670.2	683.8	700.4	723.2	741.6	756.1	756.1
22.5°	546.1	575.5	603.1	630.3	661.9	681.6	698.7	725.4	738.6	741.6	729.8
25°	527.7	557.1	587.3	621.1	657.0	674.6	693.9	718.8	723.2	711.0	680.3
27.5°	505.8	538.7	572.9	609.3	647.0	668.9	686.4	703.1	694.7	661.9	614.1
30°	483.5	519.0	557.5	592.2	637.8	657.9	672.8	677.6	651.3	597.9	536.1
32.5°	460.2	494.9	535.6	577.3	623.3	642.6	652.2	639.5	591.3	523.8	448.4
35°	433.1	472.1	514.6	558.0	603.6	618.0	623.7	592.6	530.8	443.6	368.6
37.5°	408.5	447.5	493.1	537.4	581.6	589.5	583.8	535.2	456.7	370.4	297.2
40°	379.6	421.2	465.9	515.5	551.8	554.0	540.0	476.9	379.6	298.5	253.3
42.5°	352.8	394.9	439.6	490.0	517.7	510.2	491.4	408.5	316.9	257.3	220.9
45°	325.2	365.1	413.3	458.0	477.8	460.2	431.7	343.6	266.1	221.4	193.3
47.5°	298.5	335.8	383.5	426.5	430.0	410.3	376.5	288.0	230.6	194.6	171.8
50°	272.2	309.5	354.2	389.7	386.2	359.0	320.8	250.3	200.3	171.8	153.0
52.5°	245.9	279.6	323.0	351.1	336.2	309.9	272.2	212.1	174.9	149.9	135.4
55°	219.6	251.2	288.4	311.6	288.0	257.7	231.0	181.9	151.7	131.5	120.5
57.5°	197.7	222.7	256.9	270.9	242.4	218.7	195.5	156.5	131.5	117.0	104.3
60°	173.6	196.4	224.4	232.7	203.4	184.1	164.4	132.4	112.6	99.9	91.6
62.5°	153.0	171.8	193.3	193.3	167.4	153.0	138.1	110.9	94.7	84.6	80.7
65°	132.8	146.4	161.7	160.0	138.1	125.4	113.5	91.6	79.3	72.3	68.4
67.5°	113.1	123.6	133.7	127.6	111.8	100.8	89.9	74.1	65.7	60.9	55.7
70°	95.1	103.4	108.7	103.0	87.2	78.0	70.1	59.6	53.0	46.9	43.8
72.5°	79.8	83.3	85.0	78.0	64.9	59.6	53.9	46.5	40.8	37.7	36.8
75°	62.2	65.3	64.0	58.7	47.8	43.8	39.4	34.2	32.9	31.1	30.2
77.5°	48.7	48.7	46.5	41.6	34.2	31.1	29.4	26.7	25.4	25.0	24.1
80°	34.6	34.2	32.9	27.6	23.2	21.5	21.5	19.7	19.3	18.4	18.4
82.5°	22.8	22.8	21.0	16.7	15.3	14.9	14.5	13.6	13.6	13.1	13.1
85°	13.6	12.7	10.5	9.2	8.8	8.8	8.3	7.9	8.3	7.9	7.9
87.5°	6.1	4.8	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
90°	0.9	3.1	5.3	7.5	9.7	10.8	11.6	13.2	14.7	16.3	17.9
92.5°	22.4	21.6	20.8	20.0	19.2	18.8	19.1	19.7	20.3	20.9	21.5
95°	58.3	51.7	45.1	38.6	32.0	28.7	29.4	30.8	32.2	33.6	35.0
97.5°	104.9	88.6	72.2	55.9	39.6	31.4	33.0	36.2	39.3	42.5	45.7
100°	158.7	131.4	104.1	76.8	49.5	35.9	37.6	41.0	44.3	47.7	51.1
102.5°	217.8	217.4	217.0	216.6	216.2	216.0	197.9	161.6	125.4	89.1	52.9
105°	272.5	278.5	284.5	290.4	296.4	299.4	272.2	217.8	163.5	109.1	54.7
107.5°	336.2	341.2	346.2	351.1	356.1	358.6	325.0	257.9	190.8	123.6	56.5
110°	397.1	401.3	405.5	409.6	413.8	415.9	387.1	329.6	272.0	214.5	156.9

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	454.5	458.1	461.7	465.2	468.8	470.6	468.9	465.5	462.2	458.8	455.4
115°	515.4	518.8	522.2	525.6	529.0	530.7	533.2	538.2	543.1	548.1	553.1
117.5°	568.3	572.3	576.3	580.2	584.2	586.2	587.9	591.3	594.7	598.1	601.5
120°	627.5	630.5	633.5	636.4	639.4	640.9	642.7	646.3	649.9	653.5	657.1
122.5°	677.7	680.9	684.1	687.2	690.4	692.0	694.0	698.0	702.0	706.0	710.0
125°	728.8	731.4	734.0	736.5	739.1	740.4	742.3	746.1	749.9	753.7	757.5
127.5°	775.4	778.2	781.0	783.7	786.5	787.9	789.4	792.4	795.4	798.4	801.4
130°	819.3	822.5	825.7	828.9	832.1	833.7	834.8	837.0	839.1	841.3	843.5
132.5°	864.1	866.7	869.3	871.9	874.5	875.8	876.9	879.1	881.2	883.4	885.6
135°	901.8	905.0	908.2	911.3	914.5	916.1	917.0	918.8	920.6	922.4	924.2
137.5°	941.2	943.6	946.0	948.4	950.8	952.0	953.0	955.0	956.9	958.9	960.9
140°	979.8	981.4	983.0	984.5	986.1	986.9	988.0	990.2	992.4	994.6	996.8
142.5°	1012.0	1013.4	1014.8	1016.2	1017.6	1018.3	1019.6	1022.2	1024.8	1027.4	1030.0
145°	1046.1	1045.9	1045.7	1045.5	1045.3	1045.2	1046.9	1050.3	1053.6	1057.0	1060.4
147.5°	1075.7	1075.1	1074.5	1073.9	1073.3	1073.0	1074.7	1078.1	1081.4	1084.8	1088.2
150°	1104.4	1103.0	1101.6	1100.2	1098.8	1098.1	1099.7	1102.9	1106.0	1109.2	1112.4
152.5°	1128.6	1127.0	1125.4	1123.8	1122.2	1121.4	1122.9	1125.9	1128.8	1131.8	1134.8
155°	1151.9	1150.1	1148.3	1146.5	1144.7	1143.8	1145.0	1147.4	1149.8	1152.2	1154.6
157.5°	1170.7	1169.1	1167.5	1165.9	1164.3	1163.5	1164.4	1166.2	1168.0	1169.8	1171.6
160°	1186.8	1185.6	1184.4	1183.3	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8
162.5°	1201.2	1200.0	1198.8	1197.6	1196.4	1195.8	1196.3	1197.3	1198.3	1199.3	1200.3
165°	1213.7	1212.5	1211.3	1210.2	1209.0	1208.4	1208.7	1209.3	1209.8	1210.4	1211.0
167.5°	1223.6	1222.4	1221.2	1220.0	1218.8	1218.2	1218.5	1219.1	1219.7	1220.3	1220.9
170°	1231.7	1230.5	1229.3	1228.1	1226.9	1226.3	1226.5	1226.9	1227.3	1227.7	1228.1
172.5°	1237.0	1235.8	1234.6	1233.5	1232.3	1231.7	1231.9	1232.3	1232.7	1233.1	1233.5
175°	1241.5	1240.1	1238.7	1237.3	1235.9	1235.2	1235.4	1235.8	1236.2	1236.6	1237.0
177.5°	1243.3	1241.9	1240.5	1239.1	1237.7	1237.0	1237.1	1237.3	1237.5	1237.7	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	653.1	654.0	655.3	661.4	662.3	664.1	663.2	663.2	663.6	662.7	663.2
5°	681.1	682.5	689.0	696.5	698.2	696.5	698.7	701.7	701.7	701.7	700.9
7.5°	707.4	712.3	719.7	730.7	732.9	735.1	739.0	736.4	737.3	741.2	739.9
10°	732.9	739.9	748.2	757.4	762.2	765.3	767.1	771.0	780.2	769.7	773.6
12.5°	757.0	767.1	775.8	785.9	789.4	793.4	794.7	798.2	798.2	797.7	800.8
15°	772.8	782.0	789.9	796.4	797.3	796.4	795.5	796.0	797.3	792.0	795.1
17.5°	776.3	777.1	779.8	777.1	777.6	768.4	763.1	761.8	749.5	750.0	760.0
20°	759.2	744.3	740.3	725.9	717.1	693.4	692.5	686.0	660.1	668.0	666.2
22.5°	712.3	686.8	653.1	636.4	628.1	603.1	583.8	570.3	561.0	551.8	547.9
25°	650.5	609.3	561.5	528.6	523.8	500.6	465.1	448.4	428.7	422.5	433.1
27.5°	570.7	517.2	463.3	412.9	403.7	382.7	364.7	352.8	330.1	328.7	329.6
30°	462.4	408.5	363.4	330.5	307.7	298.1	286.2	277.5	268.3	271.8	272.6
32.5°	380.0	328.7	286.7	269.1	258.6	252.5	242.4	236.7	232.7	231.4	231.0
35°	302.0	267.8	249.0	231.9	225.7	221.4	213.9	211.3	207.8	208.2	208.2
37.5°	258.6	230.1	216.1	207.3	201.6	199.4	194.6	192.0	189.8	188.9	190.2
40°	223.1	203.4	194.6	186.7	181.9	181.0	178.4	175.3	172.7	173.1	174.5
42.5°	197.2	185.8	175.3	169.2	165.7	164.4	162.2	160.0	160.0	158.7	158.2
45°	176.6	167.4	158.7	153.0	150.8	149.0	146.4	146.0	144.2	144.6	145.1
47.5°	158.2	150.8	144.2	138.5	136.3	135.9	133.2	131.5	131.5	131.1	130.6
50°	141.6	134.1	128.4	125.4	122.3	121.4	121.0	120.5	119.7	119.7	120.1
52.5°	128.0	120.5	116.2	113.5	111.8	110.9	110.9	110.5	110.5	110.5	110.0
55°	113.1	106.9	103.4	102.6	101.7	101.3	100.8	99.9	99.5	100.4	99.5
57.5°	99.1	96.9	93.8	92.9	90.7	90.7	89.4	88.5	87.7	88.5	88.5
60°	88.1	85.0	83.3	80.7	78.9	77.1	75.0	74.5	73.6	73.2	72.8
62.5°	76.7	74.1	69.7	65.7	63.1	61.4	60.5	60.0	60.0	59.6	59.6
65°	64.0	57.9	55.7	54.4	53.9	53.5	52.6	52.2	52.6	52.2	52.6
67.5°	50.0	49.1	47.8	46.9	46.5	46.0	46.0	45.6	45.6	45.6	45.6
70°	43.4	41.2	40.8	39.9	39.9	39.4	39.4	39.4	39.4	39.0	39.9
72.5°	35.9	34.6	34.2	33.8	33.8	33.8	33.3	33.3	33.3	32.9	33.3
75°	29.4	28.9	28.1	28.1	27.6	28.1	27.6	27.6	27.2	27.6	27.6
77.5°	23.7	23.2	22.8	22.8	22.4	22.4	22.4	22.4	22.4	22.4	22.8
80°	18.0	17.5	17.1	17.5	17.1	17.5	17.1	17.1	17.5	17.1	17.1
82.5°	13.1	12.7	12.7	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3
85°	7.9	7.5	7.5	7.9	7.5	7.9	7.5	7.5	7.5	7.9	7.9
87.5°	3.5	3.9	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.9
90°	18.9	19.9	20.9	21.9	22.4	22.6	23.0	23.4	23.8	24.2	23.8
92.5°	21.9	22.3	22.7	23.1	23.3	23.4	23.6	23.8	24.0	24.2	24.0
95°	36.0	37.0	37.9	38.9	39.4	39.3	39.1	38.9	38.7	38.5	38.7
97.5°	46.3	46.9	47.5	48.1	48.4	48.5	48.7	48.9	49.1	49.3	49.1
100°	52.7	54.3	55.9	57.5	58.3	58.5	58.9	59.3	59.7	60.1	59.7
102.5°	55.1	57.3	59.4	61.6	62.7	63.0	63.6	64.2	64.8	65.4	64.8
105°	56.9	59.1	61.2	63.4	64.5	64.9	65.7	66.5	67.3	68.1	67.3
107.5°	58.7	60.9	63.0	65.2	66.3	66.7	67.5	68.3	69.1	69.9	69.1
110°	137.0	117.0	97.1	77.2	67.2	67.6	68.4	69.2	70.0	70.8	70.0

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	369.5	283.7	197.8	111.9	69.0	69.3	69.9	70.5	71.1	71.7	71.1
115°	460.9	368.6	276.4	184.1	138.0	130.8	116.5	102.2	87.8	73.5	87.8
117.5°	573.0	544.5	516.0	487.5	473.3	447.2	395.0	342.8	290.6	238.4	290.6
120°	659.5	661.9	664.2	666.6	667.8	654.4	627.5	600.6	573.7	546.8	573.7
122.5°	711.2	712.4	713.5	714.7	715.3	715.4	715.6	715.8	716.0	716.2	716.0
125°	758.9	760.3	761.6	763.0	763.7	764.0	764.6	765.2	765.8	766.4	765.8
127.5°	803.4	805.4	807.4	809.4	810.4	810.5	810.7	810.8	811.0	811.2	811.0
130°	845.7	847.9	850.1	852.3	853.4	853.3	853.1	852.9	852.7	852.5	852.7
132.5°	887.4	889.2	891.0	892.8	893.7	893.6	893.4	893.2	893.0	892.8	893.0
135°	926.2	928.2	930.2	932.2	933.2	933.0	932.6	932.2	931.8	931.4	931.8
137.5°	962.9	964.9	966.9	968.9	969.9	969.6	969.0	968.4	967.8	967.2	967.8
140°	998.6	1000.4	1002.2	1004.0	1004.9	1004.4	1003.4	1002.4	1001.4	1000.4	1001.4
142.5°	1031.6	1033.2	1034.7	1036.3	1037.1	1036.6	1035.6	1034.7	1033.7	1032.7	1033.7
145°	1061.8	1063.2	1064.6	1066.0	1066.7	1066.2	1065.2	1064.2	1063.2	1062.2	1063.2
147.5°	1089.2	1090.2	1091.2	1092.2	1092.7	1092.3	1091.5	1090.7	1089.9	1089.1	1089.9
150°	1113.6	1114.8	1116.0	1117.2	1117.8	1117.3	1116.3	1115.3	1114.3	1113.3	1114.3
152.5°	1136.0	1137.2	1138.4	1139.6	1140.2	1139.5	1138.1	1136.8	1135.4	1134.0	1135.4
155°	1155.8	1157.0	1158.1	1159.3	1159.9	1159.1	1157.5	1156.0	1154.4	1152.8	1154.4
157.5°	1173.0	1174.4	1175.8	1177.2	1177.9	1177.1	1175.5	1173.9	1172.3	1170.7	1172.3
160°	1188.0	1189.2	1190.4	1191.6	1192.2	1191.5	1190.1	1188.7	1187.3	1185.9	1187.3
162.5°	1201.7	1203.1	1204.5	1205.9	1206.6	1205.7	1203.9	1202.1	1200.3	1198.5	1200.3
165°	1212.4	1213.8	1215.2	1216.6	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1212.4
167.5°	1222.3	1223.7	1225.1	1226.5	1227.2	1226.3	1224.5	1222.7	1220.9	1219.1	1220.9
170°	1229.5	1230.9	1232.2	1233.6	1234.3	1233.4	1231.6	1229.9	1228.1	1226.3	1228.1
172.5°	1234.9	1236.3	1237.6	1239.0	1239.7	1238.8	1237.0	1235.3	1233.5	1231.7	1233.5
175°	1238.4	1239.8	1241.2	1242.6	1243.3	1242.3	1240.3	1238.3	1236.3	1234.3	1236.3
177.5°	1239.3	1240.7	1242.1	1243.5	1244.2	1243.3	1241.5	1239.7	1237.9	1236.1	1237.9
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	664.9	661.9	661.0	661.9	661.0	661.4	658.4	647.0	650.0	645.2	647.8
5°	702.6	700.0	694.3	693.4	692.5	691.7	687.3	677.2	673.3	666.7	666.2
7.5°	738.6	738.6	734.2	731.1	727.2	724.1	718.4	703.5	697.4	689.5	685.1
10°	774.1	762.7	767.5	764.4	754.8	753.0	742.5	733.7	721.9	714.0	707.0
12.5°	799.5	796.0	791.6	789.0	786.3	780.6	773.6	751.3	745.1	729.4	721.5
15°	798.6	796.4	797.7	797.7	796.9	795.5	789.9	773.6	763.1	747.8	734.2
17.5°	755.7	761.4	767.1	771.0	779.8	783.7	789.0	779.3	772.8	759.6	745.1
20°	680.7	694.7	711.4	714.9	722.8	746.0	756.5	764.9	767.5	763.1	751.3
22.5°	576.4	588.2	628.6	627.7	639.1	666.7	697.4	722.4	742.1	753.0	748.6
25°	451.5	468.1	489.6	505.8	543.1	584.3	622.4	662.3	696.5	726.7	734.2
27.5°	341.5	363.4	380.5	401.9	420.8	469.4	518.5	580.8	620.7	678.1	707.9
30°	276.1	286.2	303.3	313.4	322.6	359.9	415.5	476.9	547.0	613.2	664.5
32.5°	235.8	242.8	255.5	259.9	269.6	294.6	329.6	385.7	458.0	538.3	605.8
35°	211.7	219.2	221.8	225.7	233.6	249.4	273.5	314.3	379.6	458.0	538.7
37.5°	191.1	195.1	202.5	205.1	207.8	219.6	235.8	264.3	307.7	372.1	461.6
40°	176.6	178.8	182.8	185.0	186.7	195.1	209.5	228.8	260.8	309.9	392.3
42.5°	161.3	163.9	166.6	169.2	171.4	178.0	186.7	205.1	226.6	263.9	323.5
45°	146.4	148.2	151.2	153.0	156.0	161.3	169.2	181.9	201.2	224.9	273.1
47.5°	132.8	135.0	136.3	138.5	140.7	146.4	153.9	162.2	178.0	201.2	236.3
50°	120.5	123.2	124.9	125.4	127.1	132.4	138.5	147.7	157.8	175.8	206.4
52.5°	111.8	112.2	113.5	115.3	114.8	117.9	123.6	130.6	141.1	155.6	178.0
55°	101.7	103.0	103.9	104.3	104.3	106.9	110.0	116.6	124.9	136.8	155.6
57.5°	89.0	90.3	92.9	93.8	95.1	96.4	97.7	102.1	109.1	120.5	135.9
60°	75.8	76.7	79.3	81.1	82.0	85.5	87.2	90.7	94.7	103.0	117.5
62.5°	60.9	61.8	63.1	64.9	66.6	71.9	76.3	79.8	82.8	88.5	100.4
65°	53.0	53.5	54.4	54.8	55.2	57.4	61.4	66.2	71.9	76.3	83.3
67.5°	46.0	46.5	46.9	47.8	48.2	48.7	50.4	51.7	57.4	63.6	68.8
70°	39.4	40.3	40.8	40.8	41.2	42.1	43.0	44.7	46.5	49.5	56.1
72.5°	33.3	33.8	34.6	34.6	34.6	35.5	36.4	37.3	38.1	39.9	42.5
75°	27.6	28.5	28.5	28.5	28.9	28.9	29.8	30.7	31.6	32.9	33.8
77.5°	22.8	22.8	22.8	22.8	23.2	23.2	23.7	24.5	25.0	25.4	26.3
80°	17.1	17.5	17.5	17.5	18.0	18.0	18.0	18.8	19.3	19.3	20.2
82.5°	12.7	12.7	12.7	13.1	12.7	13.1	13.1	13.6	13.1	13.6	14.0
85°	7.9	7.9	7.9	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.8
87.5°	3.9	3.9	3.9	3.9	3.9	3.9	3.9	3.9	4.4	3.9	3.9
90°	23.4	23.0	22.6	22.4	21.9	20.9	19.9	18.9	17.9	16.3	14.7
92.5°	23.8	23.6	23.4	23.3	23.1	22.7	22.3	21.9	21.5	20.9	20.3
95°	38.9	39.1	39.3	39.4	38.9	37.9	37.0	36.0	35.0	33.6	32.2
97.5°	48.9	48.7	48.5	48.4	48.1	47.5	46.9	46.3	45.7	42.5	39.3
100°	59.3	58.9	58.5	58.3	57.5	55.9	54.3	52.7	51.1	47.7	44.3
102.5°	64.2	63.6	63.0	62.7	61.6	59.4	57.3	55.1	52.9	49.1	45.4
105°	66.5	65.7	64.9	64.5	63.4	61.2	59.1	56.9	54.7	50.9	47.1
107.5°	68.3	67.5	66.7	66.3	65.2	63.0	60.9	58.7	56.5	52.6	48.7
110°	69.2	68.4	67.6	67.2	77.2	97.1	117.0	137.0	156.9	214.5	272.0

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	70.5	69.9	69.3	69.0	111.9	197.8	283.7	369.5	455.4	458.8	462.2
115°	102.2	116.5	130.8	138.0	184.1	276.4	368.6	460.9	553.1	548.1	543.1
117.5°	342.8	395.0	447.2	473.3	487.5	516.0	544.5	573.0	601.5	598.1	594.7
120°	600.6	627.5	654.4	667.8	666.6	664.2	661.9	659.5	657.1	653.5	649.9
122.5°	715.8	715.6	715.4	715.3	714.7	713.5	712.4	711.2	710.0	706.0	702.0
125°	765.2	764.6	764.0	763.7	763.0	761.6	760.3	758.9	757.5	753.7	749.9
127.5°	810.8	810.7	810.5	810.4	809.4	807.4	805.4	803.4	801.4	798.4	795.4
130°	852.9	853.1	853.3	853.4	852.3	850.1	847.9	845.7	843.5	841.3	839.1
132.5°	893.2	893.4	893.6	893.7	892.8	891.0	889.2	887.4	885.6	883.4	881.2
135°	932.2	932.6	933.0	933.2	932.2	930.2	928.2	926.2	924.2	922.4	920.6
137.5°	968.4	969.0	969.6	969.9	968.9	966.9	964.9	962.9	960.9	958.9	956.9
140°	1002.4	1003.4	1004.4	1004.9	1004.0	1002.2	1000.4	998.6	996.8	994.6	992.4
142.5°	1034.7	1035.6	1036.6	1037.1	1036.3	1034.7	1033.2	1031.6	1030.0	1027.4	1024.8
145°	1064.2	1065.2	1066.2	1066.7	1066.0	1064.6	1063.2	1061.8	1060.4	1057.0	1053.6
147.5°	1090.7	1091.5	1092.3	1092.7	1092.2	1091.2	1090.2	1089.2	1088.2	1084.8	1081.4
150°	1115.3	1116.3	1117.3	1117.8	1117.2	1116.0	1114.8	1113.6	1112.4	1109.2	1106.0
152.5°	1136.8	1138.1	1139.5	1140.2	1139.6	1138.4	1137.2	1136.0	1134.8	1131.8	1128.8
155°	1156.0	1157.5	1159.1	1159.9	1159.3	1158.1	1157.0	1155.8	1154.6	1152.2	1149.8
157.5°	1173.9	1175.5	1177.1	1177.9	1177.2	1175.8	1174.4	1173.0	1171.6	1169.8	1168.0
160°	1188.7	1190.1	1191.5	1192.2	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1184.4
162.5°	1202.1	1203.9	1205.7	1206.6	1205.9	1204.5	1203.1	1201.7	1200.3	1199.3	1198.3
165°	1213.8	1215.2	1216.6	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1210.4	1209.8
167.5°	1222.7	1224.5	1226.3	1227.2	1226.5	1225.1	1223.7	1222.3	1220.9	1220.3	1219.7
170°	1229.9	1231.6	1233.4	1234.3	1233.6	1232.2	1230.9	1229.5	1228.1	1227.7	1227.3
172.5°	1235.3	1237.0	1238.8	1239.7	1239.0	1237.6	1236.3	1234.9	1233.5	1233.1	1232.7
175°	1238.3	1240.3	1242.3	1243.3	1242.6	1241.2	1239.8	1238.4	1237.0	1236.6	1236.2
177.5°	1239.7	1241.5	1243.3	1244.2	1243.5	1242.1	1240.7	1239.3	1237.9	1237.7	1237.5
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	643.9	641.7	641.7	640.4	640.4	633.4	633.4	635.6	632.9	629.9	625.5
5°	660.5	655.7	654.4	652.7	647.0	638.2	634.7	633.4	628.1	621.5	614.1
7.5°	676.3	668.4	664.5	660.5	653.1	640.8	633.8	629.0	621.1	611.0	601.4
10°	691.7	681.6	671.5	666.7	656.2	640.8	630.7	622.9	611.5	597.9	584.3
12.5°	705.7	684.7	682.9	673.3	657.9	640.4	625.0	613.6	599.2	583.4	567.6
15°	718.0	696.5	686.0	677.2	657.0	635.1	618.9	604.9	585.6	567.6	548.3
17.5°	724.1	700.9	693.9	679.4	658.8	630.3	608.4	591.3	570.3	548.8	526.9
20°	730.2	703.1	691.7	681.6	653.5	621.1	596.6	576.8	553.6	528.2	504.1
22.5°	733.3	703.1	689.5	675.5	648.3	611.0	582.1	558.9	531.7	505.8	476.9
25°	728.0	700.4	684.2	669.8	639.1	598.7	565.4	539.1	510.2	480.8	451.5
27.5°	714.9	694.3	675.5	660.5	626.4	583.0	547.9	518.1	488.3	455.4	425.6
30°	690.4	681.1	666.2	649.6	612.3	568.9	527.3	496.6	463.7	430.9	399.7
32.5°	652.2	660.1	650.5	636.0	595.7	549.7	505.4	474.3	438.3	402.8	374.3
35°	605.8	633.8	628.6	618.5	578.1	529.1	484.8	447.1	411.1	375.2	346.7
37.5°	554.9	597.4	601.8	595.7	558.0	508.0	459.4	422.5	385.7	349.3	320.4
40°	485.2	550.5	564.6	567.2	536.9	482.6	431.7	395.8	359.4	323.9	288.9
42.5°	421.2	503.6	521.2	532.1	510.2	457.6	406.3	366.4	330.5	298.5	263.4
45°	361.2	447.1	475.6	489.6	480.0	429.1	376.1	338.8	305.9	276.6	242.8
47.5°	299.4	385.7	425.6	448.0	448.0	400.2	347.1	310.3	278.8	253.8	224.0
50°	258.2	330.1	371.3	400.6	408.5	370.8	320.8	284.9	255.1	227.9	205.1
52.5°	220.0	284.5	318.7	349.3	372.1	339.3	291.5	259.0	229.7	204.3	186.3
55°	190.2	238.4	269.6	303.3	328.7	307.3	263.0	231.4	206.0	185.0	169.6
57.5°	161.7	203.8	229.2	259.0	286.2	270.0	234.5	207.3	185.0	166.6	153.0
60°	137.6	171.8	191.5	214.8	248.5	237.1	207.8	182.8	164.8	148.2	136.8
62.5°	117.0	144.2	160.9	177.5	208.2	202.9	180.1	160.9	145.5	131.5	121.9
65°	96.0	118.3	131.5	146.0	170.5	172.7	154.3	140.7	126.7	114.4	105.6
67.5°	77.6	95.1	106.9	119.2	138.9	145.1	132.4	121.0	109.1	99.1	91.2
70°	62.7	75.0	83.7	93.4	109.6	117.0	110.5	102.6	92.9	84.6	77.6
72.5°	49.5	57.4	62.7	70.1	83.3	90.7	90.3	83.3	76.3	70.6	64.9
75°	36.4	42.5	46.9	51.7	62.2	69.3	71.0	67.9	60.9	56.5	52.2
77.5°	27.6	31.1	33.3	36.8	44.3	50.4	53.0	52.2	47.3	43.8	40.8
80°	21.0	21.9	22.8	24.1	30.2	35.9	37.7	37.3	34.6	33.3	29.8
82.5°	14.9	15.3	15.8	16.2	18.4	23.2	25.0	25.9	23.7	22.4	19.3
85°	8.8	9.2	9.2	10.1	10.5	11.8	14.9	14.9	14.5	12.7	12.3
87.5°	4.4	4.4	3.9	3.9	4.4	4.8	5.7	6.6	5.7	5.3	4.8
90°	13.2	11.6	10.8	9.7	7.5	5.3	3.1	0.9	3.1	5.3	7.5
92.5°	19.7	19.1	18.8	19.2	20.0	20.8	21.6	22.4	21.6	20.8	20.0
95°	30.8	29.4	28.7	32.0	38.6	45.1	51.7	58.3	51.7	45.1	38.6
97.5°	36.2	33.0	31.4	39.6	55.9	72.2	88.6	104.9	88.6	72.2	55.9
100°	41.0	37.6	35.9	49.5	76.8	104.1	131.4	158.7	131.4	104.1	76.8
102.5°	161.6	197.9	216.0	216.2	216.6	217.0	217.4	217.8	217.4	217.0	216.6
105°	217.8	272.2	299.4	296.4	290.4	284.5	278.5	272.5	278.5	284.5	290.4
107.5°	257.9	325.0	358.6	356.1	351.1	346.2	341.2	336.2	341.2	346.2	351.1
110°	329.6	387.1	415.9	413.8	409.6	405.5	401.3	397.1	401.3	405.5	409.6

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	465.5	468.9	470.6	468.8	465.2	461.7	458.1	454.5	458.1	461.7	465.2
115°	538.2	533.2	530.7	529.0	525.6	522.2	518.8	515.4	518.8	522.2	525.6
117.5°	591.3	587.9	586.2	584.2	580.2	576.3	572.3	568.3	572.3	576.3	580.2
120°	646.3	642.7	640.9	639.4	636.4	633.5	630.5	627.5	630.5	633.5	636.4
122.5°	698.0	694.0	692.0	690.4	687.2	684.1	680.9	677.7	680.9	684.1	687.2
125°	746.1	742.3	740.4	739.1	736.5	734.0	731.4	728.8	731.4	734.0	736.5
127.5°	792.4	789.4	787.9	786.5	783.7	781.0	778.2	775.4	778.2	781.0	783.7
130°	837.0	834.8	833.7	832.1	828.9	825.7	822.5	819.3	822.5	825.7	828.9
132.5°	879.1	876.9	875.8	874.5	871.9	869.3	866.7	864.1	866.7	869.3	871.9
135°	918.8	917.0	916.1	914.5	911.3	908.2	905.0	901.8	905.0	908.2	911.3
137.5°	955.0	953.0	952.0	950.8	948.4	946.0	943.6	941.2	943.6	946.0	948.4
140°	990.2	988.0	986.9	986.1	984.5	983.0	981.4	979.8	981.4	983.0	984.5
142.5°	1022.2	1019.6	1018.3	1017.6	1016.2	1014.8	1013.4	1012.0	1013.4	1014.8	1016.2
145°	1050.3	1046.9	1045.2	1045.3	1045.5	1045.7	1045.9	1046.1	1045.9	1045.7	1045.5
147.5°	1078.1	1074.7	1073.0	1073.3	1073.9	1074.5	1075.1	1075.7	1075.1	1074.5	1073.9
150°	1102.9	1099.7	1098.1	1098.8	1100.2	1101.6	1103.0	1104.4	1103.0	1101.6	1100.2
152.5°	1125.9	1122.9	1121.4	1122.2	1123.8	1125.4	1127.0	1128.6	1127.0	1125.4	1123.8
155°	1147.4	1145.0	1143.8	1144.7	1146.5	1148.3	1150.1	1151.9	1150.1	1148.3	1146.5
157.5°	1166.2	1164.4	1163.5	1164.3	1165.9	1167.5	1169.1	1170.7	1169.1	1167.5	1165.9
160°	1183.3	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8	1185.6	1184.4	1183.3
162.5°	1197.3	1196.3	1195.8	1196.4	1197.6	1198.8	1200.0	1201.2	1200.0	1198.8	1197.6
165°	1209.3	1208.7	1208.4	1209.0	1210.2	1211.3	1212.5	1213.7	1212.5	1211.3	1210.2
167.5°	1219.1	1218.5	1218.2	1218.8	1220.0	1221.2	1222.4	1223.6	1222.4	1221.2	1220.0
170°	1226.9	1226.5	1226.3	1226.9	1228.1	1229.3	1230.5	1231.7	1230.5	1229.3	1228.1
172.5°	1232.3	1231.9	1231.7	1232.3	1233.5	1234.6	1235.8	1237.0	1235.8	1234.6	1233.5
175°	1235.8	1235.4	1235.2	1235.9	1237.3	1238.7	1240.1	1241.5	1240.1	1238.7	1237.3
177.5°	1237.3	1237.1	1237.0	1237.7	1239.1	1240.5	1241.9	1243.3	1241.9	1240.5	1239.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	623.7	624.2	625.5	621.5	615.4	612.8	604.9	603.6	602.3	602.3	603.6
5°	609.7	607.9	608.4	600.9	592.2	586.9	576.0	577.7	572.0	568.5	569.4
7.5°	594.4	589.5	589.1	579.5	568.5	558.9	547.5	544.8	539.6	533.4	530.8
10°	575.1	571.6	565.0	554.0	540.0	532.1	516.8	507.6	506.3	497.1	493.5
12.5°	555.4	549.2	542.6	527.3	511.5	498.8	487.4	477.3	470.3	462.4	457.2
15°	532.6	525.1	517.7	501.4	483.0	470.3	453.2	438.3	417.7	401.5	392.3
17.5°	507.6	499.2	489.2	471.2	453.2	435.7	404.1	386.6	372.1	362.5	356.8
20°	481.7	472.5	462.4	444.5	413.3	382.7	365.1	351.5	342.8	333.1	326.1
22.5°	454.5	444.9	433.9	405.9	373.0	351.5	337.9	325.2	312.5	307.3	303.8
25°	429.1	420.3	406.3	368.2	342.3	322.6	307.3	298.9	292.4	285.3	278.8
27.5°	402.8	386.6	366.9	334.9	318.7	298.5	287.5	281.4	270.0	265.2	262.1
30°	371.3	353.3	334.4	311.6	292.8	278.8	268.7	258.6	252.0	247.2	242.0
32.5°	339.3	322.2	310.3	286.7	272.6	258.2	248.5	242.4	232.7	229.7	227.5
35°	311.6	297.2	286.7	267.4	254.2	241.1	234.1	224.9	218.7	213.0	209.5
37.5°	284.5	276.6	265.6	249.4	235.4	224.9	215.2	212.1	203.8	200.8	197.2
40°	265.6	253.8	244.6	230.6	218.7	207.3	201.2	194.2	188.5	183.7	182.3
42.5°	242.8	234.1	228.8	213.5	201.2	194.6	187.2	179.3	174.9	170.9	166.1
45°	225.7	217.8	210.4	198.1	187.2	178.8	172.3	167.0	159.5	157.8	150.3
47.5°	207.8	199.9	194.2	181.9	171.8	163.9	159.1	152.1	146.0	142.0	138.5
50°	189.8	183.2	178.0	167.4	158.7	150.3	143.8	136.8	134.1	127.6	125.4
52.5°	172.7	168.3	162.6	152.5	143.8	136.8	129.7	124.0	120.1	116.6	114.0
55°	158.2	151.2	148.6	137.6	130.2	122.7	116.6	113.1	108.3	106.1	103.9
57.5°	142.0	138.1	133.7	125.4	117.0	110.0	105.6	100.4	97.7	95.1	93.4
60°	128.0	122.3	118.8	111.8	104.3	97.7	93.8	89.9	86.3	84.2	80.7
62.5°	111.8	107.4	105.2	97.7	91.6	85.5	82.0	78.0	75.4	71.4	67.1
65°	97.7	94.2	91.6	85.5	79.8	74.1	70.6	65.7	62.2	60.0	59.6
67.5°	85.5	82.8	78.9	73.2	67.5	63.1	59.2	55.2	54.8	53.9	53.9
70°	71.9	69.3	67.1	60.9	56.1	51.3	50.4	49.1	47.8	47.3	46.5
72.5°	60.0	57.9	55.2	50.0	45.1	43.8	43.0	42.1	40.8	40.3	39.9
75°	48.7	45.6	43.8	39.0	37.7	36.8	35.9	34.6	33.8	33.3	32.4
77.5°	37.3	34.2	34.2	31.6	30.7	29.4	28.5	27.6	27.2	26.3	26.3
80°	26.3	26.3	25.4	24.1	22.8	22.4	21.0	20.6	20.2	20.6	19.7
82.5°	19.3	17.5	17.5	16.7	15.8	15.3	14.5	14.5	14.0	14.0	14.0
85°	11.0	11.0	10.5	9.6	9.2	9.2	8.8	8.8	8.3	8.3	7.9
87.5°	4.4	3.9	4.4	3.9	3.9	3.5	3.5	3.5	3.1	3.5	3.1
90°	9.7	10.8	11.6	13.2	14.7	16.3	17.9	18.9	19.9	20.9	21.9
92.5°	19.2	18.8	19.1	19.7	20.3	20.9	21.5	21.9	22.3	22.7	23.1
95°	32.0	28.7	29.4	30.8	32.2	33.6	35.0	36.0	37.0	37.9	38.9
97.5°	39.6	31.4	33.0	36.2	39.3	42.5	45.7	46.3	46.9	47.5	48.1
100°	49.5	35.9	37.6	41.0	44.3	47.7	51.1	52.7	54.3	55.9	57.5
102.5°	216.2	216.0	197.9	161.6	125.4	89.1	52.9	55.1	57.3	59.4	61.6
105°	296.4	299.4	272.2	217.8	163.5	109.1	54.7	56.9	59.1	61.2	63.4
107.5°	356.1	358.6	325.0	257.9	190.8	123.6	56.5	58.7	60.9	63.0	65.2
110°	413.8	415.9	387.1	329.6	272.0	214.5	156.9	137.0	117.0	97.1	77.2

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	468.8	470.6	468.9	465.5	462.2	458.8	455.4	369.5	283.7	197.8	111.9
115°	529.0	530.7	533.2	538.2	543.1	548.1	553.1	460.9	368.6	276.4	184.1
117.5°	584.2	586.2	587.9	591.3	594.7	598.1	601.5	573.0	544.5	516.0	487.5
120°	639.4	640.9	642.7	646.3	649.9	653.5	657.1	659.5	661.9	664.2	666.6
122.5°	690.4	692.0	694.0	698.0	702.0	706.0	710.0	711.2	712.4	713.5	714.7
125°	739.1	740.4	742.3	746.1	749.9	753.7	757.5	758.9	760.3	761.6	763.0
127.5°	786.5	787.9	789.4	792.4	795.4	798.4	801.4	803.4	805.4	807.4	809.4
130°	832.1	833.7	834.8	837.0	839.1	841.3	843.5	845.7	847.9	850.1	852.3
132.5°	874.5	875.8	876.9	879.1	881.2	883.4	885.6	887.4	889.2	891.0	892.8
135°	914.5	916.1	917.0	918.8	920.6	922.4	924.2	926.2	928.2	930.2	932.2
137.5°	950.8	952.0	953.0	955.0	956.9	958.9	960.9	962.9	964.9	966.9	968.9
140°	986.1	986.9	988.0	990.2	992.4	994.6	996.8	998.6	1000.4	1002.2	1004.0
142.5°	1017.6	1018.3	1019.6	1022.2	1024.8	1027.4	1030.0	1031.6	1033.2	1034.7	1036.3
145°	1045.3	1045.2	1046.9	1050.3	1053.6	1057.0	1060.4	1061.8	1063.2	1064.6	1066.0
147.5°	1073.3	1073.0	1074.7	1078.1	1081.4	1084.8	1088.2	1089.2	1090.2	1091.2	1092.2
150°	1098.8	1098.1	1099.7	1102.9	1106.0	1109.2	1112.4	1113.6	1114.8	1116.0	1117.2
152.5°	1122.2	1121.4	1122.9	1125.9	1128.8	1131.8	1134.8	1136.0	1137.2	1138.4	1139.6
155°	1144.7	1143.8	1145.0	1147.4	1149.8	1152.2	1154.6	1155.8	1157.0	1158.1	1159.3
157.5°	1164.3	1163.5	1164.4	1166.2	1168.0	1169.8	1171.6	1173.0	1174.4	1175.8	1177.2
160°	1182.1	1181.5	1182.1	1183.3	1184.4	1185.6	1186.8	1188.0	1189.2	1190.4	1191.6
162.5°	1196.4	1195.8	1196.3	1197.3	1198.3	1199.3	1200.3	1201.7	1203.1	1204.5	1205.9
165°	1209.0	1208.4	1208.7	1209.3	1209.8	1210.4	1211.0	1212.4	1213.8	1215.2	1216.6
167.5°	1218.8	1218.2	1218.5	1219.1	1219.7	1220.3	1220.9	1222.3	1223.7	1225.1	1226.5
170°	1226.9	1226.3	1226.5	1226.9	1227.3	1227.7	1228.1	1229.5	1230.9	1232.2	1233.6
172.5°	1232.3	1231.7	1231.9	1232.3	1232.7	1233.1	1233.5	1234.9	1236.3	1237.6	1239.0
175°	1235.9	1235.2	1235.4	1235.8	1236.2	1236.6	1237.0	1238.4	1239.8	1241.2	1242.6
177.5°	1237.7	1237.0	1237.1	1237.3	1237.5	1237.7	1237.9	1239.3	1240.7	1242.1	1243.5
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	603.6	602.7	600.1	600.9	599.6	599.6	598.7	598.7	598.7	600.9	599.6
5°	570.7	567.6	564.6	563.2	561.9	560.6	560.6	560.2	564.1	563.2	566.7
7.5°	529.9	529.1	522.9	522.9	520.7	519.8	522.0	522.5	522.9	523.8	526.0
10°	493.5	491.4	482.6	483.5	482.2	480.4	481.7	480.8	483.9	484.8	483.9
12.5°	450.6	446.6	437.0	432.2	426.9	423.0	427.8	424.3	436.6	440.1	449.7
15°	393.6	386.2	379.6	379.6	374.8	371.3	373.4	377.4	380.0	384.0	385.7
17.5°	355.5	352.4	347.1	344.1	342.8	341.5	341.5	343.2	348.9	348.5	352.0
20°	323.0	321.3	318.7	314.7	313.4	312.5	312.5	312.5	316.5	320.0	322.2
22.5°	300.7	299.4	297.6	292.4	289.7	288.9	291.0	292.4	295.4	298.1	300.2
25°	278.3	275.3	272.2	270.4	269.1	269.1	270.0	270.4	271.8	273.1	275.7
27.5°	259.9	257.7	253.3	248.5	248.5	247.2	248.1	249.0	252.0	256.4	258.6
30°	239.3	238.9	237.1	235.4	233.6	232.7	234.5	235.8	236.3	238.4	238.4
32.5°	224.4	221.4	218.3	216.5	215.7	215.2	215.7	217.4	217.4	220.0	223.1
35°	209.5	207.8	204.7	201.6	200.8	198.6	200.3	202.1	205.1	206.4	207.8
37.5°	193.3	191.1	189.8	188.9	187.2	187.6	186.3	188.9	191.5	191.1	192.0
40°	181.0	177.1	173.1	172.7	172.3	171.8	171.8	172.3	174.0	175.8	178.4
42.5°	165.2	163.9	160.4	156.9	156.0	155.2	154.3	156.0	159.5	162.6	163.9
45°	149.0	147.3	146.4	143.8	142.0	141.6	140.7	142.9	146.0	147.3	148.2
47.5°	134.1	133.7	131.1	131.5	130.2	130.6	130.2	131.5	131.5	132.8	133.7
50°	124.0	122.7	121.4	120.5	119.2	119.2	118.8	119.2	121.0	122.7	122.3
52.5°	114.0	111.8	111.3	110.9	110.0	110.9	109.6	110.0	111.8	112.6	112.2
55°	102.1	101.7	100.8	99.9	99.5	99.1	99.1	99.1	100.8	102.1	102.6
57.5°	92.9	90.7	89.0	89.0	87.2	86.8	87.7	88.1	89.4	90.3	91.2
60°	80.2	79.3	76.7	75.4	72.8	72.3	72.3	74.1	76.3	79.3	80.2
62.5°	66.6	65.3	64.9	64.9	64.9	64.9	64.9	64.9	64.9	65.3	65.3
65°	59.2	59.6	59.2	58.7	59.2	59.2	58.7	58.7	58.7	59.2	59.6
67.5°	53.0	52.6	53.0	52.6	52.2	52.2	51.7	52.2	52.6	53.0	53.0
70°	46.0	46.0	45.6	46.0	45.6	45.1	44.7	44.7	45.6	46.0	46.0
72.5°	39.4	39.4	39.0	39.0	38.1	38.1	38.6	38.1	38.1	39.4	39.4
75°	32.9	32.4	32.0	32.0	31.6	31.6	31.6	31.1	32.0	32.0	32.4
77.5°	25.9	25.9	25.9	25.4	25.4	25.0	25.0	25.4	25.4	25.4	25.9
80°	19.7	19.7	19.7	19.3	18.8	18.8	18.8	18.8	18.8	19.3	18.8
82.5°	13.6	13.6	13.6	13.6	13.6	13.1	13.1	13.1	13.6	13.6	13.1
85°	8.3	7.9	8.3	8.3	7.9	8.3	7.9	7.9	7.5	7.5	7.9
87.5°	3.5	3.1	2.6	2.6	3.1	2.6	2.6	2.6	3.1	2.6	2.6
90°	22.4	22.6	23.0	23.4	23.8	24.2	23.8	23.4	23.0	22.6	22.4
92.5°	23.3	23.4	23.6	23.8	24.0	24.2	24.0	23.8	23.6	23.4	23.3
95°	39.4	39.3	39.1	38.9	38.7	38.5	38.7	38.9	39.1	39.3	39.4
97.5°	48.4	48.5	48.7	48.9	49.1	49.3	49.1	48.9	48.7	48.5	48.4
100°	58.3	58.5	58.9	59.3	59.7	60.1	59.7	59.3	58.9	58.5	58.3
102.5°	62.7	63.0	63.6	64.2	64.8	65.4	64.8	64.2	63.6	63.0	62.7
105°	64.5	64.9	65.7	66.5	67.3	68.1	67.3	66.5	65.7	64.9	64.5
107.5°	66.3	66.7	67.5	68.3	69.1	69.9	69.1	68.3	67.5	66.7	66.3
110°	67.2	67.6	68.4	69.2	70.0	70.8	70.0	69.2	68.4	67.6	67.2

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	69.0	69.3	69.9	70.5	71.1	71.7	71.1	70.5	69.9	69.3	69.0
115°	138.0	130.8	116.5	102.2	87.8	73.5	87.8	102.2	116.5	130.8	138.0
117.5°	473.3	447.2	395.0	342.8	290.6	238.4	290.6	342.8	395.0	447.2	473.3
120°	667.8	654.4	627.5	600.6	573.7	546.8	573.7	600.6	627.5	654.4	667.8
122.5°	715.3	715.4	715.6	715.8	716.0	716.2	716.0	715.8	715.6	715.4	715.3
125°	763.7	764.0	764.6	765.2	765.8	766.4	765.8	765.2	764.6	764.0	763.7
127.5°	810.4	810.5	810.7	810.8	811.0	811.2	811.0	810.8	810.7	810.5	810.4
130°	853.4	853.3	853.1	852.9	852.7	852.5	852.7	852.9	853.1	853.3	853.4
132.5°	893.7	893.6	893.4	893.2	893.0	892.8	893.0	893.2	893.4	893.6	893.7
135°	933.2	933.0	932.6	932.2	931.8	931.4	931.8	932.2	932.6	933.0	933.2
137.5°	969.9	969.6	969.0	968.4	967.8	967.2	967.8	968.4	969.0	969.6	969.9
140°	1004.9	1004.4	1003.4	1002.4	1001.4	1000.4	1001.4	1002.4	1003.4	1004.4	1004.9
142.5°	1037.1	1036.6	1035.6	1034.7	1033.7	1032.7	1033.7	1034.7	1035.6	1036.6	1037.1
145°	1066.7	1066.2	1065.2	1064.2	1063.2	1062.2	1063.2	1064.2	1065.2	1066.2	1066.7
147.5°	1092.7	1092.3	1091.5	1090.7	1089.9	1089.1	1089.9	1090.7	1091.5	1092.3	1092.7
150°	1117.8	1117.3	1116.3	1115.3	1114.3	1113.3	1114.3	1115.3	1116.3	1117.3	1117.8
152.5°	1140.2	1139.5	1138.1	1136.8	1135.4	1134.0	1135.4	1136.8	1138.1	1139.5	1140.2
155°	1159.9	1159.1	1157.5	1156.0	1154.4	1152.8	1154.4	1156.0	1157.5	1159.1	1159.9
157.5°	1177.9	1177.1	1175.5	1173.9	1172.3	1170.7	1172.3	1173.9	1175.5	1177.1	1177.9
160°	1192.2	1191.5	1190.1	1188.7	1187.3	1185.9	1187.3	1188.7	1190.1	1191.5	1192.2
162.5°	1206.6	1205.7	1203.9	1202.1	1200.3	1198.5	1200.3	1202.1	1203.9	1205.7	1206.6
165°	1217.3	1216.6	1215.2	1213.8	1212.4	1211.0	1212.4	1213.8	1215.2	1216.6	1217.3
167.5°	1227.2	1226.3	1224.5	1222.7	1220.9	1219.1	1220.9	1222.7	1224.5	1226.3	1227.2
170°	1234.3	1233.4	1231.6	1229.9	1228.1	1226.3	1228.1	1229.9	1231.6	1233.4	1234.3
172.5°	1239.7	1238.8	1237.0	1235.3	1233.5	1231.7	1233.5	1235.3	1237.0	1238.8	1239.7
175°	1243.3	1242.3	1240.3	1238.3	1236.3	1234.3	1236.3	1238.3	1240.3	1242.3	1243.3
177.5°	1244.2	1243.3	1241.5	1239.7	1237.9	1236.1	1237.9	1239.7	1241.5	1243.3	1244.2
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7	630.7
2.5°	600.9	603.1	602.3	597.4	602.3	603.6	606.2	608.8	610.6	613.2	615.4
5°	563.2	567.6	570.3	567.6	576.4	577.7	583.8	587.3	592.6	597.0	600.5
7.5°	527.7	531.2	536.5	537.4	542.6	548.8	557.5	566.3	574.6	579.0	583.0
10°	489.6	495.7	503.6	501.9	509.8	519.4	528.6	542.6	549.7	557.5	564.6
12.5°	451.5	455.4	465.9	469.4	480.8	488.3	501.0	509.8	527.3	536.5	542.6
15°	384.8	401.1	414.2	430.0	444.9	458.9	470.3	486.1	501.4	508.5	518.5
17.5°	354.6	362.1	369.9	377.8	397.1	422.1	442.3	459.4	472.5	481.7	493.5
20°	323.0	330.5	339.3	346.7	358.5	376.5	401.5	430.9	446.6	456.3	467.7
22.5°	300.7	307.7	313.4	320.0	329.2	342.3	361.2	397.6	418.6	430.4	440.5
25°	276.6	285.3	291.5	296.3	303.8	318.2	333.6	354.2	391.9	401.1	415.1
27.5°	259.9	262.6	269.6	277.0	284.5	292.4	308.1	325.7	351.1	371.3	388.4
30°	240.2	246.8	253.3	256.4	263.0	274.4	284.0	302.9	322.6	338.4	359.0
32.5°	225.3	229.2	233.6	241.1	247.2	255.1	264.7	280.5	297.2	307.3	323.0
35°	208.6	211.3	220.5	223.5	229.7	237.6	247.2	259.5	277.5	285.3	296.7
37.5°	192.9	199.0	201.6	208.6	214.3	222.2	229.2	243.3	255.1	264.3	274.8
40°	180.6	183.2	188.0	194.2	199.0	205.1	213.9	224.0	236.7	244.1	253.3
42.5°	165.7	167.9	174.0	177.5	185.4	191.1	196.4	208.6	220.0	225.7	234.9
45°	149.5	154.7	158.7	165.7	170.1	177.1	183.7	192.4	202.9	209.5	214.8
47.5°	135.4	140.7	144.6	151.2	158.2	161.3	168.3	177.5	187.2	192.4	199.9
50°	124.0	125.8	133.2	136.3	143.8	149.9	154.7	162.6	173.1	176.2	182.3
52.5°	113.1	114.4	119.2	123.2	129.7	135.0	141.1	148.6	157.4	162.2	167.0
55°	103.4	104.3	106.5	110.9	115.3	121.9	127.6	134.6	142.0	147.3	151.7
57.5°	92.5	94.2	96.0	98.6	103.0	109.1	115.3	121.9	128.0	131.5	137.2
60°	79.8	82.4	85.5	88.5	91.6	96.0	103.0	109.1	114.8	117.9	122.3
62.5°	66.2	71.4	74.1	77.6	80.2	84.2	89.4	96.4	100.4	104.3	107.8
65°	59.6	60.0	60.5	64.0	68.8	72.8	77.6	82.8	89.0	91.6	94.2
67.5°	53.0	53.5	54.4	54.8	56.5	60.9	66.2	71.9	76.7	78.5	81.1
70°	46.5	46.5	48.2	48.7	49.1	49.5	53.9	59.6	64.0	66.2	69.3
72.5°	39.4	39.9	40.8	41.2	42.1	43.0	44.3	47.3	52.6	54.8	58.3
75°	32.4	32.9	33.3	33.8	35.1	35.5	36.8	38.6	40.8	43.4	45.6
77.5°	25.9	25.9	26.3	27.2	28.1	28.5	29.8	30.7	31.6	32.9	34.6
80°	19.3	19.7	19.7	20.6	20.6	21.0	21.5	22.8	23.7	24.5	25.4
82.5°	13.1	14.0	14.0	14.0	14.5	14.9	15.3	15.3	16.2	16.7	18.0
85°	7.9	8.3	8.3	8.3	7.9	8.8	8.8	9.2	9.2	9.2	9.6
87.5°	3.1	2.6	3.1	3.1	3.1	3.5	3.1	3.1	3.5	3.9	3.9
90°	21.9	20.9	19.9	18.9	17.9	16.3	14.7	13.2	11.6	10.8	9.7
92.5°	23.1	22.7	22.3	21.9	21.5	20.9	20.3	19.7	19.1	18.8	19.2
95°	38.9	37.9	37.0	36.0	35.0	33.6	32.2	30.8	29.4	28.7	32.0
97.5°	48.1	47.5	46.9	46.3	45.7	42.5	39.3	36.2	33.0	31.4	39.6
100°	57.5	55.9	54.3	52.7	51.1	47.7	44.3	41.0	37.6	35.9	49.5
102.5°	61.6	59.4	57.3	55.1	52.9	89.1	125.4	161.6	197.9	216.0	216.2
105°	63.4	61.2	59.1	56.9	54.7	109.1	163.5	217.8	272.2	299.4	296.4
107.5°	65.2	63.0	60.9	58.7	56.5	123.6	190.8	257.9	325.0	358.6	356.1
110°	77.2	97.1	117.0	137.0	156.9	214.5	272.0	329.6	387.1	415.9	413.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	111.9	197.8	283.7	369.5	455.4	458.8	462.2	465.5	468.9	470.6	468.8
115°	184.1	276.4	368.6	460.9	553.1	548.1	543.1	538.2	533.2	530.7	529.0
117.5°	487.5	516.0	544.5	573.0	601.5	598.1	594.7	591.3	587.9	586.2	584.2
120°	666.6	664.2	661.9	659.5	657.1	653.5	649.9	646.3	642.7	640.9	639.4
122.5°	714.7	713.5	712.4	711.2	710.0	706.0	702.0	698.0	694.0	692.0	690.4
125°	763.0	761.6	760.3	758.9	757.5	753.7	749.9	746.1	742.3	740.4	739.1
127.5°	809.4	807.4	805.4	803.4	801.4	798.4	795.4	792.4	789.4	787.9	786.5
130°	852.3	850.1	847.9	845.7	843.5	841.3	839.1	837.0	834.8	833.7	832.1
132.5°	892.8	891.0	889.2	887.4	885.6	883.4	881.2	879.1	876.9	875.8	874.5
135°	932.2	930.2	928.2	926.2	924.2	922.4	920.6	918.8	917.0	916.1	914.5
137.5°	968.9	966.9	964.9	962.9	960.9	958.9	956.9	955.0	953.0	952.0	950.8
140°	1004.0	1002.2	1000.4	998.6	996.8	994.6	992.4	990.2	988.0	986.9	986.1
142.5°	1036.3	1034.7	1033.2	1031.6	1030.0	1027.4	1024.8	1022.2	1019.6	1018.3	1017.6
145°	1066.0	1064.6	1063.2	1061.8	1060.4	1057.0	1053.6	1050.3	1046.9	1045.2	1045.3
147.5°	1092.2	1091.2	1090.2	1089.2	1088.2	1084.8	1081.4	1078.1	1074.7	1073.0	1073.3
150°	1117.2	1116.0	1114.8	1113.6	1112.4	1109.2	1106.0	1102.9	1099.7	1098.1	1098.8
152.5°	1139.6	1138.4	1137.2	1136.0	1134.8	1131.8	1128.8	1125.9	1122.9	1121.4	1122.2
155°	1159.3	1158.1	1157.0	1155.8	1154.6	1152.2	1149.8	1147.4	1145.0	1143.8	1144.7
157.5°	1177.2	1175.8	1174.4	1173.0	1171.6	1169.8	1168.0	1166.2	1164.4	1163.5	1164.3
160°	1191.6	1190.4	1189.2	1188.0	1186.8	1185.6	1184.4	1183.3	1182.1	1181.5	1182.1
162.5°	1205.9	1204.5	1203.1	1201.7	1200.3	1199.3	1198.3	1197.3	1196.3	1195.8	1196.4
165°	1216.6	1215.2	1213.8	1212.4	1211.0	1210.4	1209.8	1209.3	1208.7	1208.4	1209.0
167.5°	1226.5	1225.1	1223.7	1222.3	1220.9	1220.3	1219.7	1219.1	1218.5	1218.2	1218.8
170°	1233.6	1232.2	1230.9	1229.5	1228.1	1227.7	1227.3	1226.9	1226.5	1226.3	1226.9
172.5°	1239.0	1237.6	1236.3	1234.9	1233.5	1233.1	1232.7	1232.3	1231.9	1231.7	1232.3
175°	1242.6	1241.2	1239.8	1238.4	1237.0	1236.6	1236.2	1235.8	1235.4	1235.2	1235.9
177.5°	1243.5	1242.1	1240.7	1239.3	1237.9	1237.7	1237.5	1237.3	1237.1	1237.0	1237.7
180°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	630.7	630.7	630.7	630.7
2.5°	619.3	618.0	625.9	634.7
5°	606.6	608.8	618.9	631.2
7.5°	593.5	598.3	610.1	626.4
10°	575.1	583.8	601.8	618.5
12.5°	557.1	568.9	586.0	605.8
15°	536.9	550.1	571.1	594.8
17.5°	514.6	529.5	554.0	579.9
20°	490.9	510.6	536.5	564.6
22.5°	464.6	488.3	515.0	546.1
25°	439.2	465.1	491.8	527.7
27.5°	414.2	439.6	469.4	505.8
30°	389.2	412.5	444.5	483.5
32.5°	362.5	386.6	420.3	460.2
35°	337.9	362.1	393.6	433.1
37.5°	311.6	337.5	367.8	408.5
40°	281.0	311.2	340.6	379.6
42.5°	255.5	287.5	316.0	352.8
45°	235.4	265.6	289.3	325.2
47.5°	216.5	241.1	265.2	298.5
50°	198.6	217.4	242.4	272.2
52.5°	180.1	196.4	217.8	245.9
55°	163.5	178.8	198.1	219.6
57.5°	148.2	159.1	178.4	197.7
60°	131.1	142.5	157.4	173.6
62.5°	116.6	125.4	139.4	153.0
65°	101.3	109.6	120.1	132.8
67.5°	87.2	94.7	103.0	113.1
70°	74.5	80.2	86.3	95.1
72.5°	60.9	67.1	72.8	79.8
75°	50.0	52.6	57.4	62.2
77.5°	38.6	42.1	44.7	48.7
80°	27.6	30.7	31.6	34.6
82.5°	18.4	20.2	21.9	22.8
85°	10.5	11.4	13.1	13.6
87.5°	3.9	4.4	5.3	6.1
90°	7.5	5.3	3.1	0.9
92.5°	20.0	20.8	21.6	22.4
95°	38.6	45.1	51.7	58.3
97.5°	55.9	72.2	88.6	104.9
100°	76.8	104.1	131.4	158.7
102.5°	216.6	217.0	217.4	217.8
105°	290.4	284.5	278.5	272.5
107.5°	351.1	346.2	341.2	336.2
110°	409.6	405.5	401.3	397.1

TEST NUMBER: P999631

CATALOG NUMBER: SA2XXRDIP-B290D925UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	465.2	461.7	458.1	454.5
115°	525.6	522.2	518.8	515.4
117.5°	580.2	576.3	572.3	568.3
120°	636.4	633.5	630.5	627.5
122.5°	687.2	684.1	680.9	677.7
125°	736.5	734.0	731.4	728.8
127.5°	783.7	781.0	778.2	775.4
130°	828.9	825.7	822.5	819.3
132.5°	871.9	869.3	866.7	864.1
135°	911.3	908.2	905.0	901.8
137.5°	948.4	946.0	943.6	941.2
140°	984.5	983.0	981.4	979.8
142.5°	1016.2	1014.8	1013.4	1012.0
145°	1045.5	1045.7	1045.9	1046.1
147.5°	1073.9	1074.5	1075.1	1075.7
150°	1100.2	1101.6	1103.0	1104.4
152.5°	1123.8	1125.4	1127.0	1128.6
155°	1146.5	1148.3	1150.1	1151.9
157.5°	1165.9	1167.5	1169.1	1170.7
160°	1183.3	1184.4	1185.6	1186.8
162.5°	1197.6	1198.8	1200.0	1201.2
165°	1210.2	1211.3	1212.5	1213.7
167.5°	1220.0	1221.2	1222.4	1223.6
170°	1228.1	1229.3	1230.5	1231.7
172.5°	1233.5	1234.6	1235.8	1237.0
175°	1237.3	1238.7	1240.1	1241.5
177.5°	1239.1	1240.5	1241.9	1243.3
180°	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)