

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P999789

Luminaire Tested: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P999789
REPORT IS A COMBINATION OF REPORTS P988344 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4642.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 0.85 / 1.01
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40	40	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	35	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	31	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	27	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	24	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	21	21	21	18
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	19	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	18	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	16	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16800	16800	16800	16800
5°	16838	17843	16897	14255
10°	16653	18861	16771	11771
15°	16292	18866	16568	8843
20°	15857	15595	16202	7295
25°	15331	9745	15661	6206
30°	14658	6240	15056	5343
35°	13839	4794	14287	4573
40°	12927	4030	13479	4000
45°	11951	3431	12451	3357
50°	10952	2914	11464	2904
55°	9846	2533	10376	2500
60°	8864	1932	9331	1908
65°	7945	1454	8415	1650
70°	6929	1161	7475	1344
75°	5857	890	6394	1016
80°	4655	605	5006	666
85°	3235	313	3546	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 165°

Vertical Angle: 45°

Luminance: 15368 cd/sqm

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.7	2.2
10°-20°	281.0	6.1
20°-30°	361.6	7.8
30°-40°	343.1	7.4
40°-50°	294.0	6.3
50°-60°	223.9	4.8
60°-70°	141.2	3.0
70°-80°	70.5	1.5
80°-90°	19.8	0.4
90°-100°	31.6	0.7
100°-110°	117.7	2.5
110°-120°	312.1	6.7
120°-130°	517.6	11.1
130°-140°	549.8	11.8
140°-150°	511.0	11.0
150°-160°	410.8	8.8
160°-170°	264.7	5.7
170°-180°	91.1	2.0
0°-30°	743.3	16.0
0°-40°	1086.3	23.4
0°-60°	1604.3	34.6
0°-90°	1835.7	39.5
90°-120°	461.3	9.9
90°-150°	2039.7	43.9
90°-180°	2806.0	60.4
0°-180°	4642.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1061	1061	1061	1061	1061	
5°	1062	1181	1066	943	1062	101
15°	1001	1333	1018	625	1001	282
25°	888	711	907	453	888	408
35°	729	350	752	334	729	456
45°	547	243	570	238	547	422
55°	370	169	389	167	370	333
65°	224	88	237	100	224	222
75°	105	46	114	53	105	113
85°	23	13	25	14	23	26
90°	1	19	1	19	1	4
95°	45	30	45	30	45	53
105°	211	53	211	53	211	225
115°	398	57	398	57	398	392
125°	563	592	563	592	563	502
135°	697	720	697	720	697	538
145°	808	821	808	821	808	506
155°	890	891	890	891	890	410
165°	938	936	938	936	938	265
175°	959	954	959	954	959	91
180°	957	957	957	957	957	

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1067.9	1072.3	1074.5	1077.5	1084.1	1088.6	1095.2	1096.7	1095.9	1098.9	1090.8
5°	1062.0	1071.6	1080.4	1087.8	1099.6	1107.0	1115.1	1124.7	1126.9	1138.0	1131.3
7.5°	1053.9	1067.9	1080.4	1095.2	1112.9	1122.5	1135.0	1149.8	1156.4	1169.7	1173.4
10°	1040.6	1060.5	1081.9	1097.4	1121.7	1138.7	1150.5	1174.1	1189.6	1209.5	1206.6
12.5°	1019.2	1045.0	1073.8	1099.6	1131.3	1142.4	1164.5	1188.9	1208.8	1227.2	1243.4
15°	1000.8	1030.3	1062.0	1093.7	1129.9	1150.5	1172.6	1204.3	1225.7	1258.2	1272.2
17.5°	975.7	1013.3	1050.9	1086.3	1129.1	1152.7	1180.0	1211.0	1242.7	1273.7	1284.7
20°	949.9	990.5	1031.0	1079.0	1127.6	1150.5	1178.5	1216.9	1247.9	1272.2	1272.2
22.5°	918.9	968.3	1014.8	1060.5	1113.6	1146.8	1175.6	1220.6	1242.7	1247.9	1227.9
25°	888.0	937.4	988.3	1045.0	1105.5	1135.0	1167.5	1209.5	1216.9	1196.2	1144.6
27.5°	851.1	906.4	963.9	1025.1	1088.6	1125.4	1154.9	1183.0	1168.9	1113.6	1033.2
30°	813.5	873.2	938.1	996.4	1073.1	1107.0	1132.1	1140.2	1095.9	1006.0	902.0
32.5°	774.4	832.6	901.2	971.3	1048.7	1081.2	1097.4	1076.0	994.9	881.3	754.5
35°	728.7	794.3	865.8	938.8	1015.5	1039.9	1049.5	997.1	893.1	746.4	620.2
37.5°	687.4	753.0	829.7	904.2	978.7	991.9	982.4	900.5	768.5	623.2	500.0
40°	638.7	708.7	784.0	867.3	928.5	932.2	908.6	802.4	638.7	502.2	426.3
42.5°	593.7	664.5	739.7	824.5	871.0	858.5	826.7	687.4	533.2	432.9	371.7
45°	547.2	614.3	695.5	770.7	803.9	774.4	726.4	578.2	447.7	372.4	325.2
47.5°	502.2	564.9	645.3	717.6	723.5	690.3	633.5	484.5	387.9	327.5	289.1
50°	458.0	520.7	595.9	655.6	649.7	604.0	539.9	421.1	337.0	289.1	257.4
52.5°	413.7	470.5	543.5	590.7	565.7	521.4	458.0	357.0	294.3	252.2	227.9
55°	369.5	422.6	485.3	524.4	484.5	433.7	388.7	306.1	255.2	221.3	202.8
57.5°	332.6	374.7	432.2	455.8	407.8	368.0	328.9	263.3	221.3	196.9	175.5
60°	292.1	330.4	377.6	391.6	342.2	309.8	276.6	222.7	189.5	168.2	154.1
62.5°	257.4	289.1	325.2	325.2	281.7	257.4	232.3	186.6	159.3	142.3	135.7
65°	223.5	246.3	272.1	269.2	232.3	210.9	191.0	154.1	133.5	121.7	115.1
67.5°	190.3	208.0	224.9	214.6	188.1	169.6	151.2	124.6	110.6	102.5	93.7
70°	160.0	174.1	182.9	173.3	146.8	131.3	118.0	100.3	89.2	78.9	73.8
72.5°	134.2	140.1	143.1	131.3	109.2	100.3	90.7	78.2	68.6	63.4	62.0
75°	104.7	109.9	107.7	98.8	80.4	73.8	66.4	57.5	55.3	52.4	50.9
77.5°	81.9	81.9	78.2	70.1	57.5	52.4	49.4	45.0	42.8	42.0	40.6
80°	58.3	57.5	55.3	46.5	39.1	36.1	36.1	33.2	32.5	31.0	31.0
82.5°	38.4	38.4	35.4	28.0	25.8	25.1	24.3	22.9	22.9	22.1	22.1
85°	22.9	21.4	17.7	15.5	14.8	14.8	14.0	13.3	14.0	13.3	13.3
87.5°	10.3	8.1	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
90°	0.7	2.4	4.1	5.8	7.5	8.3	8.9	10.2	11.4	12.7	13.9
92.5°	17.3	16.7	16.1	15.4	14.8	14.5	14.7	15.2	15.7	16.1	16.6
95°	45.0	39.9	34.9	29.8	24.7	22.2	22.7	23.8	24.9	25.9	27.0
97.5°	81.0	68.4	55.8	43.1	30.5	24.2	25.4	27.9	30.4	32.8	35.3
100°	122.6	101.5	80.4	59.3	38.2	27.7	29.0	31.6	34.3	36.9	39.5
102.5°	168.3	168.0	167.7	167.4	167.1	166.9	152.9	124.9	96.9	68.9	40.9
105°	210.6	215.2	219.8	224.4	229.0	231.3	210.3	168.3	126.3	84.3	42.3
107.5°	259.7	263.6	267.4	271.3	275.2	277.1	251.2	199.3	147.4	95.5	43.6
110°	306.8	310.0	313.3	316.5	319.8	321.4	299.2	254.7	210.2	165.7	121.2



TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	351.2	354.0	356.7	359.5	362.2	363.6	362.3	359.7	357.1	354.5	351.9
115°	398.3	400.9	403.5	406.2	408.8	410.1	412.0	415.9	419.7	423.6	427.4
117.5°	439.1	442.2	445.3	448.4	451.5	453.0	454.3	456.9	459.6	462.2	464.8
120°	484.9	487.2	489.5	491.8	494.1	495.2	496.6	499.4	502.1	504.9	507.7
122.5°	523.6	526.1	528.5	531.0	533.5	534.7	536.2	539.3	542.4	545.5	548.6
125°	563.1	565.1	567.1	569.1	571.1	572.1	573.6	576.5	579.4	582.4	585.3
127.5°	599.1	601.3	603.4	605.6	607.7	608.8	610.0	612.3	614.6	616.9	619.2
130°	633.1	635.6	638.0	640.5	643.0	644.2	645.0	646.7	648.4	650.1	651.8
132.5°	667.7	669.7	671.7	673.7	675.7	676.7	677.5	679.2	680.9	682.6	684.3
135°	696.8	699.3	701.7	704.2	706.7	707.9	708.6	710.0	711.3	712.7	714.1
137.5°	727.3	729.1	731.0	732.8	734.7	735.6	736.4	737.9	739.4	741.0	742.5
140°	757.1	758.3	759.5	760.8	762.0	762.6	763.4	765.1	766.8	768.5	770.2
142.5°	782.0	783.1	784.2	785.3	786.4	786.9	787.9	789.9	791.9	793.9	795.9
145°	808.3	808.1	808.0	807.8	807.7	807.6	808.9	811.5	814.2	816.8	819.4
147.5°	831.2	830.7	830.3	829.8	829.3	829.1	830.4	833.0	835.7	838.3	840.9
150°	853.3	852.2	851.2	850.1	849.0	848.5	849.7	852.2	854.7	857.1	859.6
152.5°	872.1	870.9	869.6	868.4	867.1	866.5	867.7	870.0	872.3	874.6	876.9
155°	890.1	888.7	887.3	885.9	884.5	883.8	884.7	886.6	888.4	890.3	892.1
157.5°	904.6	903.4	902.2	900.9	899.7	899.1	899.8	901.2	902.5	903.9	905.3
160°	917.1	916.2	915.2	914.3	913.4	912.9	913.4	914.3	915.2	916.2	917.1
162.5°	928.2	927.3	926.3	925.4	924.5	924.0	924.4	925.2	925.9	926.7	927.5
165°	937.9	937.0	936.0	935.1	934.2	933.7	933.9	934.4	934.9	935.3	935.8
167.5°	945.5	944.6	943.6	942.7	941.8	941.3	941.5	942.0	942.5	942.9	943.4
170°	951.7	950.8	949.9	949.0	948.1	947.6	947.7	948.0	948.3	948.6	948.9
172.5°	955.9	955.0	954.0	953.1	952.2	951.7	951.9	952.2	952.5	952.8	953.1
175°	959.3	958.2	957.2	956.1	955.0	954.5	954.7	955.0	955.3	955.6	955.9
177.5°	960.7	959.6	958.6	957.5	956.4	955.9	956.0	956.1	956.3	956.4	956.6
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1098.9	1100.4	1102.6	1112.9	1114.4	1117.3	1115.8	1115.8	1116.6	1115.1	1115.8
5°	1146.1	1148.3	1159.4	1171.9	1174.8	1171.9	1175.6	1180.7	1180.7	1180.7	1179.3
7.5°	1190.3	1198.4	1211.0	1229.4	1233.1	1236.8	1243.4	1239.0	1240.5	1247.1	1244.9
10°	1233.1	1244.9	1258.9	1274.4	1282.5	1287.7	1290.6	1297.3	1312.8	1295.1	1301.7
12.5°	1273.7	1290.6	1305.4	1322.3	1328.2	1334.9	1337.1	1343.0	1343.0	1342.3	1347.4
15°	1300.2	1315.7	1329.0	1340.0	1341.5	1340.0	1338.6	1339.3	1341.5	1332.7	1337.8
17.5°	1306.1	1307.6	1312.0	1307.6	1308.3	1292.8	1284.0	1281.8	1261.1	1261.9	1278.8
20°	1277.4	1252.3	1245.6	1221.3	1206.6	1166.7	1165.3	1154.2	1110.7	1124.0	1121.0
22.5°	1198.4	1155.7	1098.9	1070.9	1056.8	1014.8	982.4	959.5	944.0	928.5	921.9
25°	1094.5	1025.1	944.7	889.4	881.3	842.2	782.5	754.5	721.3	711.0	728.7
27.5°	960.2	870.3	779.5	694.7	679.2	643.8	613.6	593.7	555.3	553.1	554.6
30°	778.1	687.4	611.4	556.1	517.7	501.5	481.6	466.8	451.4	457.3	458.7
32.5°	639.4	553.1	482.3	452.8	435.1	424.8	407.8	398.3	391.6	389.4	388.7
35°	508.1	450.6	418.9	390.1	379.8	372.4	359.9	355.5	349.6	350.3	350.3
37.5°	435.1	387.2	363.6	348.8	339.3	335.6	327.5	323.0	319.3	317.9	320.1
40°	375.4	342.2	327.5	314.2	306.1	304.6	300.2	295.0	290.6	291.3	293.5
42.5°	331.9	312.7	295.0	284.7	278.8	276.6	272.9	269.2	269.2	267.0	266.2
45°	297.2	281.7	267.0	257.4	253.7	250.8	246.3	245.6	242.6	243.4	244.1
47.5°	266.2	253.7	242.6	233.1	229.4	228.6	224.2	221.3	221.3	220.5	219.8
50°	238.2	225.7	216.1	210.9	205.8	204.3	203.6	202.8	201.3	201.3	202.1
52.5°	215.4	202.8	195.4	191.0	188.1	186.6	186.6	185.9	185.9	185.9	185.1
55°	190.3	180.0	174.1	172.6	171.1	170.4	169.6	168.2	167.4	168.9	167.4
57.5°	166.7	163.0	157.8	156.4	152.7	152.7	150.5	149.0	147.5	149.0	149.0
60°	148.2	143.1	140.1	135.7	132.8	129.8	126.1	125.4	123.9	123.2	122.4
62.5°	129.1	124.6	117.3	110.6	106.2	103.3	101.8	101.0	101.0	100.3	100.3
65°	107.7	97.4	93.7	91.5	90.7	90.0	88.5	87.8	88.5	87.8	88.5
67.5°	84.1	82.6	80.4	78.9	78.2	77.4	77.4	76.7	76.7	76.7	76.7
70°	73.0	69.3	68.6	67.1	67.1	66.4	66.4	66.4	66.4	65.6	67.1
72.5°	60.5	58.3	57.5	56.8	56.8	56.8	56.1	56.1	56.1	55.3	56.1
75°	49.4	48.7	47.2	47.2	46.5	47.2	46.5	46.5	45.7	46.5	46.5
77.5°	39.8	39.1	38.4	38.4	37.6	37.6	37.6	37.6	37.6	37.6	38.4
80°	30.2	29.5	28.8	29.5	28.8	29.5	28.8	28.8	29.5	28.8	28.8
82.5°	22.1	21.4	21.4	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
85°	13.3	12.5	12.5	13.3	12.5	13.3	12.5	12.5	12.5	13.3	13.3
87.5°	5.9	6.6	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	6.6
90°	14.7	15.4	16.2	16.9	17.3	17.5	17.8	18.1	18.4	18.7	18.4
92.5°	16.9	17.2	17.5	17.8	18.0	18.1	18.2	18.4	18.5	18.7	18.5
95°	27.8	28.6	29.3	30.1	30.5	30.4	30.3	30.1	30.0	29.8	30.0
97.5°	35.8	36.2	36.7	37.2	37.4	37.5	37.6	37.8	37.9	38.1	37.9
100°	40.7	41.9	43.2	44.4	45.0	45.2	45.5	45.8	46.1	46.4	46.1
102.5°	42.6	44.3	46.0	47.7	48.5	48.7	49.2	49.7	50.1	50.6	50.1
105°	44.0	45.7	47.4	49.1	49.9	50.2	50.8	51.4	52.0	52.6	52.0
107.5°	45.3	47.0	48.7	50.4	51.3	51.6	52.2	52.8	53.4	54.0	53.4
110°	105.8	90.4	75.0	59.6	51.9	52.2	52.8	53.5	54.1	54.7	54.1

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	285.5	219.2	152.8	86.5	53.3	53.5	54.0	54.5	54.9	55.4	54.9
115°	356.1	284.9	213.6	142.3	106.7	101.2	90.1	79.0	67.9	56.8	67.9
117.5°	442.8	420.8	398.7	376.7	365.7	345.5	305.2	264.9	224.5	184.2	224.5
120°	509.5	511.4	513.2	515.1	516.0	505.6	484.8	464.1	443.3	422.5	443.3
122.5°	549.5	550.4	551.3	552.2	552.7	552.8	552.9	553.1	553.2	553.4	553.2
125°	586.4	587.4	588.5	589.6	590.1	590.3	590.8	591.3	591.7	592.2	591.7
127.5°	620.8	622.3	623.9	625.4	626.2	626.3	626.4	626.6	626.7	626.9	626.7
130°	653.5	655.2	656.9	658.6	659.4	659.3	659.2	659.0	658.9	658.7	658.9
132.5°	685.7	687.1	688.5	689.9	690.6	690.5	690.4	690.2	690.1	689.9	690.1
135°	715.7	717.2	718.8	720.3	721.1	720.9	720.6	720.3	720.0	719.7	720.0
137.5°	744.1	745.6	747.2	748.7	749.5	749.3	748.8	748.3	747.9	747.4	747.9
140°	771.6	773.0	774.4	775.8	776.5	776.1	775.3	774.6	773.8	773.0	773.8
142.5°	797.1	798.3	799.6	800.8	801.4	801.0	800.2	799.5	798.7	797.9	798.7
145°	820.5	821.6	822.7	823.8	824.3	823.9	823.1	822.4	821.6	820.8	821.6
147.5°	841.7	842.4	843.2	843.9	844.3	844.0	843.4	842.8	842.2	841.6	842.2
150°	860.5	861.4	862.3	863.2	863.7	863.3	862.6	861.8	861.1	860.3	861.1
152.5°	877.8	878.8	879.7	880.6	881.1	880.6	879.5	878.4	877.3	876.2	877.3
155°	893.0	894.0	894.9	895.8	896.3	895.7	894.5	893.2	892.0	890.8	892.0
157.5°	906.4	907.4	908.5	909.6	910.1	909.5	908.3	907.0	905.8	904.6	905.8
160°	918.0	918.9	919.8	920.7	921.2	920.7	919.6	918.5	917.5	916.4	917.5
162.5°	928.6	929.6	930.7	931.8	932.3	931.6	930.2	928.9	927.5	926.1	927.5
165°	936.9	937.9	939.0	940.1	940.6	940.1	939.0	937.9	936.9	935.8	936.9
167.5°	944.5	945.5	946.6	947.7	948.2	947.5	946.1	944.8	943.4	942.0	943.4
170°	950.0	951.1	952.2	953.3	953.8	953.1	951.7	950.4	949.0	947.6	949.0
172.5°	954.2	955.2	956.3	957.4	957.9	957.2	955.8	954.5	953.1	951.7	953.1
175°	957.0	958.0	959.1	960.2	960.7	959.9	958.4	956.9	955.3	953.8	955.3
177.5°	957.7	958.7	959.8	960.9	961.4	960.7	959.3	958.0	956.6	955.2	956.6
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1118.8	1113.6	1112.2	1113.6	1112.2	1112.9	1107.7	1088.6	1093.7	1085.6	1090.0
5°	1182.2	1177.8	1168.2	1166.7	1165.3	1163.8	1156.4	1139.4	1132.8	1121.7	1121.0
7.5°	1242.7	1242.7	1235.3	1230.2	1223.5	1218.4	1208.8	1183.7	1173.4	1160.1	1152.7
10°	1302.4	1283.3	1291.4	1286.2	1270.0	1267.0	1249.3	1234.6	1214.7	1201.4	1189.6
12.5°	1345.2	1339.3	1331.9	1327.5	1323.1	1313.5	1301.7	1264.1	1253.8	1227.2	1213.9
15°	1343.7	1340.0	1342.3	1342.3	1340.8	1338.6	1329.0	1301.7	1284.0	1258.2	1235.3
17.5°	1271.5	1281.0	1290.6	1297.3	1312.0	1318.7	1327.5	1311.3	1300.2	1278.1	1253.8
20°	1145.3	1168.9	1197.0	1202.9	1216.1	1255.2	1272.9	1286.9	1291.4	1284.0	1264.1
22.5°	969.8	989.7	1057.6	1056.1	1075.3	1121.7	1173.4	1215.4	1248.6	1267.0	1259.7
25°	759.6	787.7	823.8	851.1	913.8	983.1	1047.3	1114.4	1171.9	1222.8	1235.3
27.5°	574.5	611.4	640.2	676.3	708.0	789.9	872.5	977.2	1044.3	1140.9	1191.1
30°	464.6	481.6	510.4	527.3	542.8	605.5	699.2	802.4	920.4	1031.8	1118.1
32.5°	396.8	408.6	430.0	437.3	453.6	495.6	554.6	649.0	770.7	905.7	1019.2
35°	356.2	368.8	373.2	379.8	393.1	419.6	460.2	528.8	638.7	770.7	906.4
37.5°	321.6	328.2	340.7	345.2	349.6	369.5	396.8	444.7	517.7	626.1	776.6
40°	297.2	300.9	307.5	311.2	314.2	328.2	352.5	385.0	438.8	521.4	660.1
42.5°	271.4	275.8	280.3	284.7	288.4	299.4	314.2	345.2	381.3	444.0	544.3
45°	246.3	249.3	254.4	257.4	262.6	271.4	284.7	306.1	338.5	378.3	459.5
47.5°	223.5	227.2	229.4	233.1	236.7	246.3	258.9	272.9	299.4	338.5	397.5
50°	202.8	207.2	210.2	210.9	213.9	222.7	233.1	248.5	265.5	295.7	347.4
52.5°	188.1	188.8	191.0	194.0	193.2	198.4	208.0	219.8	237.5	261.8	299.4
55°	171.1	173.3	174.8	175.5	175.5	180.0	185.1	196.2	210.2	230.1	261.8
57.5°	149.7	151.9	156.4	157.8	160.0	162.3	164.5	171.8	183.6	202.8	228.6
60°	127.6	129.1	133.5	136.4	137.9	143.8	146.8	152.7	159.3	173.3	197.7
62.5°	102.5	104.0	106.2	109.2	112.1	121.0	128.3	134.2	139.4	149.0	168.9
65°	89.2	90.0	91.5	92.2	92.9	96.6	103.3	111.4	121.0	128.3	140.1
67.5°	77.4	78.2	78.9	80.4	81.1	81.9	84.8	87.0	96.6	106.9	115.8
70°	66.4	67.9	68.6	68.6	69.3	70.8	72.3	75.2	78.2	83.3	94.4
72.5°	56.1	56.8	58.3	58.3	58.3	59.7	61.2	62.7	64.2	67.1	71.5
75°	46.5	47.9	47.9	47.9	48.7	48.7	50.2	51.6	53.1	55.3	56.8
77.5°	38.4	38.4	38.4	38.4	39.1	39.1	39.8	41.3	42.0	42.8	44.3
80°	28.8	29.5	29.5	29.5	30.2	30.2	30.2	31.7	32.5	32.5	33.9
82.5°	21.4	21.4	21.4	22.1	21.4	22.1	22.1	22.9	22.1	22.9	23.6
85°	13.3	13.3	13.3	14.0	14.0	14.0	14.0	14.0	14.0	14.0	14.8
87.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.4	6.6	6.6
90°	18.1	17.8	17.5	17.3	16.9	16.2	15.4	14.7	13.9	12.7	11.4
92.5°	18.4	18.2	18.1	18.0	17.8	17.5	17.2	16.9	16.6	16.1	15.7
95°	30.1	30.3	30.4	30.5	30.1	29.3	28.6	27.8	27.0	25.9	24.9
97.5°	37.8	37.6	37.5	37.4	37.2	36.7	36.2	35.8	35.3	32.8	30.4
100°	45.8	45.5	45.2	45.0	44.4	43.2	41.9	40.7	39.5	36.9	34.3
102.5°	49.7	49.2	48.7	48.5	47.7	46.0	44.3	42.6	40.9	38.9	36.9
105°	51.4	50.8	50.2	49.9	49.1	47.4	45.7	44.0	42.3	40.3	38.3
107.5°	52.8	52.2	51.6	51.3	50.4	48.7	47.0	45.3	43.6	41.9	40.3
110°	53.5	52.8	52.2	51.9	51.6	50.4	48.7	47.0	45.3	43.6	41.9

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	54.5	54.0	53.5	53.3	86.5	152.8	219.2	285.5	351.9	354.5	357.1
115°	79.0	90.1	101.2	106.7	142.3	213.6	284.9	356.1	427.4	423.6	419.7
117.5°	264.9	305.2	345.5	365.7	376.7	398.7	420.8	442.8	464.8	462.2	459.6
120°	464.1	484.8	505.6	516.0	515.1	513.2	511.4	509.5	507.7	504.9	502.1
122.5°	553.1	552.9	552.8	552.7	552.2	551.3	550.4	549.5	548.6	545.5	542.4
125°	591.3	590.8	590.3	590.1	589.6	588.5	587.4	586.4	585.3	582.4	579.4
127.5°	626.6	626.4	626.3	626.2	625.4	623.9	622.3	620.8	619.2	616.9	614.6
130°	659.0	659.2	659.3	659.4	658.6	656.9	655.2	653.5	651.8	650.1	648.4
132.5°	690.2	690.4	690.5	690.6	689.9	688.5	687.1	685.7	684.3	682.6	680.9
135°	720.3	720.6	720.9	721.1	720.3	718.8	717.2	715.7	714.1	712.7	711.3
137.5°	748.3	748.8	749.3	749.5	748.7	747.2	745.6	744.1	742.5	741.0	739.4
140°	774.6	775.3	776.1	776.5	775.8	774.4	773.0	771.6	770.2	768.5	766.8
142.5°	799.5	800.2	801.0	801.4	800.8	799.6	798.3	797.1	795.9	793.9	791.9
145°	822.4	823.1	823.9	824.3	823.8	822.7	821.6	820.5	819.4	816.8	814.2
147.5°	842.8	843.4	844.0	844.3	843.9	843.2	842.4	841.7	840.9	838.3	835.7
150°	861.8	862.6	863.3	863.7	863.2	862.3	861.4	860.5	859.6	857.1	854.7
152.5°	878.4	879.5	880.6	881.1	880.6	879.7	878.8	877.8	876.9	874.6	872.3
155°	893.2	894.5	895.7	896.3	895.8	894.9	894.0	893.0	892.1	890.3	888.4
157.5°	907.0	908.3	909.5	910.1	909.6	908.5	907.4	906.4	905.3	903.9	902.5
160°	918.5	919.6	920.7	921.2	920.7	919.8	918.9	918.0	917.1	916.2	915.2
162.5°	928.9	930.2	931.6	932.3	931.8	930.7	929.6	928.6	927.5	926.7	925.9
165°	937.9	939.0	940.1	940.6	940.1	939.0	937.9	936.9	935.8	935.3	934.9
167.5°	944.8	946.1	947.5	948.2	947.7	946.6	945.5	944.5	943.4	942.9	942.5
170°	950.4	951.7	953.1	953.8	953.3	952.2	951.1	950.0	948.9	948.6	948.3
172.5°	954.5	955.8	957.2	957.9	957.4	956.3	955.2	954.2	953.1	952.8	952.5
175°	956.9	958.4	959.9	960.7	960.2	959.1	958.0	957.0	955.9	955.6	955.3
177.5°	958.0	959.3	960.7	961.4	960.9	959.8	958.7	957.7	956.6	956.4	956.3
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1083.4	1079.7	1079.7	1077.5	1077.5	1065.7	1065.7	1069.4	1065.0	1059.8	1052.4
5°	1111.4	1103.3	1101.1	1098.1	1088.6	1073.8	1067.9	1065.7	1056.8	1045.8	1033.2
7.5°	1138.0	1124.7	1118.1	1111.4	1098.9	1078.2	1066.4	1058.3	1045.0	1028.1	1011.9
10°	1163.8	1146.8	1129.9	1121.7	1104.0	1078.2	1061.3	1048.0	1028.8	1006.0	983.1
12.5°	1187.4	1152.0	1149.0	1132.8	1107.0	1077.5	1051.7	1032.5	1008.2	981.6	955.1
15°	1208.0	1171.9	1154.2	1139.4	1105.5	1068.6	1041.4	1017.8	985.3	955.1	922.6
17.5°	1218.4	1179.3	1167.5	1143.1	1108.5	1060.5	1023.7	994.9	959.5	923.4	886.5
20°	1228.7	1183.0	1163.8	1146.8	1099.6	1045.0	1003.7	970.6	931.5	888.7	848.1
22.5°	1233.8	1183.0	1160.1	1136.5	1090.8	1028.1	979.4	940.3	894.6	851.1	802.4
25°	1225.0	1178.5	1151.2	1126.9	1075.3	1007.4	951.4	907.1	858.5	809.0	759.6
27.5°	1202.9	1168.2	1136.5	1111.4	1053.9	980.9	921.9	871.7	821.6	766.3	716.1
30°	1161.6	1146.1	1121.0	1093.0	1030.3	957.3	887.2	835.6	780.3	725.0	672.6
32.5°	1097.4	1110.7	1094.5	1070.1	1002.3	924.8	850.3	798.0	737.5	677.8	629.8
35°	1019.2	1066.4	1057.6	1040.6	972.8	890.2	815.7	752.3	691.8	631.3	583.4
37.5°	933.7	1005.2	1012.6	1002.3	938.8	854.8	772.9	711.0	649.0	587.8	539.1
40°	816.4	926.3	949.9	954.3	903.4	812.0	726.4	666.0	604.8	545.0	486.0
42.5°	708.7	847.4	876.9	895.3	858.5	770.0	683.7	616.6	556.1	502.2	443.2
45°	607.7	752.3	800.2	823.8	807.6	722.0	632.8	570.1	514.8	465.4	408.6
47.5°	503.7	649.0	716.1	753.7	753.7	673.3	584.1	522.2	469.1	427.0	376.9
50°	434.4	555.3	624.7	674.1	687.4	623.9	539.9	479.4	429.2	383.5	345.2
52.5°	370.2	478.6	536.2	587.8	626.1	570.8	490.4	435.9	386.5	343.7	313.4
55°	320.1	401.2	453.6	510.4	553.1	517.0	442.5	389.4	346.6	311.2	285.4
57.5°	272.1	342.9	385.7	435.9	481.6	454.3	394.6	348.8	311.2	280.3	257.4
60°	231.6	289.1	322.3	361.4	418.2	399.0	349.6	307.5	277.3	249.3	230.1
62.5°	196.9	242.6	270.7	298.7	350.3	341.5	303.1	270.7	244.9	221.3	205.0
65°	161.5	199.1	221.3	245.6	286.9	290.6	259.6	236.7	213.1	192.5	177.7
67.5°	130.5	160.0	180.0	200.6	233.8	244.1	222.7	203.6	183.6	166.7	153.4
70°	105.5	126.1	140.9	157.1	184.4	196.9	185.9	172.6	156.4	142.3	130.5
72.5°	83.3	96.6	105.5	118.0	140.1	152.7	151.9	140.1	128.3	118.7	109.2
75°	61.2	71.5	78.9	87.0	104.7	116.5	119.5	114.3	102.5	95.1	87.8
77.5°	46.5	52.4	56.1	62.0	74.5	84.8	89.2	87.8	79.7	73.8	68.6
80°	35.4	36.9	38.4	40.6	50.9	60.5	63.4	62.7	58.3	56.1	50.2
82.5°	25.1	25.8	26.6	27.3	31.0	39.1	42.0	43.5	39.8	37.6	32.5
85°	14.8	15.5	15.5	17.0	17.7	19.9	25.1	25.1	24.3	21.4	20.7
87.5°	7.4	7.4	6.6	6.6	7.4	8.1	9.6	11.1	9.6	8.9	8.1
90°	10.2	8.9	8.3	7.5	5.8	4.1	2.4	0.7	2.4	4.1	5.8
92.5°	15.2	14.7	14.5	14.8	15.4	16.1	16.7	17.3	16.7	16.1	15.4
95°	23.8	22.7	22.2	24.7	29.8	34.9	39.9	45.0	39.9	34.9	29.8
97.5°	27.9	25.4	24.2	30.5	43.1	55.8	68.4	81.0	68.4	55.8	43.1
100°	31.6	29.0	27.7	38.2	59.3	80.4	101.5	122.6	101.5	80.4	59.3
102.5°	124.9	152.9	166.9	167.1	167.4	167.7	168.0	168.3	168.0	167.7	167.4
105°	168.3	210.3	231.3	229.0	224.4	219.8	215.2	210.6	215.2	219.8	224.4
107.5°	199.3	251.2	277.1	275.2	271.3	267.4	263.6	259.7	263.6	267.4	271.3
110°	254.7	299.2	321.4	319.8	316.5	313.3	310.0	306.8	310.0	313.3	316.5

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	359.7	362.3	363.6	362.2	359.5	356.7	354.0	351.2	354.0	356.7	359.5
115°	415.9	412.0	410.1	408.8	406.2	403.5	400.9	398.3	400.9	403.5	406.2
117.5°	456.9	454.3	453.0	451.5	448.4	445.3	442.2	439.1	442.2	445.3	448.4
120°	499.4	496.6	495.2	494.1	491.8	489.5	487.2	484.9	487.2	489.5	491.8
122.5°	539.3	536.2	534.7	533.5	531.0	528.5	526.1	523.6	526.1	528.5	531.0
125°	576.5	573.6	572.1	571.1	569.1	567.1	565.1	563.1	565.1	567.1	569.1
127.5°	612.3	610.0	608.8	607.7	605.6	603.4	601.3	599.1	601.3	603.4	605.6
130°	646.7	645.0	644.2	643.0	640.5	638.0	635.6	633.1	635.6	638.0	640.5
132.5°	679.2	677.5	676.7	675.7	673.7	671.7	669.7	667.7	669.7	671.7	673.7
135°	710.0	708.6	707.9	706.7	704.2	701.7	699.3	696.8	699.3	701.7	704.2
137.5°	737.9	736.4	735.6	734.7	732.8	731.0	729.1	727.3	729.1	731.0	732.8
140°	765.1	763.4	762.6	762.0	760.8	759.5	758.3	757.1	758.3	759.5	760.8
142.5°	789.9	787.9	786.9	786.4	785.3	784.2	783.1	782.0	783.1	784.2	785.3
145°	811.5	808.9	807.6	807.7	807.8	808.0	808.1	808.3	808.1	808.0	807.8
147.5°	833.0	830.4	829.1	829.3	829.8	830.3	830.7	831.2	830.7	830.3	829.8
150°	852.2	849.7	848.5	849.0	850.1	851.2	852.2	853.3	852.2	851.2	850.1
152.5°	870.0	867.7	866.5	867.1	868.4	869.6	870.9	872.1	870.9	869.6	868.4
155°	886.6	884.7	883.8	884.5	885.9	887.3	888.7	890.1	888.7	887.3	885.9
157.5°	901.2	899.8	899.1	899.7	900.9	902.2	903.4	904.6	903.4	902.2	900.9
160°	914.3	913.4	912.9	913.4	914.3	915.2	916.2	917.1	916.2	915.2	914.3
162.5°	925.2	924.4	924.0	924.5	925.4	926.3	927.3	928.2	927.3	926.3	925.4
165°	934.4	933.9	933.7	934.2	935.1	936.0	937.0	937.9	937.0	936.0	935.1
167.5°	942.0	941.5	941.3	941.8	942.7	943.6	944.6	945.5	944.6	943.6	942.7
170°	948.0	947.7	947.6	948.1	949.0	949.9	950.8	951.7	950.8	949.9	949.0
172.5°	952.2	951.9	951.7	952.2	953.1	954.0	955.0	955.9	955.0	954.0	953.1
175°	955.0	954.7	954.5	955.0	956.1	957.2	958.2	959.3	958.2	957.2	956.1
177.5°	956.1	956.0	955.9	956.4	957.5	958.6	959.6	960.7	959.6	958.6	957.5
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1049.5	1050.2	1052.4	1045.8	1035.5	1031.0	1017.8	1015.5	1013.3	1013.3	1015.5
5°	1025.9	1022.9	1023.7	1011.1	996.4	987.5	969.1	972.0	962.4	956.5	958.0
7.5°	1000.1	991.9	991.2	975.0	956.5	940.3	921.1	916.7	907.9	897.5	893.1
10°	967.6	961.7	950.6	932.2	908.6	895.3	869.5	854.0	851.8	836.3	830.4
12.5°	934.4	924.1	913.0	887.2	860.7	839.3	820.1	803.1	791.3	778.1	769.2
15°	896.1	883.5	871.0	843.7	812.7	791.3	762.6	737.5	702.8	675.6	660.1
17.5°	854.0	840.0	823.1	792.8	762.6	733.1	680.0	650.5	626.1	609.9	600.3
20°	810.5	795.0	778.1	747.8	695.5	643.8	614.3	591.5	576.7	560.5	548.7
22.5°	764.8	748.6	730.1	682.9	627.6	591.5	568.6	547.2	525.8	517.0	511.1
25°	722.0	707.3	683.7	619.5	576.0	542.8	517.0	503.0	491.9	480.1	469.1
27.5°	677.8	650.5	617.3	563.5	536.2	502.2	483.8	473.5	454.3	446.2	441.0
30°	624.7	594.4	562.7	524.4	492.7	469.1	452.1	435.1	424.1	416.0	407.1
32.5°	570.8	542.1	522.2	482.3	458.7	434.4	418.2	407.8	391.6	386.5	382.8
35°	524.4	500.0	482.3	449.9	427.8	405.6	393.8	378.3	368.0	358.4	352.5
37.5°	478.6	465.4	446.9	419.6	396.0	378.3	362.1	357.0	342.9	337.8	331.9
40°	446.9	427.0	411.5	387.9	368.0	348.8	338.5	326.7	317.1	309.0	306.8
42.5°	408.6	393.8	385.0	359.2	338.5	327.5	314.9	301.6	294.3	287.6	279.5
45°	379.8	366.5	354.0	333.4	314.9	300.9	289.8	281.0	268.5	265.5	253.0
47.5°	349.6	336.3	326.7	306.1	289.1	275.8	267.7	255.9	245.6	239.0	233.1
50°	319.3	308.3	299.4	281.7	267.0	253.0	241.9	230.1	225.7	214.6	210.9
52.5°	290.6	283.2	273.6	256.7	241.9	230.1	218.3	208.7	202.1	196.2	191.8
55°	266.2	254.4	250.0	231.6	219.0	206.5	196.2	190.3	182.2	178.5	174.8
57.5°	239.0	232.3	224.9	210.9	196.9	185.1	177.7	168.9	164.5	160.0	157.1
60°	215.4	205.8	199.9	188.1	175.5	164.5	157.8	151.2	145.3	141.6	135.7
62.5°	188.1	180.7	177.0	164.5	154.1	143.8	137.9	131.3	126.9	120.2	112.8
65°	164.5	158.6	154.1	143.8	134.2	124.6	118.7	110.6	104.7	101.0	100.3
67.5°	143.8	139.4	132.8	123.2	113.6	106.2	99.6	92.9	92.2	90.7	90.7
70°	121.0	116.5	112.8	102.5	94.4	86.3	84.8	82.6	80.4	79.7	78.2
72.5°	101.0	97.4	92.9	84.1	76.0	73.8	72.3	70.8	68.6	67.9	67.1
75°	81.9	76.7	73.8	65.6	63.4	62.0	60.5	58.3	56.8	56.1	54.6
77.5°	62.7	57.5	57.5	53.1	51.6	49.4	47.9	46.5	45.7	44.3	44.3
80°	44.3	44.3	42.8	40.6	38.4	37.6	35.4	34.7	33.9	34.7	33.2
82.5°	32.5	29.5	29.5	28.0	26.6	25.8	24.3	24.3	23.6	23.6	23.6
85°	18.4	18.4	17.7	16.2	15.5	15.5	14.8	14.8	14.0	14.0	13.3
87.5°	7.4	6.6	7.4	6.6	6.6	5.9	5.9	5.9	5.2	5.9	5.2
90°	7.5	8.3	8.9	10.2	11.4	12.7	13.9	14.7	15.4	16.2	16.9
92.5°	14.8	14.5	14.7	15.2	15.7	16.1	16.6	16.9	17.2	17.5	17.8
95°	24.7	22.2	22.7	23.8	24.9	25.9	27.0	27.8	28.6	29.3	30.1
97.5°	30.5	24.2	25.4	27.9	30.4	32.8	35.3	35.8	36.2	36.7	37.2
100°	38.2	27.7	29.0	31.6	34.3	36.9	39.5	40.7	41.9	43.2	44.4
102.5°	167.1	166.9	152.9	124.9	96.9	68.9	40.9	42.6	44.3	46.0	47.7
105°	229.0	231.3	210.3	168.3	126.3	84.3	42.3	44.0	45.7	47.4	49.1
107.5°	275.2	277.1	251.2	199.3	147.4	95.5	43.6	45.3	47.0	48.7	50.4
110°	319.8	321.4	299.2	254.7	210.2	165.7	121.2	105.8	90.4	75.0	59.6

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	362.2	363.6	362.3	359.7	357.1	354.5	351.9	285.5	219.2	152.8	86.5
115°	408.8	410.1	412.0	415.9	419.7	423.6	427.4	356.1	284.9	213.6	142.3
117.5°	451.5	453.0	454.3	456.9	459.6	462.2	464.8	442.8	420.8	398.7	376.7
120°	494.1	495.2	496.6	499.4	502.1	504.9	507.7	509.5	511.4	513.2	515.1
122.5°	533.5	534.7	536.2	539.3	542.4	545.5	548.6	549.5	550.4	551.3	552.2
125°	571.1	572.1	573.6	576.5	579.4	582.4	585.3	586.4	587.4	588.5	589.6
127.5°	607.7	608.8	610.0	612.3	614.6	616.9	619.2	620.8	622.3	623.9	625.4
130°	643.0	644.2	645.0	646.7	648.4	650.1	651.8	653.5	655.2	656.9	658.6
132.5°	675.7	676.7	677.5	679.2	680.9	682.6	684.3	685.7	687.1	688.5	689.9
135°	706.7	707.9	708.6	710.0	711.3	712.7	714.1	715.7	717.2	718.8	720.3
137.5°	734.7	735.6	736.4	737.9	739.4	741.0	742.5	744.1	745.6	747.2	748.7
140°	762.0	762.6	763.4	765.1	766.8	768.5	770.2	771.6	773.0	774.4	775.8
142.5°	786.4	786.9	787.9	789.9	791.9	793.9	795.9	797.1	798.3	799.6	800.8
145°	807.7	807.6	808.9	811.5	814.2	816.8	819.4	820.5	821.6	822.7	823.8
147.5°	829.3	829.1	830.4	833.0	835.7	838.3	840.9	841.7	842.4	843.2	843.9
150°	849.0	848.5	849.7	852.2	854.7	857.1	859.6	860.5	861.4	862.3	863.2
152.5°	867.1	866.5	867.7	870.0	872.3	874.6	876.9	877.8	878.8	879.7	880.6
155°	884.5	883.8	884.7	886.6	888.4	890.3	892.1	893.0	894.0	894.9	895.8
157.5°	899.7	899.1	899.8	901.2	902.5	903.9	905.3	906.4	907.4	908.5	909.6
160°	913.4	912.9	913.4	914.3	915.2	916.2	917.1	918.0	918.9	919.8	920.7
162.5°	924.5	924.0	924.4	925.2	925.9	926.7	927.5	928.6	929.6	930.7	931.8
165°	934.2	933.7	933.9	934.4	934.9	935.3	935.8	936.9	937.9	939.0	940.1
167.5°	941.8	941.3	941.5	942.0	942.5	942.9	943.4	944.5	945.5	946.6	947.7
170°	948.1	947.6	947.7	948.0	948.3	948.6	948.9	950.0	951.1	952.2	953.3
172.5°	952.2	951.7	951.9	952.2	952.5	952.8	953.1	954.2	955.2	956.3	957.4
175°	955.0	954.5	954.7	955.0	955.3	955.6	955.9	957.0	958.0	959.1	960.2
177.5°	956.4	955.9	956.0	956.1	956.3	956.4	956.6	957.7	958.7	959.8	960.9
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1015.5	1014.1	1009.6	1011.1	1008.9	1008.9	1007.4	1007.4	1007.4	1011.1	1008.9
5°	960.2	955.1	949.9	947.7	945.5	943.3	943.3	942.5	949.2	947.7	953.6
7.5°	891.6	890.2	879.8	879.8	876.2	874.7	878.4	879.1	879.8	881.3	885.0
10°	830.4	826.7	812.0	813.5	811.3	808.3	810.5	809.0	814.2	815.7	814.2
12.5°	758.2	751.5	735.3	727.2	718.3	711.7	719.8	713.9	734.6	740.5	756.7
15°	662.3	649.7	638.7	638.7	630.6	624.7	628.4	635.0	639.4	646.1	649.0
17.5°	598.1	593.0	584.1	578.9	576.7	574.5	574.5	577.5	587.1	586.3	592.2
20°	543.5	540.6	536.2	529.5	527.3	525.8	525.8	525.8	532.5	538.4	542.1
22.5°	505.9	503.7	500.8	491.9	487.5	486.0	489.7	491.9	497.1	501.5	505.2
25°	468.3	463.2	458.0	455.0	452.8	452.8	454.3	455.0	457.3	459.5	463.9
27.5°	437.3	433.7	426.3	418.2	418.2	416.0	417.4	418.9	424.1	431.4	435.1
30°	402.7	401.9	399.0	396.0	393.1	391.6	394.6	396.8	397.5	401.2	401.2
32.5°	377.6	372.4	367.3	364.3	362.9	362.1	362.9	365.8	365.8	370.2	375.4
35°	352.5	349.6	344.4	339.3	337.8	334.1	337.0	340.0	345.2	347.4	349.6
37.5°	325.2	321.6	319.3	317.9	314.9	315.7	313.4	317.9	322.3	321.6	323.0
40°	304.6	298.0	291.3	290.6	289.8	289.1	289.1	289.8	292.8	295.7	300.2
42.5°	278.0	275.8	269.9	264.0	262.6	261.1	259.6	262.6	268.5	273.6	275.8
45°	250.8	247.8	246.3	241.9	239.0	238.2	236.7	240.4	245.6	247.8	249.3
47.5°	225.7	224.9	220.5	221.3	219.0	219.8	219.0	221.3	221.3	223.5	224.9
50°	208.7	206.5	204.3	202.8	200.6	200.6	199.9	200.6	203.6	206.5	205.8
52.5°	191.8	188.1	187.3	186.6	185.1	186.6	184.4	185.1	188.1	189.5	188.8
55°	171.8	171.1	169.6	168.2	167.4	166.7	166.7	166.7	169.6	171.8	172.6
57.5°	156.4	152.7	149.7	149.7	146.8	146.0	147.5	148.2	150.5	151.9	153.4
60°	135.0	133.5	129.1	126.9	122.4	121.7	121.7	124.6	128.3	133.5	135.0
62.5°	112.1	109.9	109.2	109.2	109.2	109.2	109.2	109.2	109.2	109.9	109.9
65°	99.6	100.3	99.6	98.8	99.6	99.6	98.8	98.8	98.8	99.6	100.3
67.5°	89.2	88.5	89.2	88.5	87.8	87.8	87.0	87.8	88.5	89.2	89.2
70°	77.4	77.4	76.7	77.4	76.7	76.0	75.2	75.2	76.7	77.4	77.4
72.5°	66.4	66.4	65.6	65.6	64.2	64.2	64.9	64.2	64.2	66.4	66.4
75°	55.3	54.6	53.8	53.8	53.1	53.1	53.1	52.4	53.8	53.8	54.6
77.5°	43.5	43.5	43.5	42.8	42.8	42.0	42.0	42.8	42.8	42.8	43.5
80°	33.2	33.2	33.2	32.5	31.7	31.7	31.7	31.7	31.7	32.5	31.7
82.5°	22.9	22.9	22.9	22.9	22.9	22.1	22.1	22.1	22.9	22.9	22.1
85°	14.0	13.3	14.0	14.0	13.3	14.0	13.3	13.3	12.5	12.5	13.3
87.5°	5.9	5.2	4.4	4.4	5.2	4.4	4.4	4.4	5.2	4.4	4.4
90°	17.3	17.5	17.8	18.1	18.4	18.7	18.4	18.1	17.8	17.5	17.3
92.5°	18.0	18.1	18.2	18.4	18.5	18.7	18.5	18.4	18.2	18.1	18.0
95°	30.5	30.4	30.3	30.1	30.0	29.8	30.0	30.1	30.3	30.4	30.5
97.5°	37.4	37.5	37.6	37.8	37.9	38.1	37.9	37.8	37.6	37.5	37.4
100°	45.0	45.2	45.5	45.8	46.1	46.4	46.1	45.8	45.5	45.2	45.0
102.5°	48.5	48.7	49.2	49.7	50.1	50.6	50.1	49.7	49.2	48.7	48.5
105°	49.9	50.2	50.8	51.4	52.0	52.6	52.0	51.4	50.8	50.2	49.9
107.5°	51.3	51.6	52.2	52.8	53.4	54.0	53.4	52.8	52.2	51.6	51.3
110°	51.9	52.2	52.8	53.5	54.1	54.7	54.1	53.5	52.8	52.2	51.9

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	53.3	53.5	54.0	54.5	54.9	55.4	54.9	54.5	54.0	53.5	53.3
115°	106.7	101.2	90.1	79.0	67.9	56.8	67.9	79.0	90.1	101.2	106.7
117.5°	365.7	345.5	305.2	264.9	224.5	184.2	224.5	264.9	305.2	345.5	365.7
120°	516.0	505.6	484.8	464.1	443.3	422.5	443.3	464.1	484.8	505.6	516.0
122.5°	552.7	552.8	552.9	553.1	553.2	553.4	553.2	553.1	552.9	552.8	552.7
125°	590.1	590.3	590.8	591.3	591.7	592.2	591.7	591.3	590.8	590.3	590.1
127.5°	626.2	626.3	626.4	626.6	626.7	626.9	626.7	626.6	626.4	626.3	626.2
130°	659.4	659.3	659.2	659.0	658.9	658.7	658.9	659.0	659.2	659.3	659.4
132.5°	690.6	690.5	690.4	690.2	690.1	689.9	690.1	690.2	690.4	690.5	690.6
135°	721.1	720.9	720.6	720.3	720.0	719.7	720.0	720.3	720.6	720.9	721.1
137.5°	749.5	749.3	748.8	748.3	747.9	747.4	747.9	748.3	748.8	749.3	749.5
140°	776.5	776.1	775.3	774.6	773.8	773.0	773.8	774.6	775.3	776.1	776.5
142.5°	801.4	801.0	800.2	799.5	798.7	797.9	798.7	799.5	800.2	801.0	801.4
145°	824.3	823.9	823.1	822.4	821.6	820.8	821.6	822.4	823.1	823.9	824.3
147.5°	844.3	844.0	843.4	842.8	842.2	841.6	842.2	842.8	843.4	844.0	844.3
150°	863.7	863.3	862.6	861.8	861.1	860.3	861.1	861.8	862.6	863.3	863.7
152.5°	881.1	880.6	879.5	878.4	877.3	876.2	877.3	878.4	879.5	880.6	881.1
155°	896.3	895.7	894.5	893.2	892.0	890.8	892.0	893.2	894.5	895.7	896.3
157.5°	910.1	909.5	908.3	907.0	905.8	904.6	905.8	907.0	908.3	909.5	910.1
160°	921.2	920.7	919.6	918.5	917.5	916.4	917.5	918.5	919.6	920.7	921.2
162.5°	932.3	931.6	930.2	928.9	927.5	926.1	927.5	928.9	930.2	931.6	932.3
165°	940.6	940.1	939.0	937.9	936.9	935.8	936.9	937.9	939.0	940.1	940.6
167.5°	948.2	947.5	946.1	944.8	943.4	942.0	943.4	944.8	946.1	947.5	948.2
170°	953.8	953.1	951.7	950.4	949.0	947.6	949.0	950.4	951.7	953.1	953.8
172.5°	957.9	957.2	955.8	954.5	953.1	951.7	953.1	954.5	955.8	957.2	957.9
175°	960.7	959.9	958.4	956.9	955.3	953.8	955.3	956.9	958.4	959.9	960.7
177.5°	961.4	960.7	959.3	958.0	956.6	955.2	956.6	958.0	959.3	960.7	961.4
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3	1061.3
2.5°	1011.1	1014.8	1013.3	1005.2	1013.3	1015.5	1020.0	1024.4	1027.3	1031.8	1035.5
5°	947.7	955.1	959.5	955.1	969.8	972.0	982.4	988.3	997.1	1004.5	1010.4
7.5°	888.0	893.9	902.7	904.2	913.0	923.4	938.1	952.9	966.9	974.2	980.9
10°	823.8	834.1	847.4	844.4	857.7	873.9	889.4	913.0	924.8	938.1	949.9
12.5°	759.6	766.3	784.0	789.9	809.0	821.6	843.0	857.7	887.2	902.7	913.0
15°	647.5	674.8	696.9	723.5	748.6	772.2	791.3	817.9	843.7	855.5	872.5
17.5°	596.6	609.2	622.5	635.7	668.2	710.2	744.1	772.9	795.0	810.5	830.4
20°	543.5	556.1	570.8	583.4	603.3	633.5	675.6	725.0	751.5	767.7	786.9
22.5°	505.9	517.7	527.3	538.4	553.9	576.0	607.7	668.9	704.3	724.2	741.2
25°	465.4	480.1	490.4	498.6	511.1	535.4	561.2	595.9	659.3	674.8	698.4
27.5°	437.3	441.8	453.6	466.1	478.6	491.9	518.5	548.0	590.7	624.7	653.4
30°	404.2	415.2	426.3	431.4	442.5	461.7	477.9	509.6	542.8	569.4	604.0
32.5°	379.1	385.7	393.1	405.6	416.0	429.2	445.5	472.0	500.0	517.0	543.5
35°	351.1	355.5	371.0	376.1	386.5	399.7	416.0	436.6	466.8	480.1	499.3
37.5°	324.5	334.8	339.3	351.1	360.6	373.9	385.7	409.3	429.2	444.7	462.4
40°	303.9	308.3	316.4	326.7	334.8	345.2	359.9	376.9	398.3	410.8	426.3
42.5°	278.8	282.5	292.8	298.7	312.0	321.6	330.4	351.1	370.2	379.8	395.3
45°	251.5	260.3	267.0	278.8	286.2	298.0	309.0	323.8	341.5	352.5	361.4
47.5°	227.9	236.7	243.4	254.4	266.2	271.4	283.2	298.7	314.9	323.8	336.3
50°	208.7	211.7	224.2	229.4	241.9	252.2	260.3	273.6	291.3	296.5	306.8
52.5°	190.3	192.5	200.6	207.2	218.3	227.2	237.5	250.0	264.8	272.9	281.0
55°	174.1	175.5	179.2	186.6	194.0	205.0	214.6	226.4	239.0	247.8	255.2
57.5°	155.6	158.6	161.5	165.9	173.3	183.6	194.0	205.0	215.4	221.3	230.8
60°	134.2	138.7	143.8	149.0	154.1	161.5	173.3	183.6	193.2	198.4	205.8
62.5°	111.4	120.2	124.6	130.5	135.0	141.6	150.5	162.3	168.9	175.5	181.4
65°	100.3	101.0	101.8	107.7	115.8	122.4	130.5	139.4	149.7	154.1	158.6
67.5°	89.2	90.0	91.5	92.2	95.1	102.5	111.4	121.0	129.1	132.0	136.4
70°	78.2	78.2	81.1	81.9	82.6	83.3	90.7	100.3	107.7	111.4	116.5
72.5°	66.4	67.1	68.6	69.3	70.8	72.3	74.5	79.7	88.5	92.2	98.1
75°	54.6	55.3	56.1	56.8	59.0	59.7	62.0	64.9	68.6	73.0	76.7
77.5°	43.5	43.5	44.3	45.7	47.2	47.9	50.2	51.6	53.1	55.3	58.3
80°	32.5	33.2	33.2	34.7	34.7	35.4	36.1	38.4	39.8	41.3	42.8
82.5°	22.1	23.6	23.6	23.6	24.3	25.1	25.8	25.8	27.3	28.0	30.2
85°	13.3	14.0	14.0	14.0	13.3	14.8	14.8	15.5	15.5	15.5	16.2
87.5°	5.2	4.4	5.2	5.2	5.2	5.9	5.2	5.2	5.9	6.6	6.6
90°	16.9	16.2	15.4	14.7	13.9	12.7	11.4	10.2	8.9	8.3	7.5
92.5°	17.8	17.5	17.2	16.9	16.6	16.1	15.7	15.2	14.7	14.5	14.8
95°	30.1	29.3	28.6	27.8	27.0	25.9	24.9	23.8	22.7	22.2	24.7
97.5°	37.2	36.7	36.2	35.8	35.3	32.8	30.4	27.9	25.4	24.2	30.5
100°	44.4	43.2	41.9	40.7	39.5	36.9	34.3	31.6	29.0	27.7	38.2
102.5°	47.7	46.0	44.3	42.6	40.9	68.9	96.9	124.9	152.9	166.9	167.1
105°	49.1	47.4	45.7	44.0	42.3	84.3	126.3	168.3	210.3	231.3	229.0
107.5°	50.4	48.7	47.0	45.3	43.6	95.5	147.4	199.3	251.2	277.1	275.2
110°	59.6	75.0	90.4	105.8	121.2	165.7	210.2	254.7	299.2	321.4	319.8

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	86.5	152.8	219.2	285.5	351.9	354.5	357.1	359.7	362.3	363.6	362.2
115°	142.3	213.6	284.9	356.1	427.4	423.6	419.7	415.9	412.0	410.1	408.8
117.5°	376.7	398.7	420.8	442.8	464.8	462.2	459.6	456.9	454.3	453.0	451.5
120°	515.1	513.2	511.4	509.5	507.7	504.9	502.1	499.4	496.6	495.2	494.1
122.5°	552.2	551.3	550.4	549.5	548.6	545.5	542.4	539.3	536.2	534.7	533.5
125°	589.6	588.5	587.4	586.4	585.3	582.4	579.4	576.5	573.6	572.1	571.1
127.5°	625.4	623.9	622.3	620.8	619.2	616.9	614.6	612.3	610.0	608.8	607.7
130°	658.6	656.9	655.2	653.5	651.8	650.1	648.4	646.7	645.0	644.2	643.0
132.5°	689.9	688.5	687.1	685.7	684.3	682.6	680.9	679.2	677.5	676.7	675.7
135°	720.3	718.8	717.2	715.7	714.1	712.7	711.3	710.0	708.6	707.9	706.7
137.5°	748.7	747.2	745.6	744.1	742.5	741.0	739.4	737.9	736.4	735.6	734.7
140°	775.8	774.4	773.0	771.6	770.2	768.5	766.8	765.1	763.4	762.6	762.0
142.5°	800.8	799.6	798.3	797.1	795.9	793.9	791.9	789.9	787.9	786.9	786.4
145°	823.8	822.7	821.6	820.5	819.4	816.8	814.2	811.5	808.9	807.6	807.7
147.5°	843.9	843.2	842.4	841.7	840.9	838.3	835.7	833.0	830.4	829.1	829.3
150°	863.2	862.3	861.4	860.5	859.6	857.1	854.7	852.2	849.7	848.5	849.0
152.5°	880.6	879.7	878.8	877.8	876.9	874.6	872.3	870.0	867.7	866.5	867.1
155°	895.8	894.9	894.0	893.0	892.1	890.3	888.4	886.6	884.7	883.8	884.5
157.5°	909.6	908.5	907.4	906.4	905.3	903.9	902.5	901.2	899.8	899.1	899.7
160°	920.7	919.8	918.9	918.0	917.1	916.2	915.2	914.3	913.4	912.9	913.4
162.5°	931.8	930.7	929.6	928.6	927.5	926.7	925.9	925.2	924.4	924.0	924.5
165°	940.1	939.0	937.9	936.9	935.8	935.3	934.9	934.4	933.9	933.7	934.2
167.5°	947.7	946.6	945.5	944.5	943.4	942.9	942.5	942.0	941.5	941.3	941.8
170°	953.3	952.2	951.1	950.0	948.9	948.6	948.3	948.0	947.7	947.6	948.1
172.5°	957.4	956.3	955.2	954.2	953.1	952.8	952.5	952.2	951.9	951.7	952.2
175°	960.2	959.1	958.0	957.0	955.9	955.6	955.3	955.0	954.7	954.5	955.0
177.5°	960.9	959.8	958.7	957.7	956.6	956.4	956.3	956.1	956.0	955.9	956.4
180°	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2	957.2

TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1061.3	1061.3	1061.3	1061.3
2.5°	1042.1	1039.9	1053.2	1067.9
5°	1020.7	1024.4	1041.4	1062.0
7.5°	998.6	1006.7	1026.6	1053.9
10°	967.6	982.4	1012.6	1040.6
12.5°	937.4	957.3	986.0	1019.2
15°	903.4	925.6	961.0	1000.8
17.5°	865.8	890.9	932.2	975.7
20°	826.0	859.2	902.7	949.9
22.5°	781.8	821.6	866.6	918.9
25°	739.0	782.5	827.5	888.0
27.5°	696.9	739.7	789.9	851.1
30°	654.9	694.0	747.8	813.5
32.5°	609.9	650.5	707.3	774.4
35°	568.6	609.2	662.3	728.7
37.5°	524.4	567.9	618.8	687.4
40°	472.7	523.6	573.0	638.7
42.5°	430.0	483.8	531.7	593.7
45°	396.0	446.9	486.8	547.2
47.5°	364.3	405.6	446.2	502.2
50°	334.1	365.8	407.8	458.0
52.5°	303.1	330.4	366.5	413.7
55°	275.1	300.9	333.4	369.5
57.5°	249.3	267.7	300.2	332.6
60°	220.5	239.7	264.8	292.1
62.5°	196.2	210.9	234.5	257.4
65°	170.4	184.4	202.1	223.5
67.5°	146.8	159.3	173.3	190.3
70°	125.4	135.0	145.3	160.0
72.5°	102.5	112.8	122.4	134.2
75°	84.1	88.5	96.6	104.7
77.5°	64.9	70.8	75.2	81.9
80°	46.5	51.6	53.1	58.3
82.5°	31.0	33.9	36.9	38.4
85°	17.7	19.2	22.1	22.9
87.5°	6.6	7.4	8.9	10.3
90°	5.8	4.1	2.4	0.7
92.5°	15.4	16.1	16.7	17.3
95°	29.8	34.9	39.9	45.0
97.5°	43.1	55.8	68.4	81.0
100°	59.3	80.4	101.5	122.6
102.5°	167.4	167.7	168.0	168.3
105°	224.4	219.8	215.2	210.6
107.5°	271.3	267.4	263.6	259.7
110°	316.5	313.3	310.0	306.8



TEST NUMBER: P999789

CATALOG NUMBER: SA2XXRDIP-B485D725UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	359.5	356.7	354.0	351.2
115°	406.2	403.5	400.9	398.3
117.5°	448.4	445.3	442.2	439.1
120°	491.8	489.5	487.2	484.9
122.5°	531.0	528.5	526.1	523.6
125°	569.1	567.1	565.1	563.1
127.5°	605.6	603.4	601.3	599.1
130°	640.5	638.0	635.6	633.1
132.5°	673.7	671.7	669.7	667.7
135°	704.2	701.7	699.3	696.8
137.5°	732.8	731.0	729.1	727.3
140°	760.8	759.5	758.3	757.1
142.5°	785.3	784.2	783.1	782.0
145°	807.8	808.0	808.1	808.3
147.5°	829.8	830.3	830.7	831.2
150°	850.1	851.2	852.2	853.3
152.5°	868.4	869.6	870.9	872.1
155°	885.9	887.3	888.7	890.1
157.5°	900.9	902.2	903.4	904.6
160°	914.3	915.2	916.2	917.1
162.5°	925.4	926.3	927.3	928.2
165°	935.1	936.0	937.0	937.9
167.5°	942.7	943.6	944.6	945.5
170°	949.0	949.9	950.8	951.7
172.5°	953.1	954.0	955.0	955.9
175°	956.1	957.2	958.2	959.3
177.5°	957.5	958.6	959.6	960.7
180°	957.2	957.2	957.2	957.2

(END OF REPORT)